



SlimSeal | SlimSeal Standard Connectors

TE Internal #: 2-2106124-2

Plug & Socket Lighting Connectors, Wire-to-Wire, 1 Position, .1 mm [2.5 in] Centerline, Sealable, Wire & Cable, 400 VAC, SlimSeal Standard Connectors

[View on TE.com >](#)

Connectors > Lighting Connectors > Plug & Socket Lighting Connectors



Connector System: **Wire-to-Wire**

Number of Positions: 1

Centerline (Pitch): .1 mm [2.5 in]

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

| | |
|-----------------------------------|--------------|
| Connector System | Wire-to-Wire |
| Sealable | Yes |
| Connector & Contact Terminates To | Wire & Cable |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 1 |
|---------------------|---|

Electrical Characteristics

| | |
|-------------------|---------|
| Operating Voltage | 300 VDC |
|-------------------|---------|

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Contact Features

| | |
|------------------------------|-------|
| Contact Current Rating (Max) | 3.5 A |
|------------------------------|-------|

Housing Features

| | |
|--------------------|---------------|
| Centerline (Pitch) | .1 mm[2.5 in] |
|--------------------|---------------|

Usage Conditions

Operating Temperature Range

-40 – 105 °C[-40 – 221 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JUNE
2023 (235)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per
homogenous material. Also BFR/CFR/PVC
Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2106136-2
Assembly, Receptacle, 2-Position



TE Part # 2106136-3
Assembly, Receptacle, 3-Position




TE Part # 2106136-4
Assembly, Receptacle, 4-Position





TE Part # 2154852-1
SlimSeal Assy, Receptacle, 1-Position



Also in the Series | SlimSeal Standard Connectors



Customers Also Bought





Documents

Product Drawings

[Contact, Tab, Tin Plated, 22-26 AWG](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2-2106124-2_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2106124-2_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2106124-2_A1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SLIMSEAL_SSL_CONNECOTS](#)

English

Product Specifications

[Application Specification](#)

English