



Product: <u>943662080</u> ☑

24 V DC DIN rail power supply unit

# **Product Description**

24 V DC DIN rail power supply unit

# **Technical Specifications**

# **Product description**

Type:	RPS 80 EEC
Description:	24 V DC DIN rail power supply unit
Part Number:	943662080

### **More Interfaces**

Voltage input:	1 x Bi-stable, quick-connect spring clamp terminals, 3-pin
Voltage output:	1 x Bi-stable, quick-connect spring clamp terminals, 4-pin

# **Power requirements**

Current consumption:	max. 1.8-1.0 A at 100-240 V AC; max. 0.85 - 0.3 A at 110 - 300 V DC
Input voltage:	100-240 V AC (+/-15%); 50-60Hz or; 110 to 300 V DC (-20/+25%)
Operating Voltage:	230 V
Output current:	3.4-3.0 A continuous; min 5.0-4.5 A for typ. 4 sec
Redundancy functions:	Power supply units can be connected in parallel
Activation Current:	13 A at 230 V AC

# **Power Output**

24 - 28 V DC (typ. 24.1 V) external adjustable	
--	--

## Software

Diagnostics:	LED (DC OK, Overload)	

# **Ambient conditions**

Operating temperature:	-25-+70 °C
Note:	from 60    C derating
Storage/transport temperature:	-40-+85 °C
Relative humidity (non-condensing):	5-95 %

# **Mechanical construction**

Dimensions (WxHxD):	32 mm x 124 mm x 102 mm
Weight:	440 g
Mounting:	DIN Rail
Protection class:	IP20

# **Mechanical stability**

IEC 60068-2-6 vibration:	Operating: 2 500Hz 0,5m²/s³
IEC 60068-2-27 shock:	10 g, 11 ms duration

#### **EMC** interference immunity

EN 61000-4-2 electrostatic discharge (ESD):	± 4 kV contact discharge; ± 8 kV air discharge
EN 61000-4-3 electromagnetic field:	10 V/m (80 MHz 2700 MHz)
EN 61000-4-4 fast transients (burst):	2 kV power line
EN 61000-4-5 surge voltage:	power lines: 2 kV (line/earth), 1 kV (line/line)
EN 61000-4-6 Conducted Immunity:	10 V (150 kHz 80 MHz)

### **EMC** emitted immunity

EN 55032:	EN 55032 Class A

### **Approvals**

Basis Standard:	CE
Safety of industrial control equipment:	cUL 60950-1, cUL 508
Safety of information technology equipment:	cUL 60950-1
Hazardous locations:	ISA 12.12.01 Class 1 Div. 2 (pending)
Shipbuilding:	DNV

### Scope of delivery and accessories

Scope of delivery:	Rail power supply, Description and operating manual

#### **Further Instructions**

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html

#### History

Update and Revision:	Revision Number: 0.106 Revision Date: 03-10-2023

#### Variants

Item #	Туре
943662080	RPS 80 EEC

# © 2023 Belden, Inc

#### All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.