Sub-base with plug-in electromechanical relay ABE7 - 16 channels - relay 10 mm





Main Range of Product Modicon ABE7 **Product or Component** Sub-base with plug-in electromechanical relay Type Sub-base type Output sub-base [Us] rated supply 19...30 V IEC 61131-2 voltage Number of Channels 16

Comple	emen	tary
--------	------	------

o o in promontary		
Supply voltage type	DC	
Product Compatibility	ABR7S23	
Contacts type and composition	1 C/O	
Status LED	Channel status 1 LED per channel Green) Power ON 1 LED Green)	
Polarity distribution	Volt-free	
Short-circuit protection	1 A internal fuse, 5 x 20 mm, fast blow PLC end)	
Fixing mode	By clips 35 mm symmetrical DIN rail) By screws solid plate with fixing kit)	
Maximum supply current	1 A	
Voltage drop on power supply fuse	0.3 V	
[Ui] rated insulation voltage	2000 V terminals/mounting rails 300 V coil circuit/contact circuits IEC 60947-1	
[Uimp] rated impulse withstand voltage	2.5 kV	
Installation category	II IEC 60664-1	
Tightening torque	5.31 lbf.in (0.6 N.m) flat Ø 3.5 mm	
Net Weight	1.71 lb(US) (0.775 kg)	

Environment

LIMIOIIIIEII	
Product Certifications	UL BV GL DNV LROS (Lloyds register of shipping) CSA EAC
IP degree of protection	IP2x conforming to IEC 60529
Resistance to incandescent wire	1382 °F (750 °C) IEC 60695-2-11
Shock resistance	15 gn 11 ms IEC 60068-2-27
Vibration resistance	2 gn 10150 Hz)IEC 60068-2-6
Resistance to electrostatic discharge	4 KV contact) level 3 IEC 61000-4-2 8 kV air) level 3 IEC 61000-4-2
Resistance to radiated fields	9.14 V/m (10 V/m) 260000001000000000 Hz)IEC 61000-4-3 level 3
Resistance to fast transients	2 kV level 3 IEC 61000-4-4
Ambient air temperature for operation	23140 °F (-560 °C) IEC 61131-2
Ambient air temperature for storage	-40176 °F (-4080 °C) IEC 61131-2
Pollution degree	2 IEC 60664-1

Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	3389110644678
Nbr. of units in pkg.	1
Package weight(Lbs)	26.56 oz (753 g)
Returnability	No
Country of origin	LV

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.03 in (7.7 cm)
Package 1 width	3.74 in (9.5 cm)
Package 1 Length	8.66 in (22 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	21.10 lb(US) (9.57 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)


Offer Sustainability

Sustainable offer status	Green Premium product	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
REACh Regulation	REACh Declaration	
REACh free of SVHC	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
Mercury free	Yes	
RoHS exemption information	€Yes	
China RoHS Regulation	China RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End Of Life Information	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	

Contractual warranty


warranty 10 months	Warranty	18 months	
--------------------	----------	-----------	--

Dimensions




(1) ABE7BV10 / BV20, ABE7BV10E / BV20E

Mounting




Wiring Diagram



(1) 16 channels

Curves for Determining Cable Type and Length According to the Current

16-channel Sub-base




- L Cable length
- I_T Total current per sub base (A)
- I_A Average current per channel (mA)
- (1) TSXCDP••2 and ABFH20H••0 cables with c.s.a. 0.08 mm² (AWG 28).
- (2) TSXCDP••3 cables with c.s.a. 0.34 mm² (AWG 22).
- (3) Cables with c.s.a. 0.13 mm² (AWG 26).

The curves are given for a voltage drop of 1 V in the cable. For n volts tolerance, multiply the length determined from the graph by n.

Electrical Durability (in Millions of Operating Cycles) Conforming to IEC 60947-5-1


DC Loads

DC12 curves



DC12control of resistive loads and of solid state loads isolated by optocoupler, I/R ≤ 1 ms.


DC13 curves



DC13switching electromagnets, L/R ≤ 2 x (Ue x le) in ms, Ue: rated operational voltage, le: rated operational current (with a protective diode on the load, DC12 curves must be used with a coefficient of 0.9 applied to the number in millions of operating cycles)


AC Loads

AC12 curves




AC12control of resistive loads and of solid state loads isolated by optocoupler, $\cos \phi \ge 0.9$.

AC14 curves



AC14control of small electromagnetic loads \leq 72 VA, make: $\cos \varphi = 0.3$, break: $\cos \varphi = 0.3$.

AC15 curves



AC15control of electromagnetic loads > 72 VA, make: $\cos \phi$ = 0.7, break: $\cos \phi$ = 0.4.