



- 1. ALL DIMENSIONS ARE IN MILLIMETERS [IN].
- 2. DIMENSIONS APPLY AFTER FINISHING.
- 3. MANUFACTURE TO BE COMPLIANT WITH EU ROHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
- 4. ELECTRICAL SPECIFICATIONS ARE FOR LISTED FOR REFERENCE ONLY.

1. CONTACT RESISTANCE: NTE $300 m\Omega$

2. INSULATION RESISTANCE: $1M\Omega$ MAX


3. DIELECTRIC RESISTANCE: 500VAC

- 5. MECHANICAL PROPERTIES
 - 1. MATERIAL: LCP UL94V-0, WHITE
 - 2. OPERATING TEMPERATURE: -25º +85°C
- 6. PACKAGE TAPE AND REEL IAW ASTM EIA-481-F

1. PITCH: 20mm

2. TAPE SIZE: 56mm

3. EMBOSSED CARRIER



©2023 TE Connectivity. All Rights Reserved.

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS DESIGNATED AGENTS.

| | DESIGNATED AGENTS. | | | | | |
|----|--------------------------|--|-------------|------------|---|--|
| | MATERIAL: | INTERPRET DIMENSIONS A TOLERANCES PER ASME Y1 | PROJECTION: | | | |
| d. | LCP CuSnP | .X ±.3 ANGLES .XX ±.20 .XXX ±.100 SURFAC | _ | | 9 | |
| | FINISH: WHITE GOLD | DRAWN: JHAGER | DT: 5/27/22 | | | |
| | | ENGR: SHAWNH DT | | T: 5/27/22 | | |



BATTERY HOLDER SURFACE MNT

| ± ⊕)- | CK1032 | | | | | | |
|----------|--------|-------|----------------------|---------|------|--|--|
| Τ' | SIZE | DWG | . NO. | | REV | | |
| 2 | A | BA | Γ-HLD-010-SMT-TR | | Α | | |
| 2 | SCALE | : 2:1 | DO NOT SCALE DRAWING | SHEET 1 | OF 1 | | |