


Features
• ± 0.5 ppm (Frequency Stability) Available
• Clipped Sinewave
• (VC)TCXO
• Tape and Reel
• H-Type Package

Applications
• GPS
• Mobile Communication Equipment
• IoT, Wearable Electronics
• WiMAX, WLAN



Part Numbering Guide

STH 21 K 18 R 48 V G - 26.000M

SUNTSU TCXO H-Type ———

2.0mm x 1.6mm ———

CLIPPED SINEWAVE ———

SUPPLY VOLTAGE

18 : 1.8V $\pm 5\%$
25: 2.5V $\pm 5\%$
28: 2.8V $\pm 5\%$
30: 3.0V $\pm 5\%$
33: 3.3V $\pm 5\%$

FREQUENCY STABILITY

O : ± 2.5 ppm
P : ± 2.0 ppm
Q : ± 1.5 ppm
R : ± 1.0 ppm
F : ± 0.5 ppm

FREQUENCY
MHz

PULLABILITY
BLANK : TCXO
G : ± 5.0 ppm

TCXO/VCTCXO
BLANK : TCXO
V : VCTCXO

OPERATING TEMPERATURE RANGE


07 : 0°C - +70°C
16 : -10°C - +60°C
17 : -10°C - +70°C
27 : -20°C - +70°C
38 : -30°C - +85°C
48 : -40°C - +85°C

Cage Code: 4GUT4
To customize your parameters contact a Suntsu representative.

Electrical Parameters	Units	Minimum	Typical	Maximum	Remarks
Frequency Range	MHz	13		52	
Frequency Tolerance at +25°C	ppm	-2.5		2.5	
Freq. Stability vs. Op Temp.	ppm	-0.5		0.5	See part numbering guide for options.
Freq. Stability vs. Supply Voltage	ppm	-0.2		0.2	V _{DD} $\pm 5\%$ change.
Freq. Stability vs. Load	ppm	-0.2		0.2	$\pm 10\%$ change
Freq. Stability vs. Aging 1 Year	ppm	-1.0		1.0	
Freq. Stability vs. Aging 10 Years	ppm	-5.0		5.0	
Operating Temperature	°C	-30		85	See part numbering guide for options.
Storage Temperature	°C	-40		85	
Supply Voltage (V _{DD})	V	1.8		3.3	See part numbering guide for options.
Current (I _{DD})	mA			2.0	
Control Voltage (VCTCXO)	V	0.4		2.4	
Pullability (VCTCXO)	ppm	± 7.0		± 16.0	See part numbering guide for options.
Linearity (VCTCXO)	%	-10		10	
Output Load (Clipped Sinewave)	k Ω //pF			10//10	
Output Logic Levels	V _{P-P}	0.8			
Symmetry (Duty Cycle)	%	40	50	60	
Start-Up Time	ms			5.0	
VC Input Impedance (VCTCXO)	k Ω	500			
Phase Noise (Typical) 1KHz Offset	dBc/Hz		-130		At 19.2MHz


Outline Drawing & Land Pattern

All dimensions are in millimeters (mm) unless otherwise noted. Drawings are not to scale.




PIN	FUNCTION
1	VC or GND
2	GND
3	OUTPUT
4	VDD

Test Circuit (Clipped Sinewave)




Waveform (Clipped Sinewave)





Tape And Reel Dimensions

All dimensions are in millimeters (mm) unless otherwise noted. Drawings are not to scale.

3,000pcs/Reel



Reflow Profile & Part Marking



Environmental Specifications

Mechanical Specifications

Temperature Cycling	MIL-STD-883, Method 1010, Condition B	Mechanical Shock	MIL-STD-202, Method 213, Condition B
Fine Leak Test	MIL-STD-883, Method 1014, Condition A	Vibration	MIL-STD-883, Method 2007, Condition A
Gross Leak Test	MIL-STD-883, Method 1014, Condition C	Moisture Resistance	MIL-STD-883, Method 1004
Solderability	MIL-STD-883, Method 2003	Resistance to Solvents	MIL-STD-202, Method 215
Moisture Sensitivity	J-STD-020, MSL 1	Resistance to Soldering Heat	MIL-STD-202, Method 210, Condition K