



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
6/28/13	A	RE-DRAWN IN AUTOCAD UPDATED TO ROHS 2 COMPLIANT	T.B.		B.S.
6/02/17	B	DIM. 150.0 WAS 152.4 DIM. 5.0 WAS 3.18 ADDED MORE DIM.	T.B.		B.S.
7/07/17	C	ADDED DIM. 5.20	T.B.		B.S.
7/17/17	D	UPDATED MOUNTING INSTRUCTION	T.B.		B.S.



SPECIFICATIONS

Plastic material - Polypropylene
 Flammability Rating -UL94-HB, UL File NO. E216959
 Temperature Range: -10°C to +100°C
 Springs - Nickel Plated Spring Steel
 Wire: 26AWG, UL1007, CSA, TR64, 300V, 80°C
 Rivets - Brass, Nickel Plated
 CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER EIA-540J000
 ROHS 2 COMPLIANT

Mounting Instruction:
 Use 4-40 machine screws.
 also adhesives and double sided tapes work well.

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735	Scale XX	Drawn By T.S.
			Approved By T.B.
decimal ±.5 (.020)	Title FOUR "C" CELL HOLDER WITH WIRE LEADS		
Fractional ± .8 (.030)		Date 07/17/17	Drawing Number BH14CW
Angular ± 3°			