

ANT-W63RPC1-UFL-100 ✓ ACTIVE

TE Internal #: L9000234-01

PCB Antenna, Triple Band, Wi-Fi, Internal/Embedded Mount, Adhesive, N-type, Omnidirectional, Single Port, Gain > 6 dBi

[View on TE.com >](#)



Antennas



Wireless Application: **Wi-Fi**

Mounting Location: **Internal/Embedded**

Mounting Type: **Adhesive**

Antenna Termination: **N-type**

Antenna Type: **PCB**

Features

Product Type Features

Antenna Product Type	Antenna
Antenna Termination	N-type

Configuration Features

Antenna Style	Patch
Mounting Location	Internal/Embedded
Antenna Type	PCB
Band Type	Triple Band
Port Configuration	Single Port

Electrical Characteristics

VSWR (Max)	<1.8:1
Impedance	50 Ω

Signal Characteristics

Gain (Max)	3.7 dB
Frequency Band	2400 – 2485 MHz
Nominal Frequency Range	2400 – 7125
Peak Gain	> 6 dBi

Body Features

Product Weight	1.6 g [.05643 oz]
----------------	-------------------



Mechanical Attachment

Polarization	Linear
Mounting Type	Adhesive

Dimensions

Cable Length	.1 m[.33 ft]
Product Width	11 mm[.43 in]
Product Length	43 mm[1.69 in]
Product Height	1.3 mm[.05 in]

Operation/Application

Directionality	Omnidirectional
----------------	-----------------

Industry Standards

Wireless Application	Wi-Fi
Primary Application	Wi-Fi

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the

product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CONMHF1-SMD-G-T
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount



TE Part # CONMHF1-SMD-T
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount




TE Part # CONUFL001-SMD
Conn UFL MHF Straight PCB Mount Jack



TE Part # CONUFL001-SMD-T
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount

Customers Also Bought



TE Part #2213627-1
ASSEMBLY, ROT DIM REC 49.22MM 5 POS 150C



TE Part #2822541-1
PUSH-PUSH MICRO SIM CONNECTOR



TE Part #2118720-2
STD SHIELD FRAME, CRS-32.00X32.00X6.00MM



TE Part #2334236-2
QSFP TO [4]SFP+, 28G, 30AWG, 1 METER



TE Part #ANT-916-CW-HWR-RPS
Antenna 1/2 Wave Whip Swivel 916MHz RPS



TE Part #L9000230-01
Antenna WiFi6/6E FPC 20x110 100 UFL




TE Part #L9000203-01
Antenna WIFI6 2.4/5/6 GHz FPC UFL 100



TE Part #L9000231-01
Antenna WIFI6 2.4/5/6 GHz RPC MHF4 100



TE Part #L9000248-01
RP-SMA Jack 50 Ohm .031 PCB Edge Mount



TE Part #RD2458-5-OTDR-NM
Dipol, RDuck, FIXED, NM 2400-5850MHz, 5dBi, O

Documents

Product Drawings

[Antenna WIFI6 2.4/5/6 GHz RPC UFL 100](#)

English



Datasheets & Catalog Pages

Sub-6 Cellular LTE-5G NR Frequency Band Guide

English

Rigid Embedded Dipole WiFi 6 Antenna

English

Virtual Antenna

English

Microslatch Ground Plane Optimization

English