


54mm Width 2500 W AC-DC and HVDC-DC Power Module

DEVELOPMENT OVERVIEW

D1U54T-M-2500-12-HxxC is a series of 2500 W 54.5 mm wide highly efficient AC and HVDC input front end power modules that provide a 12Vdc main output and a standby output. The high power density low-profile packaging achieves >58 W/in3 and provides active current sharing capability, a multifunction status LED, hardware logic signals, PMBus™ digital communications. This power module is ideal for delivering reliable power to servers, workstations, storage systems and other 12 V distributed power architectures.



D100+1 W 2000 12 110+	0					1 0
INPUT CHARACTERISTIC	CS					
Parameter	Conditions		Min.	Nom.	Max.	Units
			90	100-120	132	Vac
Input Voltage Range 1,3			180	200-277	305	Vac
			190	190-400	132 Vac 305 Vac 400 Vdc 63 Hz 84 Vac 192 Vdc 80 Vac 190 Apk Max. Units % %	Vdc
Input AC Source Frequency	/		47	50 / 60	63	Hz
Turn-on Input Voltage	Pomp up		74		84	Vac
Turri-ori iriput voitage	Ramp up		185		192	Vdc
Turn-off Input Voltage	Ramp down		70		80	Vac
Tutti-oit input voitage	namp down		180		190	Vdc
Maximum Input Current	100-120/200-277 Vac, 50 / 60 Ha	7			16	Α
Maximum input current	190-400 Vdc			15	Α	
Inrush Current	Cold start; <200 ms, 264 Vac 25 of x-caps	°C; excludes effects			50	Apk
Power Factor	230 Vac / 60 Hz; 100% load			0.99		%
Parameter	Conditions		Min.	Тур.	Max.	Units
		@ 10% load	90.0	90.5		%
Efficiency	230 Vac/230 Vdc, 25 °C	@ 20% load	94.0	94.1		%
Efficiency	Excluding fan load	@ 50% load	96.0	96.1		
		@ 100% load	91.0	93.3		%

OUTPUT	VOLTAGE CHARACTERIST	rics				
Output	Parameter	Conditions	Min.	Nom.	Max.	Units
	Voltage Set Point	230Vac; 50% load; 25 °C; measured at remote sense	11.94	12.00	12.06	Vdc
	Line and Load Regulation ⁵	Measured at power module side of connector	-1		+1.5	%
12 V	Ripple Voltage & Noise ^{4,5}	20MHz bandwidth			120	mV p-p
	0. 1. 1. 0	180-305 Vac; 190-400 Vdc			208.3	A -1-
	Output Current ¹	90-132 Vac			105	Adc
	Load Capacitance				30,000	μF
	Voltage Set Point	230 Vac; 50% load; Tamb =25 °C, at remote sense	3.28	3.30	3.32	Vdc
	Line and Load Regulation ⁶	Measured at power module side of connector	3.14	3.30	3.46	Vdc
3.3 Vsb	Ripple Voltage & Noise ^{4,6}	20 MHz Bandwidth			75	mV p-p
	Output Current				3	Adc
	Load Capacitance				3,000	μF
	Voltage Set Point	230 Vac; 50% load; Tamb =25 °C, Measured at remote sense	4.98	5.00	5.03	
5 Vsb	Line and Load Regulation ⁶	Measured at power module side of connector	4.76	5.00	5.24	Vdc
OSV C	Ripple Voltage & Noise ^{4,6}	20 MHz Bandwidth			75	mV p-p
	Output Current				3	Adc
	Load Capacitance				3,000	μF
	Voltage Set Point	230 Vac; 50% load; Tamb =25 °C, Measured at remote sense	11.94	12.00	12.06	Vdc
12 Vsb	Line and Load Regulation ⁶	Measured at power module side of connector	11.70	12.00	12.30	Vdc
12 VSD	Ripple Voltage & Noise ^{4,6}	20MHz Bandwidth			120	mV p-p
	Output Current				3	Adc
	Load Capacitance				1,000	μF

- Includes standby output at 100% FL
- Insert power supply into mating connector prior to applying input voltage

 Measured with 0.1 µF of ceramic capacitance and 10 µF of tantalum capacitance on each of the power supply outputs. A short coaxial cable to scope is used.
- Minimum Load of 8.5 A applied to meet these limits. Minimum Load of 0.25 A applied to meet these limits



Typical unit shown for illustration purposes only

FEATURES

- 2500 W continuous main 12 Vdc output power
- 96% minimum efficiency at 50% load, 80 PLUS® certified Titanium
- Anderson Saf-D-Grid Input Connector for full HVDC
- Compact high power density of >58 W/in³
- 3.3 / 5.0 / 12 Vdc Standby Output Options
- 54.5 mm x 321.5 mm x 40.0 mm (<1U height)
- Comprehensive Temperature, Current & Voltage fault
- N+1 redundancy, hot pluggable
- Active ISHARE for main output includes ORing isolation for both outputs
- PMBus™1.2 digital communications
- RoHS Compliant
- Two Year Warranty







For full details visit our website:

www.murata-ps.com/rohs




















54mm Width 2500 W AC-DC and HVDC-DC Power Module

OUTPUT CHARACTERIST	ics				
Parameter	Conditions	Min.	Тур.	Max.	Units
Startup Time	AC ramp up			3	S
	12 V Main 50% load change step (max.), ≥10%; 1 A/µs slew rate; 2,000 µF output capacitance	-5		+5	% nom
Transient Response	Recovery Time to within output regulation limits		2		ms
	Vsb, 50% load change step (max.), ≥10%; 1 A/µs slew rate	-5		+5	% nom
	Recovery Time to within Vsb output regulation limits		2		ms
Current sharing accuracy	Main output; 30% -100% full load	-5		+5	%
Hot Swap Transients	All outputs remain in regulation	-5		+5	%
Holdun Timo	230-240 Vac / 240-400 V HVDC input voltage ranges, 2500 W load, main output dropping to 10.8V	10			ms
Holdup Time	115-240 Vac / 190-400 V HVDC input voltage ranges, 1200 W load, main output dropping to 10.8 V	20			ms

ENVIRONMENTAL CHAP			_		11.11
Parameter	Conditions	Min.	Тур.	Max.	Units
Storage Temperature Range		-40		70	°C
Operating Temperature Range ^{1,2}	Refer to <u>De-rating curves</u> for details	-5		50	C
Operating Humidity	Non-condensing	5		90	%
Storage Humidity	Non-condensing	5		95	70
Altitude 1,2,3	De-rating applies ≥40 °C intake temperature			4000	m
Shock	30G non-operating				
MTBF	Per Telcordia SR-332 M1C3 @40 °C, 230 Vac, 100% full load	540K			Hrs.
Safety Approval Standards (Pending)	IEC 60950-1:2005, IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2 IEC 62368-1:2014 [CSA] CAN/CSA-C22.2 No. 62368-1:14 [CSA] UL 62368-1 2nd Ed. [CSA] EN 62368-1:2014+A11 [TÜV SUD] IS 13252(Part 1):2010/ IEC 60950-1:2005 (BIS) CNS13438 (095/06/01), CNS14336-1 (099/09/30), CNS 15663 5 (102) [BSMI] GB17625.1-2012, GB4943.1-2011, GB/T9254-2008 (Class A) [CQC] K60950-1 (2011-12) [KCC]				
1 15	Dual 200/4200/40/100DC fine provided as a series protective element in both in	nnut "line" and "nout	ral" connectio	n	
Input Fuse	Dual 20A/420VAC/420DC fuse provided as a series protective element in both in	riput iirie ariu rieui	iai comiccio	11	

Meets NEBS abnormal requirements of 55 °C (Sea Level), adjusted to 65°C (@ 1 °C/1,000 ft) to approximate the effects of altitude of 1800M
Based on a power supply operating in a free air environment. Performance within end user's system may be impacted due to the effects of back-pressure imposed by the end use system design. Power module is protected from OTP faults by internal OTP sensors. Refer to PMBus ACAN for additional details. It is incumbent upon the end-user to ensure sufficient access to airflow when designing the system in which these modules will be installed.

Meets China safety spacing requirements





PROTECTION CHARACTERISTICS						
Output Voltage	Parameter	Conditions	Min.	Тур.	Max.	Units
-	Over temperature ²	Auto restart	76	80	84	°C
	Overvoltage	Latching ¹	13.0	14	16.0	V
12V	Overcurrent (180-264 Vac)	Hiccup mode, 5 retries before Latch-off ¹ . Protection is delayed 100 ms to accommodate Peak Power	220		250	
	Overcurrent (90-150 Vac)	Hiccup mode, 5 retries before Latch-off ¹	105		120	Α
12Vsb	Overvoltage	Latching ¹	13.0		16.0	V
12720	Overcurrent	Hiccup	3.1		4.5	Α
5.0Vsb	Overvoltage	Latching ¹	5.4		6.2	V
5.0780	Overcurrent	Hiccup	3.1		5.0	А
3.3Vsb	Overvoltage	Latching ¹	3.6		4.4	V
3.3780	Overcurrent	Hiccup	3.1		5.0	А

EMISSIONS AND IMMUNITY		
Parameter	Conditions	Units
Input Current Harmonics	IEC/EN 61000-3-2	Complies with Class A limits
Voltage Fluctuation and Flicker	IEC/EN 61000-3-3	Complies
Conducted Emissions	FCC 47 CFR Part15/CISPR22/EN55032	Class A with 6 dB margin
ESD Immunity	IEC/EN 61000-4-2	±8KV Contact; ±15KV air discharge; Criteria A
Radiated Field Immunity	IEC/EN 61000-4-3	$3V/m$, 1 KHz, 80% AM, 80 MHz to 1 GHz Criteria A 4
Electrical Fast Transients/Burst Immunity	IEC/EN 61000-4-4	Level 3 (2 kV), criteria A ⁴
Surge Immunity	IEC/EN 61000-4-5	Level 3 (2 kV Line-Earth, 1 kV Line-Line), Criteria A ³
RF Conducted Immunity	IEC/EN 61000-4-6	Level 2 (3 V/m) Criteria A ⁴
		230 Vin, 100% load, Phase 0°, Dip 100% Duration 10 ms (A)
Voltage Dips, Interruptions	IEC/EN 61000-4-11	230 Vin, 50% load, Phase 0°, Dip 100% Duration 20 ms (Vsb:A, V1:B)
		230 Vin, 100% load, Phase 0°, Dip 100% Duration > 20 ms (Vsb, V1:B)

STATUS INDICATOR (SINGLE BICOLOUR LED)	
Condition	LED Status
Standby Mode: Main output = OFF; AC PRESENT	Blinking green 1 Hz
Standby Mode: Main output = ON; No faults detected	Solid green
Fault Detected ⁵ ;Main output, Vsb output, Fan, overtemperature, input OVP	Solid Amber
AC input power absent or no I2C slave address detected (See ADDR signal for configuration details); Vsb OVP	Off
Power Supply Warning Event ⁵	Blinking Amber
Cold Redundant mode – "COLD_STANDBY" / "FORCED STANDBY" MODE	Blinking green 2 Hz

ISOLATION CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Insulation Safety Rating /	Input to Output - Reinforced	5000			Vdc
Test Voltage	Input to Chassis - Basic	2500			Vdc
Isolation	Output to Chassis (functional isolation only)	500			Vdc

^{1.} Latch-off requires recycling either the input power or toggling PS_ON to resume operation

^{2.} As detected by the internal air intake PMBus reporting sensor. Warning indication (PMbus status register bits and Amber LED status) occurs at 95 °C nominal and recovers at 90 °C nominal; fault indication and shutdown engages at 100 °C nominal and recovers at 95 °C nominal. Operating above the maximum specified operating temperature is consider abnormal and prolonged operation under such conditions may negatively impact power supply and is not recommended. Should airflow through the power module be inadequate or restricted, the power module's internal hot-spot sensors may act to self-protect by shutting down the main output regardless of the intake airflow temperature. Refer to PMBus ACAN for additional details such as reading temperature and fault thresholds.

^{3.} Measured at power supply's input connector

Contingent upon final system design

^{5.} LED Indication is concurrent with the PMbus™ Status_XX Register fault/warn bit flags. LED fault/warn state clears upon removal of fault/warn stimulus however associated PMBus™ set fault/warn bit flags and SMBALERT# signal (faults only) can only be cleared by writing "CLEAR_FAULTS" PMBus command or recycling the input power, or toggling PS_ON signal. Refer to PMBus™ ACAN for further details including fault/warn thresholds, supported register bits and masking capability



STATUS AND CONTROL SIGNALS				
Signal Name	1/0	Description	Interface Details	
INPUT_OK Link to: Pin_Table	Output	INPUT_OK signal is driven high when input source is present and within acceptable limits and driven low to indicate loss of input power. This signal deasserts ≥ 5 ms before loss of main output and provides an accurate indication of loss of AC input voltage.	Pulled up via 511R to internal house-keeping supply voltage 2 and pulled down to DC Return via 10 $\rm k\Omega$ resistor	
PW_OK (Output OK) Link to: <u>Pin_Table</u>	Output	The signal is asserted, driven high, by the power supply to indicate 12V main output is valid. Should a 12v main output fault occur, the PW_OK signal will de-assert + driven low. PW_OK output is driven low to indicate that the main output is outside of lower limit of regulation.	Pulled up internally via 10 $k\Omega$ to internal house-keeping supply voltage 2 . A logic high >2.0Vdc A logic low <0.8Vdc Driven low by internal CMOS buffer (open drain output)	
SMBALERT# (FAULT) Link to: <u>Pin_Table</u>	Output	SMBALERT# is driven low to alert the system that the power supply has detected a fault condition as defined in the PMBus ACAN, supported STATUS_XX Register fault bits ¹. This alert asserts when any of the supported STATUS_XX register fault bits are set. This signal is driven high to indicate normal operation. SMBAERT# is de-asserts (fault indication cleared) by either of the following, provided the fault condition is removed: 1) recycling input power 2) Issuing "clear_faults" PMBus command 3) toggling the PS_ON signal The LED fault indication reflects the SMBALERT# status	Pulled up internally via 10 kΩ to house-keeping supply voltage ². A logic high >2.0Vdc A logic low <0.8Vdc Driven low by internal CMOS buffer (open drain output)	
PRESENT_L (Power Supply Absent) Link to: Pin_Table	Output	The signal is used to detect the presence (installed) of a Power module by the host system and is connected to power module's logic SGND within the power module.	Passive connection to +VSB_Return. A logic low <0.8 Vdc	
PS_ON (Main Out Enable/Disable)	Input	This signal ¹⁸ is pulled up, within the power supply, to the internal housekeeping supply. The power supply main 12V output will be enabled when this signal is pulled low (to output return). In the low state the signal input shall not source more than 1mA of current. The 12V main output will be disabled when the input is driven higher than 2.4 V, or open circuited. Cycling this signal shall clear latched fault conditions.	Pulled up internally to internal bias supply ² . A logic high >2.0 Vdc A logic low <0.8 Vdc Input is via CMOS Schmitt trigger buffer	



STATUS AND CONT	TROL SIG	NALS			
Signal Name	1/0	Description			Interface Details
		An external pull-down resistor ≤180 ADDR pin and +12V Main / VSB_R This same resistor also sets the slav	eturn to enable/turn-on the ma	in output.	
ADDD (Address)		External Resistor Value (K-ohm, ≤+/5%) Pin D2	INTERNAL CONTROLLER	EXTERNAL EEPROM	DC valtage between the
ADDR (Address)		0.82	0xB0	0xA0	DC voltage between the
Link to:	Input	2.7	0xB2	0xA2	limits of 0 and +3.3 Vdc
Pin Table		5.6	0xB4	0xA4	System side pull-down
LED Table		8.2	0xB6	0xA6	resistor required, ≤180 kΩ
		15	0xB8	0xA8	
		27	0xBA	0xAA	
		56	0xBC	0xAC	
		180	0xBE	0xAE	
		100	ONDE	ON IL	
SCL (Serial Clock) Link to: <u>Pin_Table</u>	Both	Requirements Rev 1.2. No additional internal capacitance is The signal is provided with a series	A serial clock [®] line compatible with PMbus [™] Power Systems Management Protocol Part 1 – General Requirements Rev 1.2. No additional internal capacitance is added that would affect the speed of the bus. The signal is provided with a series isolator device to disconnect the internal power supply bus in the event that the power module is unpowered.		
SDA (Serial Data) Link to: <u>Pin_Table</u>	Both	Requirements Rev 1.2. The signal is provided with a series	A serial data [©] line compatible with PMbus™ Power Systems Management Protocol Part 1 – General		
V1_SENSE & V1SENSE_RTN Link to: Pin_Table Pin_Table	Input	The voltage sense will interact with due to connection resistance betwe If remote sense compensation is no 1. V1_SENSE directly conn 2. V1_SENSE_RTN directly	= '		
ISHARE Link to: Pin_table 1. PMBus comma	Both	This signal is connected between sl voltage controls the current share b voltage and also can change the buthe voltage on the pin/ISHARE bus with sharing the same 100% load this with the voltage.	his signal is connected between sharing units forming an ISHARE bus. It is a bi-directional analog bus obtage controls the current share between sharing units. The power module responds to change in bus obtage and also can change the bus voltage based on the load drawn from it. For single Power module, we voltage on the pin/ISHARE bus would read approximately 8 Vdc at 100% load. For two identical units haring the same 100% load this would read approximately 4 Vdc for perfect current sharing (i.e. 50% load capability per unit). This signal is also used by cold redundant enabled power supplies to elermine Main output on/off state.		

PMBus command SMBAERT_MASK write transactions are support; the system/host can configure the specific fault bits that effect SMBALERT;

^{2.} Approximately 3.1 Vdc for 3.3 / 12Vsb models or 4.8 Vdc for 5Vsb models, internal reference "STBY_PULL"




54mm Width 2500 W AC-DC and HVDC-DC Power Module

TIMING SPECIFICATIONS

Unless otherwise specified, the following notes apply to all timing specifications:


- 1. Ta= 25 °C, Vin & Vin nom. = 200-240 Vac
- 2. Resistive load, 100% full load, both outputs

Turn-On Delay & Output Rise Time



Time	Min	Max
Vsb Rise time; see Fig. 1	3 ms	9 ms
V1 Rise time; see Fig. 2	7 ms	15 ms
Vsb Power-on-delay; see Fig. 3		2700 ms
V1 Power-on-delay; see Fig. 4		3000 ms
V1 PS_ON delay; see Fig. 5	100 ms	400 ms
V1 PW_OK delay; see Fig. 6	100 ms	400 ms
Input_OK detect; see Fig. 7	100 ms	1500 ms

Shutdown by PS_ON. Fall Time and Signaling



V1 PS_OFF delay	0 ms	5 ms	
PW_OK delay off	1 ms		


Min

Max

Notes

Turn-Off Timing







54mm Width 2500 W AC-DC and HVDC-DC Power Module

TYPICAL PERFORMANCE DATA

TIMING CHARACTERISTICS

The following terms may be used interchangeably throughout this section: "Enable" = "PS_ON" signal; "V1" = 12V Main output; "V2" = Vsb output; "PGOOD" = PW_OK



Fig. 1
Vsb output risetime; 25C 230Vac in, 100% load



12V main output rise-time; 25C 230Vac in, 100% load




Fig. 3
Vsb power on delay; 25C 230Vac in, 100% load



12V main power on delay; 25C 230Vac in, 100% load









54mm Width 2500 W AC-DC and HVDC-DC Power Module

TYPICAL PERFORMANCE DATA

TIMING CHARACTERISTICS



Vin Detect, 90vrms (60hz) input, 25C 230Vac in, Min. load



Vsb hold-up; 25C 230Vac in, 100% load



V1 holdup; 25C 230Vac in, 100% load



Input Fail detect; 25C; 90Vac input; Min. Load





PW_OK delay off; 25C 230Vac in, 100% load

54mm Width 2500 W AC-DC and HVDC-DC Power Module

TYPICAL PERFORMANCE DATA


Efficiency Performance





POWER DE-RATING VS TEMPERATURE & INPUT VOLTAGE

The following tables illustrate the maximum Main 12V output power and current vs air intake temperature and nominal input voltage. The standby output may be loaded up to 100% FL without further impact to De-rating.






Fig. 14

Main Output Power De-rating table Front to Back airflow models (Hx3C)




Fig. 15 Main Output Current De-rating table Front to Back airflow models (Hx3C)

All B-F Airflow Models (Hx4C)





Fig. 16 Main Output Power De-rating table Back to Front airflow models (Hx4C)

Fig. 17 Main Output Current De-rating table Front to Back airflow models (Hx4C)

Link back to front page

54mm Width 2500 W AC-DC and HVDC-DC Power Module

DC OUTPUT & SIGNAL INTERFACE CONNECTOR System Side: FCI/Amphenol 10106264-6003003LF 2X 6.60 2X 10.41 - 2X 3 05 REE CODE DESCRIPTION SID SIGNAL CONTACT, ROW A HP PRODUCT NO. ROW S SID SINAL CONTACT, ROW B G SID SIGNAL CONTACT, ROW C 10106264-6003003LF H3|H3|H1|H1|H1 Н SID SIGNAL CONTRACT, ROW D H1 MFBL HIGH POWER CONACT (3.43) НЗ SID HISH POWER CONNIACT(3.43) HA METAL HOLD DOWN






54mm Width 2500 W AC-DC and HVDC-DC Power Module

(CONTINUED)					
DC OUTPUT & SIGNAL INTERFACE CONNECTOR					
PIN ASSIGNMENTS					
Pin	Signal Name	Comments			
P4, P5, P6	V1	+ 12V main output			
P1, P2, P3	V1 & V2 RETURN	+12V Main/VSB output_Return			
A3	SDA	Short Pin1 I2C data signal line; shorter MLFB pin; Link to signal details			
B3	SCL	Short Pin1 I2C clock signal line; shorter MLFB pin; Link to signal details			
C3	PS_ON	Short Pin1 Remote on/off Short; shorter MLFB pin			
D3	SMBALERT#	Short Pin1 2C alert signal; shorter MLFB pin; Link to signal details			
A2	V1_SENSE_R	- Remote Sense/ return; Link to signal details			
B2	V1_SENSE	+ Remote Sense; Link to signal details			
C2	PW_OK	Power OK; Link to signal details			
D2	ADDR	Address Selection (select by external pull down resistor); Link to signal details			
A1	PRESENT_L	PS Present; Link to signal details			
B1	Vsb	Standby output			
C1	INPUT_OK	Indicates input power status; Link to signal details			
D1	ISHARE	Current share bus; Link to signal details			

WIRING DIAGRAM


1 + 1 WIRING EXAMPLE




CURRENT SHARING NOTES

- 1. Main Output current sharing is achieved using the active current share method.
- 2. Current sharing can be achieved with or without the remote (V_SENSE) connected to the
- 3. +Vsb Outputs can be tied together for redundancy but total combined output power must not exceed the rated standby power of a single unit. The +Vsb output has an internal ORing MOSFET for additional redundancy/internal short protection.
- 4. Main output power of units sharing must not exceed the rated power of a single unit during power up.
- 5. The current sharing pin D1 is connected between sharing units (forming an ISHARE bus). It is an input and/or an output (bi-directional analog bus) as the voltage on the line controls the current share between sharing units. A power supply will respond to a change in this voltage but a power supply can also change the voltage depending on the load drawn from it. On a single unit the voltage on the pin (and the common ISHARE bus would read approximately 8VDC at 100% load (power module capability). For two units sharing the same load this would read approximately 4 Vdc for perfect current sharing (i.e. 50% power capability per unit).
- 6. The load for both the main 12V and the Vsb outputs at initial startup shall not be allowed to exceed the capability of a single unit. The load can be increased after a delay of 3 sec (minimum), to allow all sharing units to achieve steady state regulation
- ① Dotted lines show optional remote sense connections. Optional remote sense lines can be attached to a load that is a distance away from the power supply to improve regulation at the load.
 ② FET, BJT, wire or switch (debounced) to turn on +12V Main Output
 ③ s180K External resistor must be fitted between the ADDR pin and +12V/VSB return in order to enable power supply. This resistor value also sets the PMBus Slave Addressing. Refer to the signal table for address options







- This drawing is a graphical representation of the product and may not show all fine details. Please contact Murata for 3D model for details
- Reference File: D75090020161_R1_14APR2020
- Dimensions in mm, Material: 0.80mm hot dipped galvanized steel, Grade G60 minimum spangle finished with a CR(6+) free corrosion resistant coating



54mm Width 2500 W AC-DC and HVDC-DC Power Module

Description	Part Number	
Connector Card	D1U54P-12-CONC2K	
AC Line Cord [©] , Adapts Saf-D-Grid [®] 400V to IEC 320 C14 or C20	Anderson Power Products (Saf-D-Grid® To IEC 320 cable configurations): 2050KN1-BK: C14, 1M Length, 14 AWG SJT 2050KN2-BK: C14, 2M Length, 14 AWG SJT 2050KN3-BK: C14, 3M Length, 14 AWG SJT 2050KH1-BK: C20, 1M Length, 14 AWG SJT 2050KH2-BK: C20, 2M Length, 14 AWG SJT 2050KH3-BK: C20 3M Length, 14 AWG SJT 2058KN1-BK: C20, 1M Length, 12 AWG SJT 2058KN2-BK: C20, 2M Length, 12 AWG SJT 2058KN3-BK: C20, 3M Length, 12 AWG SJT Contact your Anderson Power Products distributor for additional options, pricing and availability.	

① It is incumbent upon the end user to ensure operation with an input cable system that complies with the electrical code and safety requirements of the country, or region of deployment.

APPLICATION NOTES				
Document Number	Description	URL Link to Document		
ACAN-82	D1U54P-12-CONC2K , Output Connector Card	Click to open ACAN-82		
ACAN-122	D1U54T-M-2500-12-HxxC PMBus™ Protocol	Click to open ACAN-122		

Murata Power Solutions, Inc. 129 Flanders Rd. Westborough, Ma 01581, USA. ISO 9001 REGISTERED



This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy. Refer to: https://www.murata-ps.com/requirements/

Murata Power Solutions, Inc. ("Murata") makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of salures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify Murata, its affiliated companies, and its representatives against any damages arising out of the use of any Murata products in safety-critical applications. Specifications are subject to change without notice.

© 2023 Murata Power Solutions, Inc