

CLM2D-CPC: PLCC4 Cyan SMD LEDs



PRODUCT DESCRIPTION

SMD LEDs is packaged in the industry standard package. These LEDs have high reliability performance and are designed to work under a wide range of environmental conditions. This high reliability feature makes them ideally suited to be used in architectural lighting application conditions

Cree LED has been certified in accordance with ISO/IATF16949.

FEATURES

- Size (mm): 3.2 x 2.8
- Color and Typical Dominant
 Wavelength:
 Gyan (500-512.5nm)
- Viewing angles: CLM2D-CPC
 30 degree minimum
- · Moisture Sensitivity Level: 5a
- · Lead Free
- · RoHS Compliant
- · Untinted Diffused Lens

APPLICATIONS

- Channel Letter
- Architectural Lighting



ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C)

Items	Symbol	Absolute Maximum Rating	Unit		
Forward Current	l _F	35	mA		
Peak Forward Current Note1	I _{FP}	100	mA		
Reverse Voltage	$V_{_{\mathrm{R}}}$	5	V		
Power Dissipation	$P_{\scriptscriptstyle D}$	140	mW		
Operation Temperature	T_{opr}	-40 ~ +100	°C		
Storage Temperature	T_{stg}	-40 ~ +100	°C		
Junction Temperature	$T_{_{\!J}}$	110	°C		
Junction/Ambient	R _{THJA}	400	°C/W		
Junction/Solder Point	R_{THJS}	180	°C/W		
Electrostatic Discharge Classification(MIL-STD-883E)	ESD	1000V			

Note:

1. Pulse width ≤ 0.1 msec, duty $\leq 1/10$.

TYPICAL ELECTRICAL & OPTICAL CHARACTERISTICS ($T_A = 25$ °C)

Characteristics	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	V _F	I _F = 20 mA	V		3.2	4.0
Reverse Current	I _R	V _R = 5 V	μΑ			10
Dominant Wavelength	$\lambda_{_{\mathrm{D}}}$	I _F = 20 mA	nm	500	506	512.5
Luminous Intensity	I _v	I _F = 20 mA	mcd	3550	4800	
50% Power Angle	201/2	I _F = 20 mA	deg	30		

^{*} Continuous reverse voltage can cause LED damage.



INTENSITY BIN LIMIT

Gyan (20 mA)					
Bin Code	Min.(mcd)	Max.(mcd)			
Yb	3550	4500			
Z0	4500	5600			
A0	5600	7100			

^{*} Tolerance of measurement of luminous intensity is ±10%

COLOR BIN LIMIT

Gyan (20 mA)					
Bin Code	Bin Code Min.(nm)				
G3	500	505			
G01	502.5	507.5			
G4	505	510			
G12	507.5	512.5			

^{*} Tolerance of measurement of dominant wavelength is ±1 nm.



ORDER CODE TABLE

Color	Kit Number	Luminous Intensity (mcd)		Dominant Wavelength				- Package
		Min.	Max.	Color Bin	Min.(nm)	Color Bin	Max.(nm)	rackage
Gyan	CLM2D-CPC-CYbA03123	3550	7100	G3	500	G12	512.5	Reel
	CLM2D-CPC-CYbA0343	3550	7100	G3	500	G4	510	Reel

Notes:

- The above kit numbers represent order codes that include multiple intensity-bin and color-bin codes. Only one intensity-bin code and one color-bin code will be shipped on each bulk. Single intensity-bin code and single color-bin codes will not be orderable.
- · Please refer to the HB LED Lamp Reliability Test Standards document for reliability test conditions.
- Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.



GRAPHS

The data below are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.

5.04.0

3.0

2.0

300 400




FIG.1 FORWARD CURRENT VS. FORWARD VOLTAGE.





FIG.3 MAXIMUM FORWARD DC CURRENT VS SOLDER TEMPERATURE (Tjmax=110°C)



(RELATIVE LUMINOUS INTENSITY)

FIG.4 RELATIVE LUMINOUS INTENSITY VS. WAVELENGTH.

600

500

WL(nm)

800






FIG.5 MAXIMUM FORWARD DC CURRENT VS AMBIENT TEMPERATURE (Tjmax=110°C)





MECHANICAL DIMENSIONS

All dimensions are in mm.



NOTES

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree LED representative or from the Product Ecology section of the Cree LED website.

Vision Advisory


WARNING: Do not look at an exposed lamp in operation. Eye injury can result.



KIT NUMBER SYSTEM

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options.


Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:






REFLOW SOLDERING


- The CLM2D-CPC is rated as a MSL 5a product.
- · The recommended floor life out of bag is 24hrs.
- · The temperature profile is as below.



Use only with CLM2D-CPC



- The packaging sizes of these SMD products are very small and the resin is still soft after solidification. Users are required to handle with care. Never touch the resin surface of SMD products.
- To avoid damaging the product's surface and interior device, it is recommended to choose a special nozzle to pick up the SMD
 products during the process of SMT production. If handling is necessary, take special care when picking up these products. The
 following method is necessary:
- Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.





PACKAGING

- The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- · Cardboard boxes will be used to protect the LEDs from mechanical shock during transportation.
- The boxes are not water resistant, and they must be kept away from water and moisture.
- · The reel pack is applied in SMD LED.
- Max 2300 pcs per reel.

