


NOTES: UNLESS OTHERWISE SPECIFIED

/1\SEE SHEET 2 FOR KEY ARRANGEMENTS AND COLORS.

2. MATERIAL:

HOUSING: THERMOPLASTIC SEAL: SILICONE RUBBER


- 3. MODIFICATIONS: N/A
- 4. SPECIFICATIONS:
 - 4.1 CURRENT RATING: 13 AMPS
 - 4.2 OPERATING TEMPERATURE: -55°C TO +125°C
 - 4.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 4.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
 - 4.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION)
 - 4.6 MATING CYCLE DURABILITY: 100 CYCLES
 - 4.7 RoHS COMPLIANT
- 5. MATING PART: AT06-08SX* PLUG (X = A,B,C,D KEYS; * = MODIFICATIONS AND COLORS)
- 6. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.




_ / `	\						
/7	٠/	CONTACT	SIZE AND	RFAR	SEAL	WIRE	RANGE:
/ '	١.	CONTINCT	0126 / 1140	1111		V V I I V L	10 11 VC L.

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL
SIZE	O.D.	O.D.	WIRE RANGE
16	2.24 mm (.088 in)	3.68 mm (.145 in)	14 - 20 AWG

		REVISIONS			
REV	ECO	DESCRIPTION	DATE	BY	APPR
A3	-	RELEASE NEW DRAWING FORMAT	27DEC13	JARRY	-





RECEPTACLE, 8 PIN, AT SERIES, KEYED


AT04-08PX-XXX

-: A3 SH:

	SEE S	SHEET 2					
QUANTITY	PART N	PART NUMBER			DE	SCRIPTION	ITEM
	MATERI			ALS	LI	ST	
UNLESS OTHER		SIGNATURE	S DATE		Λ	mphonol	
	All dimensions are in metric(mm). Tolerances are as follows:		27DEC13		$\overline{}$	mphenol	
1 PL DEC ±0.30 Fractions ±1/64 2 PL DEC ±0.15 Angles ±1° 3 PL DEC ±0.08		CHECKED:		Sine Systems - www.amphenol-sine.com			
3) Note reference	3) Note reference = X			44724 Morley Drive			
MATERIAL SPECIFICA	TIONS:	APPROVAL:				Clinton Township, MI 48036	
		CUSTOMER:	!		RE	CEPTACLE, 8 PIN, AT SERIES,	
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLI				KEYED	
		SPECIFICATION SAID PEI SPECIFICATIONS AND PEI SHOWN HEREON ARE THI THE AMPHENOL CORPOR OF REPRODUCTION ARE DIMENSIONS ARE SUBJEC	RFORMANCE DATA E PROPERTY OF ATION. NO RIGHTS IMPLIED. ALL	B (J-	AT04-08PX-XXX	A3
NEXT ASS'Y:	NEXT ASS'Y:		IONS.	SCALE: NO	NE	SHEET 1 OF	2


		REVISIONS			
REV	ECO	DESCRIPTION	DATE	BY	APPR
A3	-	RELEASE NEW DRAWING FORMAT	27DEC13	JARRY	-

P/N AT04-08P KEY-A CONFIGURATION STANDARD COLOR: GREY




KEY-A CONFIGURATION				
COLOR	PART NUMBER			
* GREY	AT04-08PA			
BLACK	AT04-08PA-BLK			
GREEN	AT04-08PA-GRN			
BROWN	AT04-08PA-BRN			

P/N AT04-08PB KEY-B CONFIGURATION STANDARD COLOR: BLACK




KEY-B CONFIGURATION				
COLOR PART NUMBER				
GREY	AT04-08PB-GRY			
*BLACK	AT04-08PB			
GREEN	AT04-08PB-GRN			
BROWN	AT04-08PB-BRN			

P/N AT04-08PC KEY-C CONFIGURATION STANDARD COLOR: GREEN



KEY-C CONFIGURATION					
COLOR PART NUMBER					
GREY	AT04-08PC-GRY				
BLACK	AT04-08PC-BLK				
* GREEN	AT04-08PC				
BROWN AT04-08PC-BRN					

P/N AT04-08PD KEY-D CONFIGURATION STANDARD COLOR: BROWN



GREEN AT04-08P					
	D-BLK				
BLACK AT04-08P					
GREY AT04-08P	D-GRY				
COLOR PART NUMBER					
KEY-D CONFIGURA	KEY-D CONFIGURATION				

NOTE:

AN ASTERISKS (*) PLACED BEFORE THE COLOR DENOTES THE STANDARD MOLDED COLOR OF THE CONNECTORS SHOWN ABOVE.

OTHER COLORS SHOWN ARE AVAILABLE VIA SPECIAL ORDER.

QUANTITY	PART N	IUMBER			DESCRIPTION		ITEM
		MA	TER	IALS	i LI	ST	
	WISE SPECIFIED	SIGNATUR	ES DAT	≡	Λ	mahanal	
All dimensions are in metric(mm). Tolerances are as follows: PL DEC ±0.30 Fractions +1/64		DRAWN: JARRY	27DEC	3		mphenol	
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:		Sine Systems - www.amphenol-sine.com			
3) Note reference	= X	ENGINEER:	44724 Morley Drive				
MATERIAL SPECIFICA	APPROVAL:				Clinton Township, MI 48036		
		CUSTOMER:			RE	CEPTACLE, 8 PIN, AT SEIRES	
			IED FOR SIGN FEATURES			KEYED	
PROCESS SPECIFICATIONS: SPECIFICATIONS AN SHOWN HEREON AR THE AMPHENOL COI OF REPRODUCTION DIMENSIONS ARE SI		SPECIFICATIONS AND PE SHOWN HEREON ARE TH THE AMPHENOL CORPOI OF REPRODUCTION ARE DIMENSIONS ARE SUBJE	RFORMANCE D. IE PROPERTY O RATION. NO RIGI IMPLIED. ALL	TS B	C-	AT04-08PX-XXX	A3
		MANUFACTURING VARIA		SCALE: NO	ONE	SHEET 2 OF	2

AT04-08PX-XXX REV: A3 SH:

RECEPTACLE, 8 PIN, AT SERIES, KEYED

2

A Series™ - Contact Size 16 Options (Works with: AT, ATV, AHD-9, ARC, DuraMate and PanelMate Series)

	Machined Contacts, Sockets & Pins			
Part Number	Description	Size	AWG	Туре
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined

Tooling - Machined Contacts					
Part Number	Description				
AUTK-16	Hand Crimp Tool, Size 16				
AUTK-100	Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20				
CA-5D12	Universal Hand Crimp Tool, Size 12/16/20				
CA-5E12	Pneumatic Crimp Tool, Size 12/16/20				

Contact Removal Tools (For both Machined or Stamped & Formed Contacts)				
Part Number	Description			
ATRT-100	Contact and Wedgelock Extraction Tool			
AT11-310-1605	Contact Removal Tool, Plastic, Size 16			

Sealing Plugs (For both Machined or Stamped & Formed Contacts)				
Part Number	Description			
A114017	Sealing Plug, Size 16, White			
A114017-SR	Sealing Plug, Size 16, SR01 Series, Black			
AT13-217-1605	Locking Sealing Plug, Size 16, Grey			
AT13-217-1605-SR	Locking Sealing Plug, Size 16, SR01 Series, Red			

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-18	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-18	Stamped & Formed		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-18	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	16-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	16-20	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	16-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	16-20	Stamped & Formed		
AT60-16-0677	Male Contact - Pin, Tin-plated	16	16-20	Stamped & Formed		
AT62-16-0677	Female Contact - Socket, Tin-plated	16	16-20	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		

Tooling - Stamped & Formed Contacts		
MFX-3950	Crimp Die - Size 16, 18-20AWG	
MFX-3953	Crimp Die - Size 16, 16-18AWG	
MFX-3975	Crimp Die - Size 16, 14-16AWG	
MFX-3990	Crimp Die - Size 16, 20-22AWG	
ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG	
ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG	
ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG	