

SERIES: PQM1-M | **DESCRIPTION:** DC-DC CONVERTER

FEATURES


- 1 W isolated output
- smaller package
- single regulated output
- 1,500 Vdc isolation
- continuous short circuit protection
- extended temperature range (-40~85°C)
- high efficiency at light load
- efficiency up to 75%
- designed to meet EN/BS EN 62368-1



| MODEL | input voltage | | output voltage (Vdc) | output current | | output power max (W) | ripple and noise ¹ typ (mVp-p) | efficiency typ (%) |
|-----------------|---------------|-------------|-------------------------|----------------|----------|-------------------------|--|-----------------------|
| | typ (Vdc) | range (Vdc) | | min (mA) | max (mA) | | | |
| PQM1-S5-S3-M* | 5 | 4.75~5.25 | 3.3 | 25 | 243 | 0.8 | 50 | 58 |
| PQM1-S5-S5-M* | 5 | 4.75~5.25 | 5 | 20 | 200 | 1 | 50 | 72 |
| PQM1-S5-S9-M* | 5 | 4.75~5.25 | 9 | 12 | 111 | 1 | 50 | 74 |
| PQM1-S5-S12-M* | 5 | 4.75~5.25 | 12 | 9 | 84 | 1 | 50 | 73 |
| PQM1-S5-S15-M* | 5 | 4.75~5.25 | 15 | 7 | 67 | 1 | 50 | 74 |
| PQM1-S12-S5-M* | 12 | 11.4~12.6 | 5 | 20 | 200 | 1 | 50 | 73 |
| PQM1-S12-S9-M | 12 | 11.4~12.6 | 9 | 12 | 111 | 1 | 50 | 74 |
| PQM1-S12-S12-M* | 12 | 11.4~12.6 | 12 | 9 | 84 | 1 | 50 | 73 |
| PQM1-S12-S15-M* | 12 | 11.4~12.6 | 15 | 7 | 67 | 1 | 50 | 75 |
| PQM1-S24-S5-M* | 24 | 22.8~25.2 | 5 | 20 | 200 | 1 | 50 | 65 |
| PQM1-S24-S9-M | 24 | 22.8~25.2 | 9 | 12 | 111 | 1 | 50 | 74 |
| PQM1-S24-S12-M* | 24 | 22.8~25.2 | 12 | 9 | 84 | 1 | 50 | 73 |
| PQM1-S24-S15-M* | 24 | 22.8~25.2 | 15 | 7 | 67 | 1 | 50 | 74 |

Note: 1. Ripple and noise are measured at 20 MHz BW by "parallel cable" method with 1 µF ceramic and 10 µF electrolytic capacitors on the output.
2. * Discontinued model.

PART NUMBER KEY



INPUT

| parameter | conditions/description | min | typ | max | units |
|-------------------------|-------------------------|------|-----|------|-------|
| operating input voltage | 5 Vdc input models | 4.75 | 5 | 5.25 | Vdc |
| | 12 Vdc input models | 11.4 | 12 | 12.6 | Vdc |
| | 24 Vdc input models | 22.8 | 24 | 25.2 | Vdc |
| surge voltage | for maximum of 1 second | | | | |
| | 5 Vdc input models | -0.7 | | 9 | Vdc |
| | 12 Vdc input models | -0.7 | | 18 | Vdc |
| | 24 Vdc input models | -0.7 | | 30 | Vdc |
| filter | capacitance filter | | | | |

OUTPUT

| parameter | conditions/description | min | typ | max | units |
|-------------------------|-------------------------------------|-----|-----|-------|-------|
| line regulation | for Vin change of 1% | | | ±0.25 | % |
| load regulation | measured from 10% load to full load | | | | |
| | 3.3 Vdc output models | | 3 | | % |
| | all other models | | 1 | | % |
| voltage accuracy | at 100% load | | | ±3 | % |
| switching frequency | at 100% load, nominal input voltage | | 100 | 300 | kHz |
| temperature coefficient | at 100% load | | | ±0.03 | %/°C |

PROTECTIONS

| parameter | conditions/description | min | typ | max | units |
|--------------------------|--------------------------------|-----|-----|-----|-------|
| short circuit protection | continuous, automatic recovery | | | | |

SAFETY AND COMPLIANCE


| parameter | conditions/description | min | typ | max | units |
|----------------------|---|-----------|-----|-----|-------|
| isolation voltage | input to output for 1 minute at 1 mA max. | 1,500 | | | Vdc |
| isolation resistance | input to output at 500 Vdc | 1,000 | | | MΩ |
| safety approvals | designed to meet 62368-1: EN, BS EN | | | | |
| conducted emissions | CISPR22/EN55022 class B (external circuit required, see Figure 1) | | | | |
| radiated emissions | CISPR22/EN55022 class B (external circuit required, see Figure 1) | | | | |
| ESD | IEC/EN61000-4-2, class B, contact ± 8kV | | | | |
| MTBF | as per MIL-HDBK-217F @ 25°C | 3,500,000 | | | hours |
| RoHS | 2011/65/EU | | | | |

ENVIRONMENTAL

| parameter | conditions/description | min | typ | max | units |
|-----------------------|-------------------------|-----|-----|-----|-------|
| operating temperature | see derating curve | -40 | | 85 | °C |
| storage temperature | | -55 | | 125 | °C |
| storage humidity | non-condensing | | | 95 | % |
| temperature rise | at full load, Ta = 25°C | | 25 | | °C |

SOLDERABILITY

| parameter | conditions/description | min | typ | max | units |
|------------------|---------------------------------|-----|-----|-----|-------|
| hand soldering | 1.5 mm from case for 10 seconds | | | 300 | °C |
| reflow soldering | see reflow soldering profile | | | 245 | °C |



MECHANICAL


| parameter | conditions/description | min | typ | max | units |
|---------------|---|-----|-----|-----|-------|
| dimensions | 15.24 x 11.20 x 7.25 (0.600 x 0.441 x 0.285 inch) | | | | mm |
| case material | epoxy resin (UL94-V0) | | | | |
| weight | | | 2.0 | | g |

MECHANICAL DRAWING

units: mm[inch]
 tolerance: $\pm 0.25[\pm 0.010]$
 pin section tolerance: $\pm 0.10[\pm 0.004]$


| PIN CONNECTIONS | |
|-----------------|----------|
| PIN | FUNCTION |
| 1 | GND |
| 2 | Vin |
| 4/5 | 0V |
| 7 | +Vo |
| 10 | NC |

NC: No Connection



DERATING CURVE

TEMPERATURE DERATING CURVE



EMC RECOMMENDED CIRCUIT

Figure 1




Table 1

| Recommended external circuit components | | | |
|---|-----------|-------|-------|
| Vout (Vdc) | C1 | C2 | LDM |
| 3.3 | 4.7μF/50V | 10μF | 6.8μH |
| 5 | 4.7μF/50V | 10μF | 6.8μH |
| 9 | 4.7μF/50V | 4.7μF | 6.8μH |
| 12 | 4.7μF/50V | 2.2μF | 6.8μH |
| 15 | 4.7μF/50V | 1μF | 6.8μH |

APPLICATION NOTES

1. Output load requirement

To ensure this module can operate efficiently and reliably, the minimum output load may not be less than 10% of the full load during operation. If the actual output power is low, connect a resistor at the output end in parallel to increase the load.

2. Overload Protection

Under normal operating conditions, the output circuit of this product has no protection against overload. The simplest method to add this is to add a circuit breaker to the circuit.

3. Recommended circuit

If you want to further decrease the input/output ripple, you can increase the capacitance accordingly or choose capacitors with low ESR (see Figure 2 & Table 2). However, the capacitance of the output filter capacitor must be appropriate. If the capacitance is too high, a startup problem might arise. For every channel of the output, to ensure safe and reliable operation, the maximum capacitance must be less than the maximum capacitive load (see Table 3).




Table 2

| Vin (Vdc) | Cin (μF) | Vo (Vdc) | Cout (μF) |
|-----------|----------|----------|-----------|
| 5 | 4.7 | 3.3 | 10 |
| 12 | 2.2 | 5 | 10 |
| 24 | 1 | 9 | 4.7 |
| -- | -- | 12 | 2.2 |
| -- | -- | 15 | 1 |

Table 3

| Vout (Vdc) | Max. Capacitive Load (μF) |
|------------|---------------------------|
| 3.3 | 220 |
| 5 | 220 |
| 9 | 220 |
| 12 | 220 |
| 15 | 220 |

Note: It's not recommended to connect any external capacitors in applications with less than 0.5 watt output.

Note: 1. Operation under minimum load will not damage the converter; however, they may not meet all specifications listed.
 2. Max. capacitive load tested at input voltage range and full load.
 3. All specifications measured at: Ta=25°C, humidity<75%, nominal input voltage and rated output load, unless otherwise specified.

REVISION HISTORY

| rev. | description | date |
|------|---|------------|
| 1.0 | initial release | 04/08/2014 |
| 1.01 | safeties updated in features and safety approvals line | 01/19/2021 |
| 1.02 | product image updated | 05/19/2021 |
| 1.03 | updated derating curve and circuit figures | 06/09/2021 |
| 1.04 | discontinued model PQM1-S5-S15-M | 09/08/2021 |
| 1.05 | efficiency updated for PQM1-S24-S5-M | 08/03/2022 |
| 1.06 | discontinued models PQM1-S5-S12-M, PQM1-S5-S3-M & PQM1-S5-S5-M | 11/11/2022 |
| 1.07 | CE removed | 11/16/2022 |
| 1.08 | discontinued model PQM1-S12-S5-M | 02/02/2023 |
| 1.09 | discontinued model PQM1-S5-S5-M-TR | 07/11/2023 |
| 1.10 | discontinued model PQM1-S24-S12-M, PQM1-S24-S12-M-TR, PQM1-S24-S15-M, PQM1-S24-S15-M-TR, PQM1-S24-S5-M & PQM1-S24-S5-M-TR | 09/26/2023 |
| 1.11 | discontinued model PQM1-S12-S12-M, PQM1-S12-S12-M-TR, PQM1-S12-S15-M, PQM1-S12-S15-M-TR, PQM1-S5-S9-M & PQM1-S5-S9-M-TR | 01/12/2024 |

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC

a bel group

Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.