
Quarton inc.

Green Cross-Line Laser

VLM-520-29 Series



FEATURES:

- Direct Green Laser Diode for large temperature operation range.
- Line-width optimize at short distance(40cm) for consumer grade Laser Cross-Line generator applications.
- This module has integrated wavy lens, collimating lens, laser diode, and APC driver circuit.
- APC driver circuit enables the laser power output safe and constant.
- Includes patented solid brass structure for the best shock resistance and better heat transfer consideration.
- Aspherical Plastic Lens and Plastic Wavy Lens provides tight Cross-Line Laser.
- Dimensions : Ø9 x 26 mm (Ø0.354" x 1.024")
- Wavelength: 505~530 nm
- Laser power output: LPT Class 1M less than 0.39mW

LPA - Class 2M - less than 1mW

- Emitting Angle : >60°7~10 VDC operation.
- Connection type : Lead wire


APPLICATIONS:

- Green Cross-Line Laser Module, Line-width optimize at short distance(40cm) for consumer grade barcode reader, leveling, alignment, adjusting, positioning, measuring, targeting and sighting device.
- Wood processing.
- Metal processing.
- Stone processing.
- Textile industry.
- Food industry.
- Automotive industry.
- Medical science.

Quarton inc.

VLM-520-29 Series

OUTLINE DIMENSIONS (UNITS: mm)



SPECIFICATIONS

SPECIFICATIONS		VLM-520-29		
		LPT	LPA	
1	Dimensions	Ø9 x 26 mm (Ø0.354" x 1.024")		
2	Operating voltage (Vop)	7~10 VDC		
3	Operating current (lop)	Less than 80mA	Less than 100mA	
4	Optical power*	4~5mW	9~10mW	
5	Laser power output**	Less than 0.39mW	Less than 1mW	
6	Laser class	Class 1M	Class 2M	
7	Wavelength at peak emission (λp)	505~530nm		
8	Collimating lens	Plastic Lens		
9	Crosshairs lens	Plastic Lens		
10	Beam shape	Crosshairs		
11	Laser Line width	1mm@40cm		
12	Laser line accuracy	80" (+/- 2mm @5M)		
13	Emitting angle	More than 60°		
14	Operating temp. range***	+15°C ~+30°C		
15	Storage temp. range	-20°C ~+65°C		
16	Housing material	Brass		
17	Potential of housing****	VDD(+)		
18	Electrostatic discharge (ESD)	30KV		

Quarton inc.

VLM-520-29 Series

19	Moisture sensitivity level (MSL)	Level 1 - acc to JEDEC J-STD-020E.		
20	Wire type	1007-26AWG		
21	Cable length	115±15mm		
22	Mean time to failure (MTTF) 25°C	5000hrs		
23	Application	Economic application		
24	Suggestion work distance	0~1 meter / 0~3 feet		

^{*} Optical power is total power output measured at the aperture of the laser.

- *** Operation temperature means within this temperature range, the laser spot/line will not be affected to change the spot size/line width. It can still work over this range, but the laser spot size or laser line width will be larger.
- **** Laser module housing is an electrical positive surface, it is imperative that contact between the laser module and the machine be avoided. This is to prevent damage from the machine electrical leakage. Surge protected power supply to the laser module is strongly recommended.

ORDER CODE

Order Code	Wavelength	Optical power*	Laser power	Laser Class	Connection
			output**		Туре
VLM-520-29 LPT	520 nm	4~5mW	Less than	Class 1M	Lead Wire
			0.39mW		
VLM-520-29 LPA	520 nm	9~10mW	Less than	Class 2M	Lead Wire
			0.9mW		

^{*} Optical power is total power output measured at the aperture of the laser.

SAFETY LABEL





^{**} According to FDA 1040.10 & IEC 60825-1 regulations, laser power output is measured by 7mm aperture stop from a 10 cm distance of the laser.

^{**} According to FDA 1040.10 & IEC 60825-1 regulations, laser power output is measured by 7mm aperture stop from a 10 cm distance of the laser.