
Green Line Laser Module with TTL Function Fan Angle 60° Uniform Line

VLM-520-57-60°Series



The newly developed glass line lens come with various fan angles and they produce high quality uniform laser line in a robust stainless housing, ideal for automation, machine vision, image processing, digital data acquisition, counting, precision 3D scanner and science & medical application. They are all come with TTL function to allow up to 10K Hz modulation frequency. They are available at 10 cm, 20 cm, 40 cm and 90 cm focus length, red & green wavelength, Class 1M and Class 2M laser class to cover within 1 meter range task. For customized focus length, wavelength and laser power output, please contact us.

FEATURES:

- Built with high precision glass line lens and glass laser collimating lens.
- Fan Angle : 60°
- Focus range: 10cm, 20cm, 40cm, 90cm, customized focus length are available by request.
- CW to 10K HZ stable power output for demanding power and speed are of important.
- Customized focus within 1 meter available please direct contact us.
- Two laser power output level: LPO Class 1M laser product

LPT - Class 2M laser product

- Dimensions : Ø10 x 40 mm (Ø0.39" x 1.575")
- Wavelength : 515~530 nm
- 3~6 VDC operation.
- Connection type : Lead wire
- Laser line demonstration : <u>https://www.youtube.com/watch?v=3_gRtxyeP28</u>

APPLICATIONS: ideal for

- Machine vision.
- Automation industry.
- Image processing.
- Medical & Science.
- Scanning.
- Precision 3D scanner.
- Counting.
- Measurement.

Headquarter

QUARTON INC.

QUARTON USA INC. Cell: 210-837-3485 contact@guarton.com

www.guarton.com


USA

@Copyright 2020 Quarton inc. All Rights Reserved.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.guarton.com

VLM-520-57-60°Series

OUTLINE DIMENSIONS (UNITS: mm)



SPECIFICATIONS

Part Number		VLM-520-57 LPO-D60-				VLM-520-57 LPT-D60-			
	T art Number		F20	F40	F90	F10	F20	F40	F90
1	Focus length	10 cm	20 cm	40 cm	90 cm	10 cm	20 cm	40 cm	90 cm
2	Fan angle / Laser line length		60° / L	ength	of Lase	er Line	as TA	BLE A	
3	Laser line width				AS TA	BLE B			
4	Recommended working range				AS TA	BLE B			
5	TTL modulation frequency			Hig	gh ON,	0-10K	Hz		
6	6 Dimensions		Ø	10 x 40) mm (Ø	Ø0.39"	x 1.57	5")	
7	Weight				18:	±1g			
8	Operating voltage (Vop)				3~6 VDC				
9	Operating current (lop)	Less than 80mA			Less than 180mA				
10	Optical power*	L	Less than 10mW			Less than 30mW			W
11	Laser power output**	Less than 0.39mW Less than				an 1mV	V		
12	Laser class		Class 1M			Clas		ss 2M	
13	Wavelength (λp)				515~5	530nm			
14	Collimating lens / Line generating lens	Aspherical glass lens							
15	Output aperture				8n	าท			
16	Beam shape				Li	ne			
17	Laser line accuracy	40"(±1mm@5M)							
18	Operating temp. range***	-20°C ~+60°C							
19	Storage temp. range	-20°C ~+85°C							
20	Housing material / color	Stainless steel / Silver							
21	Potential of housing	Insulated							

Headquarter QUARTON INC.

QUARTON USA INC.

USA

@Copyright 2020 Quarton inc. All Rights Reserved.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.quarton.com Cell: 210-837-3485 contact@quarton.com www.quarton.com

VLM-520-57-60°Series

22	Electrostatic discharge (ESD)	30KV
23	Moisture sensitivity level (MSL)	Level 1 - acc to JEDEC J-STD-020E.
24	Wire type	2464 3-WIRE CABLE 26 AWG
25	Cable length	330±30mm
26	Mean time to failure (MTTF) 25°C	Above 10000 hrs
27	International Protection Marking	IP65
20	Application	Precision fine line for Automation, Machine vision and
20	Application	Medical with modulation function
29	Suggestion work distance	0~1.2 meters / 0~4 feet

* Optical power is total power output measured at the aperture of the laser.

** According to FDA 1040.10 & IEC 60825-1 regulations, laser power output is measured by 7mm aperture stop from a 10 cm distance of the laser.

*** Operation temperature means within this temperature range, the laser spot/line will not be affected to change the spot size/line width. It can still work over this range, but the laser spot size or laser line width will be larger.


SAFETY LABEL

LPO:

CLASS I LASER PRODUCT



TABLE A: Laser Line Length Table:



Length of laser line:

Distance	10 cm	20 cm	40 cm	100 cm					
Fan angle	(4 inch)	(8 inch)	(16 inch)	(40 inch)					
5°	0.9 cm	1.75 cm	3.5 cm	7.85 cm					
	(0.35")	(0.7")	(1.4")	(3")					
10°	1.75cm	3.5 cm	7 cm	17.5 cm					
	(0.6″)	(1.4")	(2.8″)	(6")					
15°	15° 2.6 cm		10.5 cm	26.3 cm					
	(1″)		(4")	(10")					
20°	3.5 cm	7 cm	14 cm	35 cm					
	(1.4")	(2.8″)	(5.6")	(14")					
30°	5.3 cm	10.7 cm	21 cm	53.5 cm					
	(2")	(4")	(8")	(20")					
45°	8.28 cm	16.6 cm	33.1 cm	82.85 cm					
	(3¼″)	(6½")	(13")	(32½")					
60°	11.5 cm	23 cm	46 cm	115.5 cm					
	(4½")	(9")	(18")	(45")					
110°	28.6 cm	57.1 cm	114.2 cm	285.6 cm					
	(11¼")	(23″)	(46")	(112½")					

Headquarter

QUARTON INC.

USA QUARTON USA INC.

@Copyright 2020 Quarton inc. All Rights Reserved.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.quarton.com

Cell: 210-837-3485 contact@quarton.com www.quarton.com

VLM-520-57-60°Series




TABLE B: Recommended working range:

Focus at 10 cm:

Working range: 0 - 20cm(0-7.9")
Best at: 7 - 14.5cm(2.8"-5.7")
Laser Line Width <1mm

					Laser Lir	e Width <2mm
Laser	Re	ecom	mende	d Work	ing Ran	ge(cm)
Fan Angle		5	10	15	20	25
5°			6.5 -	16	-21	
10°		I	8 - 1	15	-19	
15°		6-	8 - 1	15	-19	
20°	4	-	7 - 1	.6	-21.5	
30°	4	- 6	- 14.5		-21	
45°	0-	5	.5 - 19	5	-19	
60°	0-		7 - 14	.5	-20	
110°	0-		7 - 1	6.5	-22.5	

Focus at 40 cm:

Working range: 3 - 72cm(1.2"-28.3")

Best at: 20 - 58cm(7.9"-22.8") Laser Line Width <1mm Laser Line Width <2mm

Laser	Reco	mmended W	orking Ran	ge(cm)
Fan Angle	15	30 4	5 60	75
5°	11-	20.5 - 5	57	-75
10°	11.5-	22 - 47.5	-61.5	
15°	7-	21 - 53	-64	
20°	6-	21 - 54	-68	I
30°	5-	21 - 54	-68	
45°	4-	22 - 5	6 -69	
60°	3-	20 - 5	8 -	72
110°	3-	21 - 5	8	-82

Focus at 20 cm:

Working range: 11 - 32cm(4.3"-12.6") Best at: 15 - 23.5cm(5.9"-9.3") Laser Line Width <1mm

				Laser Lin	e Width <2m
Laser	Recom	mende	d Work	ing Ran	ge(cm)
Fan Angle	10	15	20	25	30
5°		12.5- 1	5 - 23	-26	
10°	10-	14	- 22	-26	
15°	10-	14.	5 - 22	-26	
20°	10-	14	.5 - 23	-27	
30°	10-	14	- 22	-26	
45°	9-	13	- 24		-34
60°	11	- 19	5 - 23.5		-32
110°	8-	12.5	- 23		-30

Focus at 90 cm:

Working range: 35 - 145cm(13.8"-57")

Best at: 56 - 116cm(22"-45.7") Laser Line Width <1mm Laser Line Width <2mm

Laser	Recommended Working Range(cm)						
Fan Angle	40	65	90	115	140		
5°	29-	45 - 9	91 -1	09			
10°	35-		57 - 119		-146		
15°	31-		57 - 119		-140		
20°	31-		59 - 12	2	-142		
30°	42-	(50 - 114		-144		
45°	40-		55 - 120		-139		
60°	35-	5	56 - 116		-145		
110°	38-	60) - 106	-1	34		

Laser Line Width <1mm Laser Line Width <2mm

Headquarter

QUARTON INC.

QUARTON USA INC.

USA

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.quarton.com

Cell: 210-837-3485 contact@quarton.com www.quarton.com

@Copyright 2020 Quarton inc. All Rights Reserved.

Optional Accessories

Quarton offers mounts, power supply boards, battery pack and USB cable switch to help you running as quickly as possible. For more information, please visit <u>www.quarton.com</u>, <u>www.quarton.com/contact</u> or email <u>contact@quarton.com</u>.

QLM-1125 - Laser Module Mount/Holder for diameter 6mm to 12.5mm, it's an ideal choose for mounted onto optical tables.

Feature:

- 4 directions adjustable.
- Can be mounted onto the optical table with screws (Screws not included).
- Engraved scale for precision adjustable.



LMPS-MP1 - Multi-function Laser Module Power Supply Board. Four input : USB, micro USB, DC Power Jack(5.5 x 2.1), and terminal block. Two channel output : 7 VDC 500mA and 5 VDC 1A. Three switches-toggle switch, remote switch and TTL signal.



Feature:

- Allow four kinds of power input: USB, micro USB, DC Power Jack(5.5x2.1) and terminal block.
- Two Channel output: 7 VDC 500mA and 5 VDC 1A.
- Built-in three switches: toggle switch, terminal block remote switch and TTL signal switch by on-board connect point.
- 7 VDC output work for all Quarton Laser Modules with 7-12 V operation Voltage (Vop).
- 5 VDC output work for all Quarton Laser Modules with 3-6 V operation Voltage (Vop).
- Three LED indicators: Input power indicator, 7V output indicator and 5V output indicator.

Headquarter QUARTON INC.


USA QUARTON USA INC.

@Copyright 2020 Quarton inc. All Rights Reserved.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.guarton.com

Cell: 210-837-3485 contact@quarton.com www.quarton.com

Optional Accessories



LMPS-MP2 - DC converter, In: 9-36V, Out: 5V 1A.



LMPS-mUSB1 - Laser Module Power Supply Board, Input: micro USB, Output: 5 VDC 500mA.

Feature:

- Micro USB connector power input.
- Output 5 VDC 500mA with alligator clips.
- For all Quarton Laser Modules that require 3-6V operation Voltage.



LMPS-DC1 - Laser Module Power Supply Board, Input: DC Power Jack(5.5 x 2.1), Output: 5 VDC 500mA.

Feature:

- DC Power Jack(5.5 x 2.1) power input.
- Output 5 VDC 500mA with alligator clips.
- For all Quarton Laser Modules that require 3-6V operation voltage.

Headquarter QUARTON INC.

USA QUARTON USA INC.

Cell: 210-837-3485 contact@quarton.com www.quarton.com

@Copyright 2020 Quarton inc. All Rights Reserved.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.quarton.com



Optional Accessories



CLM-BP4N3 - Battery pack (4* AA batteries)

*** AA Batteries are **NOT** included in package.

Feature:

- USB Output Voltage: 5 VDC.
- Color: Black.



CLM-USBSW - USB Cable Switch.

Feature:

- Length: 28cm.
- Color: Black.



CLM-UM3M - USB to micro USB Cable.

Feature:

- Length: 3 meters.
- Color: Black.

Headquarter

QUARTON INC.

Tel: 886-2-2648-5656 Fax: 886-2-2648-5522 contact@quarton.com www.quarton.com USA QUARTON USA INC.

erved. Tel: 886-2-2648-56

Cell: 210-837-3485 contact@quarton.com www.quarton.com

@Copyright 2020 Quarton inc. All Rights Reserved.