



VHP69273X22J

Vehicular 5-Port MIMO Antenna
698-960 MHz / 1710-2700 MHz /
4900-5900 MHz / GNSS

The Laird Connectivity vehicular five-port MIMO antenna covers the 698-960/1710-2700 MHz and 2300-2700/4900-5900 MHz frequency ranges with an added global navigational antenna. Configured with two 3G/4G ports and two dual band Wi-Fi ports and a fifth port configured with a GNSS navigational antenna.

Connector options include, but not limited to, SMA male connectors for 3G/4G LTE and GNSS ports with an RPSMA male connector for the Wi-Fi port. The housing incorporates a low-profile, rugged design that meets IP67, EN61373 Shock & Vibration and EN50155 Temperature and Humidity standards. The antenna also features high impact, UV-resistant polycarbonate plastic radome available in black or white.

APPLICATIONS

- FirstNet/Public Safety
- Passenger Fleet
- Commercial Vehicle Fleet
- Rail Transit

ELECTRICAL SPECIFICATIONS

Number of Ports	3G/4G LTE - 2		Wi-Fi - 2	
	698-960	1710-2700	2300-2700	4900-5900
Operating Frequency (MHz)	698-960	1710-2700	2300-2700	4900-5900
VSWR - Avg.**	<1.7:1	<1.6:1	<1.7:1	<1.4:1
VSWR - Max**	<2.0:1	<2.0:1	<2.0:1	<2.0:1
Gain - Peak (dBi)*	4.1	5.9	6.2	6.5
Gain Horizon 30° - Max (dBi)*	N/A	N/A	N/A	6.2
Typical Port-to-Port Isolation**	698-960	1710-2700	2300-2700	4900-5900
LTE 1 to LTE 2	>14	>26	>28	N/A
LTE 1 to Wi-Fi 1	>27	>18	>20	>31
LTE 1 to Wi-Fi 2	>26	>19	>23	>29
LTE 2 to Wi-Fi 1	>27	>19	>23	>28
LTE 2 to Wi-Fi 2	>26	>18	>20	>33
Wi-Fi 1 to Wi-Fi 2	N/A	N/A	>20	>29

ELECTRICAL SPECIFICATIONS

Nominal Impedance (Ohms)	50
Max Power - Ambient 25°C (W)	50
Polarization	Vertical Linear
Horizontal Plane 3 dB Beamwidth Port 1	Omnidirectional

* Measured on 1 ft (30.48 cm) diameter ground plane

** Measured on 1 ft (30.48 cm) diameter ground plane and 17 ft (518 cm)

MECHANICAL SPECIFICATIONS

Dimensions - diameter x height - mm (in.)	132 x 87 (5.20 x 3.4)
Weight - kg (lbs)	Approximately 1.16 (2.55)
Cable Type	LMR [®] -195 or equivalent
Mounting	P- Mount
Radome and Base Plate Material	PC, UL94 - V0 Rating, UV Stable

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature - °C (°F)	-30 to +70 (-22 to +158)
Storage Temperature - °C (°F)	-40 to +85 (-40 to +185)
Shock and Vibration Tests	EN61373 Compliant
Temperature and Humidity Tests	EN50155 Compliant
Ingress Protection Rating	IP67
Material Substance Compliance	RoHS

GNSS ANTENNA SPECIFICATIONS

Model Number	VHP69273x22J		
Number of Ports	GNSS- 1		
Frequency Band (MHz)	Beidou	GPS	GLONASS
Frequency of Operation (MHz)	1561.098 ± 2.046	1.575.42 ± 1.023	1602.0 ± 5.0
Amplifier Gain (dB)	28 dB ± 3		
Nominal Impedance (Ohms)	50 Ω		
Output VSWR	< 2:1		
DC Voltage	2.5 - 7 Vdc		
Current Consumption, mA	8.5 ± 3 (at 3.0V)		
Input Max Power, dBm	-10		
Out of Band Rejection, dBc	> 80 (698- 960 MHz)	> 80 (1428- 2700 MHz)	> 70 (4900- 5800 MHz)
Working/Storage Temperature	-40°C - +85°C (-40°F - +185°F)		
Connector	SMA-Male		
Cable - Exposed Length	RG174-518.2 cm (17 ft.)		


CONFIGURATION

PART NUMBER	CABLE LENGTH	CONNECTOR LTE PORTS	CONNECTOR WI-FI PORTS	COLOR	NAVIGATION
VHP69273B22J-518A	5.18m (17ft)	SMA Male	RPSMA Male	Black	GNSS
VHP69273W22J-518A	5.18m (17ft)	SMA Male	RPSMA Male	White	GNSS

PACKAGING INFORMATION

PACKAGE DIMENSIONS	CARTON	MASTER CARTON	AIR PALLET	OCEAN PALLET
Number of Antennas	4	8	192	240
Height- mm (in.)	305 (12.0)	305 (12.0)	1363 (53.66)	1668 (65.67)
Length- mm (in.)	525 (20.7)	525 (20.7)	1200 (47.24)	1200 (47.24)
Width- mm (in.)	132 (5.22)	265 (10.4)	800 (31.5)	800 (31.5)
Shipping Weight- kg (lb.)	5.0 (11)	10.1 (22.3)	255 (562)	316 (697)




MECHANICAL DRAWING






RADIATION PATTERN - LTE/CELL RTS

— Port 1 — Port 2




698 MHz






851 MHz



960 MHz






1710 MHz






— Port 1 — Port 2




1880 MHz






1930 MHz



2170 MHz






2310 MHz






— Port 1 — Port 2

2700 MHz






RADIATION PATTERN - WIFI PORTS

2300 MHz






2400 MHz






— Port 1 — Port 2




2500 MHz






2700 MHz



4900 MHz






5470 MHz






— Port 1 — Port 2

5725 MHz



5925 MHz



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

©2021 TE Connectivity. All Rights Reserved.

11/21 Original

