


2 Watt

- Regulated Single & Dual Output
- 2:1 Input Range
- Compact DIP8 Package
- 1500 VDC Isolation
- Operating Temperature -40 °C to +95 °C
- ITE Safety Approvals
- Full Load at 70 °C
- Class A Conducted & Radiated Emissions
- 3 Year Warranty



Dimensions:

IEU02:
0.55 x 0.55 x 0.31" (14.0 x 14.0 x 8.0 mm)

Models & Ratings

| Input voltage | Output voltage | Output current | Input current ⁽¹⁾ | | Maximum capacitive load ⁽²⁾ | Efficiency | Model number |
|---------------|----------------|----------------|------------------------------|-----------|--|------------|--------------|
| | | | No load | Full load | | | |
| 4.5-10V | 3V3 | 400 mA | 40 mA | 335 mA | 100 µF | 79% | IEU0205S3V3 |
| | 5 V | 400 mA | | 495 mA | 100 µF | 81% | IEU0205S05 |
| | 12V | 167 mA | | 470 mA | 100 µF | 85% | IEU0205S12 |
| | 15V | 134 mA | | 460 mA | 100 µF | 87% | IEU0205S15 |
| | ±5V | ±200 mA | | 480 mA | ±100 µF | 83% | IEU0205D05 |
| | ±12V | ±83 mA | | 470 mA | ±100 µF | 85% | IEU0205D12 |
| | ±15V | ±67 mA | | 475 mA | ±100 µF | 85% | IEU0205D15 |
| 9-18V | 3V3 | 400 mA | 27 mA | 140 mA | 100 µF | 80% | IEU0212S3V3 |
| | 5 V | 400 mA | | 200 mA | 100 µF | 83% | IEU0212S05 |
| | 12V | 167 mA | | 190 mA | 100 µF | 87% | IEU0212S12 |
| | 15V | 134 mA | | 195 mA | 100 µF | 87% | IEU0212S15 |
| | ±5V | ±200 mA | | 200 mA | ±100 µF | 84% | IEU0212D05 |
| | ±12V | ±83 mA | | 195 mA | ±100 µF | 86% | IEU0212D12 |
| | ±15V | ±67 mA | | 195 mA | ±100 µF | 86% | IEU0212D15 |
| 18-36V | 3V3 | 400 mA | 15 mA | 70 mA | 100 µF | 79% | IEU0224S3V3 |
| | 5 V | 400 mA | | 100 mA | 100 µF | 84% | IEU0224S05 |
| | 12V | 167 mA | | 95 mA | 100 µF | 86% | IEU0224S12 |
| | 15V | 134 mA | | 95 mA | 100 µF | 87% | IEU0224S15 |
| | ±5V | ±200 mA | | 100 mA | ±100 µF | 84% | IEU0224D05 |
| | ±12V | ±83 mA | | 95 mA | ±100 µF | 86% | IEU0224D12 |
| | ±15V | ±67 mA | | 95 mA | ±100 µF | 86% | IEU0224D15 |
| 36-75V | 3V3 | 400 mA | 8 mA | 35 mA | 100 µF | 79% | IEU0248S3V3 |
| | 5 V | 400 mA | | 50 mA | 100 µF | 83% | IEU0248S05 |
| | 12V | 167 mA | | 50 mA | 100 µF | 85% | IEU0248S12 |
| | 15V | 134 mA | | 50 mA | 100 µF | 86% | IEU0248S15 |
| | ±5V | ±200 mA | | 50 mA | ±100 µF | 82% | IEU0248D05 |
| | ±12V | ±83 mA | | 50 mA | ±100 µF | 84% | IEU0248D12 |
| | ±15V | ±67 mA | | 50 mA | ±100 µF | 84% | IEU0248D15 |

Notes

1. Input currents measured at nominal input voltage.
2. Maximum capacitive load is per output.

Input

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|---------------------|--------------------|---------|---------|-------------|--------------------|
| Input Voltage Range | 4.5 | | 10 | VDC | 5 V nominal |
| | 9.0 | | 18 | | 12 V nominal |
| | 18.0 | | 36 | | 24 V nominal |
| | 36.0 | | 75 | | 48 V nominal |
| Input Filter | Internal Capacitor | | | | |
| Input Surge | | | 12 | VDC for 1 s | 5 V nominal |
| | | | 25 | | 12 V nominal |
| | | | 50 | | 24 V models |
| | | | 100 | | 48 V models |

Output

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|--------------------------|---------|---------|---------|-------------|---|
| Output Voltage | 3.3 | | 30 | VDC | See Models and Ratings table |
| Initial Set Accuracy | | | ±1.5 | % | At full load |
| Output Voltage Balance | | | ±2.0 | % | For dual output with balanced loads |
| Minimum Load | | | | A | No minimum load required |
| Line Regulation | | | ±0.2 | % | From minimum to maximum input at full load |
| Load Regulation | | | ±1.0 | % | From 0 to full load |
| Cross Regulation | | | ±5.0 | % | On dual output models when one load is varied between 25% and 100% and other is fixed at 100% |
| Transient Response | | | 5 | % deviation | Recovery within 1% in less than 500 µs for a 25% load change. |
| Ripple & Noise | | 70 | | mV pk-pk | 20 MHz bandwidth. Measured using 0.47 µF ceramic capacitor. |
| Overload Protection | | 180 | | % | |
| Short Circuit Protection | | | | | Continuous, with auto recovery |
| Maximum Capacitive Load | | | | | See Models and Ratings table |
| Temperature Coefficient | | | 0.02 | %/°C | |

General

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|----------------------------|-----------------|-------------|---------|-------------------|------------------------------|
| Efficiency | | 84 | | % | See Models and Ratings table |
| Isolation: Input to Output | 1500/1800 | | | VDC | 60 s/1 s |
| Isolation Resistance | 10 ⁹ | | | Ω | At 500 VDC |
| Isolation Capacitance | | 100 | | pF | |
| Switching Frequency | | 100 | | kHz | |
| Power Density | | | 21.3 | W/in ³ | |
| Mean Time Between Failure | | 4.2 | | MHrs | MIL-HDBK-217F, +25 °C GB |
| Weight | | 0.008 (3.9) | | lb (g) | |

Environmental

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|---------------------------------|----------------|---------|---------|-------|------------------------------|
| Operating Temperature | -40 | | +95 | °C | See Derating Curve. |
| Storage Temperature | -50 | | +125 | °C | |
| Case Temperature | | | +95 | °C | |
| Humidity | | | 95 | %RH | Non-condensing |
| Cooling | | | | | Natural convection |
| Case Flammability | UL 94V-0 Rated | | | | Non conductive black plastic |
| Lead-Free Reflow Solder Process | | | | | IPC/JEDEC J-STD-020D.1 |

EMC: Emissions

| Phenomenon | Standard | Test Level | Notes & Conditions |
|------------|----------|------------|----------------------|
| Conducted | EN55022 | Class A | See application note |
| Radiated | EN55022 | Class A | See application note |


EMC: Immunity

| Phenomenon | Standard | Test Level | Criteria | Notes & Conditions |
|-----------------|-------------|------------------------------------|----------|--|
| ESD | EN61000-4-2 | ±8 kV air discharge, ±6 kV contact | A | |
| Radiated | EN61000-4-3 | 10 V/m | A | |
| EFT/Burst | EN61000-4-4 | ±2 kV | A | With external input capacitor, suggested part is CHEMI-CON KY 220µF/100V |
| Surge | EN61000-4-5 | ±1 kV | A | With external input capacitor, suggested part is CHEMI-CON KY 220µF/100V |
| Conducted | EN61000-4-6 | 10 V rms | A | |
| Magnetic Fields | EN61000-4-8 | 3 A/m | A | |

Safety Approvals

| Safety Agency | Safety Standard | Notes & Conditions |
|---------------|------------------------------|------------------------|
| CB Report | IEC60950-1 | Information Technology |
| UL | UL/cUL60950-1, UL/cUL62368-1 | Information Technology |

Mechanical Details




| Pin Connections | | |
|-----------------|--------|--------|
| Pin | Single | Dual |
| 1 | -Vin | -Vin |
| 4 | +Vin | +Vin |
| 5 | +Vout | +Vout |
| 6 | No Pin | Common |
| 7 | -Vout | -Vout |

Notes


- All dimensions are in inches (mm)
- Weight: 0.008 lbs (3.9g) approx.
- Tolerance: X.XX±0.01 (X.X±0.25)
X.XXX±0.005 (X.XX±0.13)
- Pin Tolerance: ±0.002 (±0.05)

Application Notes

Derating Curve



EMI Filter



| Model | C1 | L1 |
|---------|--------------|---------|
| IEU0205 | 4.7 µF/16 V | 3.3 µH |
| IEU0212 | 4.7 µF/25 V | 18.0 µH |
| IEU0224 | 4.7 µF/50 V | 39.0 µH |
| IEU0248 | 2.2 µF/100 V | 68.0 µH |

C1 = 1206 X7R MLCC, L1 = SCD0504T series