kHz Range Crystal unit

FC-135R

SEIKO EPSON CORPORATION

Product name Product Number / Ordering code

FC-135R 32.768000 kHz 12.5 +20.0-20.0 X1A0001410003xx


Please refer to the 5.Packing information about xx (last 2 digits)

Complies with EU RoHS directive

Reference weight Typ. 11 mg


1.Absolute maximum ratings						
Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions / Remarks
Storage temperature	T_stg	-55	-	+125	°C	Storage as single product
Maximum drive level	GL	-	0.5	-	μW	

2.Specificatoins(characterist	ics)					
Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions / Remarks
Nominal frequency	f_nom	-	32.768	-	kHz	
Operating temperature	T_use	-40	-	+85	٥C	
Level of drive	DL	-	0.1	-	μW	
Frequency tolerance	f_tol	-20	-	+20	x 10 ⁻⁶	+25ºC DL=0.1μW
Turnover temperature	Ti	+20	+25	+30	°C	
Parabolic coefficient	В	-	-	-0.04	x 10 ⁻⁶ /°C ²	
Load capacitance	CL	-	12.5	-	pF	
Motional resistance (ESR)	R1	-	35	50	kΩ	
Motional capacitance	C1	-	3.4	-	fF	
Shunt capacitance	C0	-	1.0	-	pF	
Motional inductance	L1	-	7.0	-	kH	
Frequency aging	f_age	-3	-	+3	x10 ⁻⁶ /yea	@+25°C, First year




4.Footprint(Recommended)	(Unit: mm)
*Do not design any circuit patterns in the sh	1.8

5.Packing	information	on		
[1]Product	number las	t 2 digits code (xx) description		The recommended code is "00"
	X1A00014	10003xx		
	Code	Condition	Code	Condition
	01	Any Q'ty vinyl bag(Tape cut)	14	1000pcs / Reel
	11	Any Q'ty / Reel	15	2000pcs / Reel
	12	250pcs / Reel	00	3000pcs / Reel
	13	500pcs / Reel		
		Code 01 11 12	01Any Q'ty vinyl bag(Tape cut)11Any Q'ty / Reel12250pcs / Reel	CodeConditionCode01Any Q'ty vinyl bag(Tape cut)1411Any Q'ty / Reel1512250pcs / Reel00



SEIKO EPSON CORPORATION



Notice

- · This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
- The information about applied data, circuitry, software, usage, etc. written in this material is intended for reference only.
- Seiko Epson does not assume any liability for the occurrence of customer damage or infringing on any patent or copyright of a third party.
- This material does not authorize the licensing for any patent or intellectual copyrights.
- When exporting the products or technology described in this material, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that you
- would not make the products available to any third party who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require
- extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
- / Space equipment (artificial satellites, rockets, etc.)
- / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.)
- / Medical instruments to sustain life
- / Submarine transmitters
- / Power stations and related
- / Fire work equipment and security equipment
- / Traffic control equipment
- / And others requiring equivalent reliability.

· All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective.

Contact us

www5.epsondevice.com/en/contact/