## Johanson Capability Guide





# Electronic Accura Through Mech

Knowles Capacitors is the result of the merging of some of the world's leading speciality capacitor manufacturers. With a combined history exceeding 175 years, Dielectric Laboratories (DLI), Johanson MFG, Novacap, Syfer and Voltronics have come together in a single organisation, with one team of great people sharing a common vision.

With facilities located worldwide, Knowles Capacitors is an outstanding, environmentally conscious global supplier. Knowles is proud to be certified to ISO 9001:2008. State-of-the-art technology and equipment in pristine facilities enable Knowles to control the product from design through manufacturing.

Knowles Capacitors is a world-class supplier of Trimmer Capacitors and microwave Tuning Elements. We offer a wide variety of variable capacitors for RF and microwave applications. Giga-Trim® capacitors



# cy anical Precision.

are miniature capacitors designed for high resolution tuning of RF power circuits. Knowles Air Capacitors are available in a variety of sizes and mounting configurations incorporating a one piece, selflocking, constant torque drive mechanism. Ceramic Trimmer Capacitors are available in surface mount, strip-line and through hole lead styles. Microwave Tuning Elements are an economical means of tuning waveguides, cavities and other microwave structures.


Please see our website at www.johansonmfg.com

### Johanson components

- Tuning Elements
- Non-magnetic Trimmer Caps
- Thin-Trim
- Cera-Trim
- Seal-Trim
- Giga-Trim
- Air Trimmer Capacitors
- Non-magnetic Variable Inductors



# *Tuning Elements*



### **Typical Applications**

- Microwave Filter Positioning
- Fiber Optic Alignment
- Metering Valve Adjustment
- X Y Z Stage Positioning
- Self Locking Fastener

Other Products Available Posi-Torque® • Taps Tuning Rotors DynaTrim / Tuners Comb Line Filters

• Limit Switch/Sensor Positioning

Features

- Basic thread diameters available from 0.060" to 1.00", SI and US customary threads Excellent electrical conduction (Contact resistance <0.01 Ω)</li>
- Capable of re-tuning/re-positioning

• Self-Locking/Constant torque mechanism • Eliminates need for "jam" nuts


positioning from 24 TPI to 108 TPI

- Available with Gold, Silver, Nickel Plating and Chromate Finish • Can be assembled with other materials, (Ceramic, Ferrites,
- Sapphire, Glass, etc.)
- Available as a set, to provide a positive stop or extended travel range

· Produced with fine-pitched threads for high resolution zero back lash

- Available in copper or ferrous alloys
- Custom torque designs available

One handed adjusting/tuning



## Non-magnetic trimmer Caps

Working

Voltage 5000 VDC

1250 VDC

1000 VDC

250 VDC

Cap. Range

1 to 7.5 pF

1.5 to 10 pF

1.5 to 19 pF

1 to 25 pF

2 to 30 pF

0.4 to 3.5 pF

0.6 to 6.0 pF

0.8 to 10 pF

1 to 30 pF

**Series** 

5610

52H

55H

59H

56H

5860

5760

5240

5640

Q

>1000 @100MHz

>1400 @195MHz

>1000 @175MHz

>1000 @175MHz

>1000 @175MHz

>10000 @100MHz

>10000 @100MHz

>4000 @100MHz

>800 @100MHz

			cs

- Working Voltage: From 250 VDC to 5000 VDC
- Long Rotational life
- Insulation Resistance: > 106 MO
- Temperature range:
- -65°C to +125°C
- RoHS Compliant parts available


### Specifications (53H18NM)

- Capacity Range: 3.0pF to 55pF (>17 Turns)
- Working Voltage: 1000 VDC (Test Volt. 2000 VDC)
- Q @ 175 MHz >800
- Insulation Resistance: >10<sup>6</sup> MEGOHMS
- Temperature Range: -65°C to +125°C
- Tuning Torque: 1.0 to 6.0 OZ. IN


_		_
		iction

### Non-magnetic structure with PTFE dielectric

- Brass Structure
- Glazed Alumina Insulation
- 574°F Solder Used in Assembly
- Gold, Silver and Chromate Finish
- Vertical Mount Version also Available




## Thin-Trim



Series	Disk Size	Capacitance	Tuning Resolution
9401	0.140" (3.56 mm)	0.25 to 4.0 pF	90°
9402	0.125" (3.18 mm)	0.5 to 25 pF	180°
9410	0.200" (5.08 mm)	1 to 50 pF	180°





### Characteristics

- Working Voltage: 250 VDC (500 VDC Test)
- Insulation Resistance: > 104 MΩ
- Temperature Range: -55°C to +125°C
- Tuning Tool: 4192
- RoHS Compliant parts available
- Non-Magnetic

### **Applications**

- RF amplifier
- LC Filters and Networks
- Broadband Wireless LAN
- Medical Devices
- Cordless and Cellular phones
- DR/Crystal Oscillator
- Microstrip line filters







Series	Disk Size	Capacitance	Tuning Resolution	
9610/9810	0.270" (6.86 mm)	1 to 50 pF	180°	
9620/9820	0.180" (4.57 mm)	0.5 to 25 pF	180°	


### **Applications**

- RF amplifier
- LC Filters and Networks
- Broadband Wireless LAN
- Medical Devices
- Cordless and Cellular phones
- DR/Crystal Oscillator
- Microstrip line filters

### Characteristics

- Working Voltage: 250 VDC (500 VDC Test)
- Long Rotational life
- Insulation Resistance: > 104  $M\Omega$
- Temperature Range: -55°C to +125°C
- RoHS Compliant parts available
- Non-Magnetic







Capacitance	Series	Q @ 250 MHz	
0.3 to 1.2 pF	27260	> 5000	
0.4 to 2.5 m5	27280	> 4000	
0.4 to 2.5 pF	47280	> 4000	
0.3 to 2.3 pF	47480	> 2000	
	17270	> 2000	
	27270	> 3000	
0.6 to 4.5 pF	47270	> 3000	
	57280	> 1000	
0 0 to 0 0 mF	27290	> 3000	
0.8 to 8.0 pF	57270	> 1000	
2.0 to 6.0 pF	47470	> 1500	

### Applications

- RF amplifier
- Impedance matching
- Crystal trimming
- Interstage coupling
- Filter tuning

**Applications** 

• RF amplifier and oscillators

• Impedance matching

Interstage couplingFilter tuning

Crystal trimming

### Characteristics


- Working Voltage: 500 VDC (1000 VDC Test)
- Long rotational life
- Insulation resistance: > 106 MΩ
- Temperature range: -65°C to +125°C
- RoHS Compliant parts available

### Air Trimmer Capacitors

	.125(	
	15/64	
5 +.015		
.32		8
6-TA		

### Characteristics

- Working Voltage: 250 VDC (500 VDC Test)
- Long Rotational life
- Insulation resistance: > 106 MΩ
- Temperature range: -65°C to +125°C
- RoHS Compliant parts available



### **Non-magnetic variable inductors NRI/NR Systems adis by Systems by Syst**




Test Equipment

### Characteristics

- Patent pending, precision machined design
- 7mm high in SMD, Vertical SMD and thru-hole versions
- Nominal values of 32 to 118nH, 2 to 7 turns
- Q as high at 121 @ 100MHz, SRF 0.7 1.5 GHz
- Superb shock, vibration and thermal tolerances
- -40°C to +85°C
- Customized version requests welcomed

	Deut Ma	L(nH) Q			(@	SRF	-	Thread	
	Part No.	Min	Nom	Max	No Core	100MHz)	(GHz)	Turns	(mm)
	JLC02E030TRSM	32	33	34	39	90	1.2	2	6
	JLC03E048TRSM	46	49	52	59	95	1	3	6
t _	JLC04E065TRSM	60	64	68	78	101	0.9	4	6
Surface Mount Horizontal	JLC05E088TRSM	74	81	87	99	114	0.9	5	8
e ≥ zo	JLC06E110TRSM	94	107	119	123	119	0.7	6	8
fac	JLC07E130TRSM	104	118	133	142	121	0.7	7	10
Sur	JLC09E160TRSM	122	130	170	191	162	0.58	9	13
	JLC13E250TRSM	185	219	270	294	199	0.43	13	18
	JLC19E375TRSM	281	345	436	457	171	0.31	19	25
	Part No.	L(nH) Q			(@	SRF	Turns	Thread	
		Min	Nom	Max	No Core	100MHz)	(GHz)		(mm)
- <u>4</u>	JLC02E030TRSM	32	33	34	39	90	1.2	2	6
Surface Mount Vertical	JLC03E048TRSM	46	49	52	59	95	1	3	6
ace Mo Vertical	JLC04E065TRSM	60	64	68	78	101	0.9	4	6
Ver	JLC05E088TRSM	74	81	87	99	114	0.9	5	8
urfa /	JLC06E110TRSM	94	107	119	123	119	0.7	6	8
SI	JLC07E130TRSM	104	118	133	142	121	0.7	7	10
	Part No.	Min	L(nł Nom	H) Q Max	No Core	(@ 100MHz)	SRF (GHz)	Turns	Thread (mm)
t	JLC02E030TRSM	32	33	34	39	90	1.2	2	6
	JLC03E048TRSM	46	49	52	59	95	1	3	6
e M tica	JLC04E065TRSM	60	64	68	78	101	0.9	4	6
Hole Mount Vertical	JLC05E088TRSM	74	81	87	99	114	0.9	5	8
	JLC06E110TRSM	94	107	119	123	119	0.7	6	8
Thru -	JLC07E130TRSM	104	118	133	142	121	0.7	7	10





www.knowlescapacitors.com



DLI-JohansonMFG-Novacap-Syfer-Voltronics

Knowles Capacitors designs, manufactures and sells special electronic components. Our products are used in military, space, telecom infrastructure, medical and industrial applications where function and reliability are crucial.



Knowles (Cazenovia) 2777 Route 20 East, Cazenovia, NY 13035 USA

Phone: +1 315 655 8710 Fax: +1 315 655 0445 KCCSales@knowles.com

hanso

Knowles (Cazenovia) 2777 Route 20 East, Cazenovia, NY 13035 USA

Phone: +1 315 655 8710 Fax: +1 315 655 0445 KCCSales@knowles.com



Knowles (Valencia) 25111 Anza Drive, Valencia, CA 91355 USA

Phone: +1 661 295 5920 Fax: +1 661 295 5928 NovacapSales@knowles.com



Knowles (UK) Ltd Hethel Engineering Centre, Chapman Way, Hethel, Norwich, Norfolk NR14 8FB

Phone: +44 1603 723300 Fax: +44 1603 723301 SyferSales@knowles.com



Knowles (Cazenovia) 2777 Route 20 East, Cazenovia, NY 13035 USA

Phone: +1 315 655 8710 Fax: +1 315 655 0445 VoltronicsSales@knowles.com