SIEMENS

Data sheet

US2:17DUB82WL11



Non-reversing motor starter, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 0.75-3.4A, 240V 50Hz / 277V 60Hz coil, Combination type, 30A fusible disconnect, 30A/600V fuse clip, Encl NEMA type 4X 304 S-Steel, Water/dust tight noncorrosive, Extra-wide enclosure

-	-			11
	au	res	sim	ilar
	-			

product brand name	Class 17	
design of the product	Non-reversing motor starter with fusible disconnect	
special product feature	ESP200 overload relay	
General technical data		
weight [lb]	48 lb	
Height x Width x Depth [in]	24 × 20 × 8 in	
touch protection against electrical shock	NA for enclosed products	
installation altitude [ft] at height above sea level maximum	6560 ft	
ambient temperature [°F]		
 during storage 	-22 +149 °F	
during operation	-4 +104 °F	
ambient temperature		
 during storage 	-30 +65 °C	
 during operation 	-20 +40 °C	
country of origin	USA	
Horsepower ratings		
yielded mechanical performance [hp] for 3-phase AC motor		
 at 200/208 V rated value 	0 hp	
• at 220/230 V rated value	0 hp	
 at 460/480 V rated value 	1.5 hp	
 at 575/600 V rated value 	2 hp	
Contactor		
size of contactor	NEMA controller size 1	
number of NO contacts for main contacts	3	
operating voltage for main current circuit at AC at 60 Hz maximum	600 V	
operational current at AC at 600 V rated value	27 A	
mechanical service life (switching cycles) of the main contacts typical	1000000	
Auxiliary contact		
number of NC contacts at contactor for auxiliary contacts	0	
number of NO contacts at contactor for auxiliary contacts	1	
number of total auxiliary contacts maximum	8	
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)	
Coil		
type of voltage of the control supply voltage	AC	
control supply voltage		

• at AC at 50 Hz rated value240 V• at AC at 60 Hz rated value277 Vholding power at AC minimum8.6 Wapparent pick-up power of magnet coil at AC218 VAapparent holding power of magnet coil at AC25 VAoperating range factor control supply voltage rated value of magnet coil0.85 1.1percental drop-out voltage of magnet coil related to the input voltage50 %ON-delay time19 29 msOFF-delay time10 24 ms	
holding power at AC minimum8.6 Wapparent pick-up power of magnet coil at AC218 VAapparent holding power of magnet coil at AC25 VAoperating range factor control supply voltage rated value of magnet coil0.85 1.1percental drop-out voltage of magnet coil related to the input voltage50 %ON-delay time19 29 ms	
apparent pick-up power of magnet coil at AC218 VAapparent holding power of magnet coil at AC25 VAoperating range factor control supply voltage rated value of magnet coil0.85 1.1percental drop-out voltage of magnet coil related to the input voltage50 %ON-delay time19 29 ms	
apparent holding power of magnet coil at AC25 VAoperating range factor control supply voltage rated value of magnet coil0.85 1.1percental drop-out voltage of magnet coil related to the input voltage50 %ON-delay time19 29 ms	
operating range factor control supply voltage rated value of magnet coil0.85 1.1percental drop-out voltage of magnet coil related to the input voltage50 %ON-delay time19 29 ms	
of magnet coilpercental drop-out voltage of magnet coil related to the input voltage50 %ON-delay time19 29 ms	
input voltage 19 29 ms	
OFF-delay time 10 24 ms	
Overload relay	
product function	
overload protection Yes	
phase failure detection Yes	
asymmetry detection Yes	
ground fault detection Yes	
test function Yes	
external reset Yes	
reset function Manual, auto	matic and remote
	0 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release 0.75 3.4 A	
tripping time at phase-loss maximum 3 s	
relative repeat accuracy 1 %	
product feature protective coating on printed-circuit board Yes	
number of NC contacts of auxiliary contacts of overload 1 relay	
number of NO contacts of auxiliary contacts of overload 1 relay	
operational current of auxiliary contacts of overload relay	
• at AC at 600 V 5 A	
• at DC at 250 V 1 A	
	C (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
• with single-phase operation at AC rated value 600 V	
• with multi-phase operation at AC rated value 300 V	
Disconnect Switch	
response value of switch disconnector 30A / 600V	
design of fuse holder Class R fuse	clins
operating class of the fuse link Class R	
Enclosure	
	loss stool
degree of protection NEMA rating 4X, 304 stair	
	aterproof & resistant to corrosion
Mounting/wiring	
mounting position vertical	
	nting and installation
type of electrical connection for supply voltage line-side Box lug	
tightening torque [lbf·in] for supply 35 35 lbf·in	
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	WG)
temperature of the conductor for supply maximum 75 °C permissible	
material of the conductor for supply AL or CU	
type of electrical connection for load-side outgoing feeder Screw-type t	erminals
tightening torque [lbf·in] for load-side outgoing feeder 20 24 lbf·in	1
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded 2x (14 10	AWG)
temperature of the conductor for load-side outgoing feeder 75 °C maximum permissible	

material of the conductor for load-side outgoing feeder	CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17DUB82WL11				
Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:17DUB82WL11				
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17DUB82WL11⟨=en				
Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17DUB82WL11/certificate				

last modified:

1/25/2022 🖸