SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YE28-0AP0



Client order no.	:
Order no. :	
Offer no. :	
Remarks :	

Rated data		
Input		
Number of phases	3 AC	
Line voltage	380 480 V +10 %	% -20 %
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	29.50 A	26.00 A
Rated current (HO)	24.50 A	21.30 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC ¹⁾
Rated power (LO)	15.00 kW	20.00 hp
Rated power (HO)	11.00 kW	15.00 hp
Rated current (LO)	32.00 A	27.00 A
Rated current (HO)	26.00 A	21.00 A
Rated current (IN)	33.00 A	
Max. output current	43.00 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Overland conshility		

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications	
Power factor λ	0.70 0.85
Offset factor $\cos \phi$	0.96
Efficiency η	0.98
Sound pressure level (1m)	67 dB
Power loss 3)	0.438 kW
Filter class (integrated)	RFI suppression filter for Category C2
EMC category (with accessories)	Category C2
Safety function "Safe Torque Off"	without
Communication	

Communication

PROFIBUS DP

Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

Item no. :

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YE28-0AP0

Ambient conditions		
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.018 m³/s (0.653 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 $^\circ C$ (104 $^\circ F), condensation and icing not permissible$	
Connections		
Signal cable		
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)	
Line side		
Version	screw-type terminal	
Conductor cross-section	1.50 16.00 mm² (AWG 16 AWG 6)	
Motor end		
Version	Screw-type terminals	
Conductor cross-section	1.50 16.00 mm² (AWG 16 AWG 6)	
DC link (for braking resistor)		
PE connection	On housing with M4 screw	
Max. motor cable length		
Shielded	150 m (492.13 ft)	

Mechanical data		
Degree of protection	IP20 / UL open	type
Frame size	FSC	
Net weight	7.66 kg (16.89	9 lb)
Dimensions		
Width	140 mm (5.51	in)
Height	295 mm (11.6	1 in)
Depth	218 mm (8.58	in)
	Standards	
Compliance with standards	UL, cUL, CE, C- SEMI F47, REA	Tick (RCM), EAC, KCC, CH
CE marking		2004/108/EC, Low- ive 2006/95/EC
Converter lo	osses to IEC61800-	9-2*
Efficiency class	IE2	
Comparison with the reference converter (90% / 100%)	39.1 %	
■ 279.0 W (1.3 %)	338.0 W (1.5 %)	438.0 W (2.0 %)
174.0 W (0.8 %)	195.0 W (0.9 %)	227.0 W (1.0 %)
138.0 W (0.6 %)	147.0 W (0.7 %)	\
25% •	•	

The percentage values show the losses in relation to the rated apparent power of the converter.

50%

90% **f**

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YE28-0AP0

Operator panel: Basic Operator Panel (BOP-2)

Screen		
LCD, monochrome		
Mechanical data		
IP55 / UL type 12		
0.140 kg (0.31 lb)		
70.00 mm (2.76 in)		
106.85 mm (4.21 in)		
19.60 mm (0.77 in)		

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during	I	
Max. operation	95 %	
	A	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	