






















PJMA-series



Feature

4kV isolation

Economical design

Suitable for BF application (Output-FG : 1MOPP, Input-Output : 2MOPP)

Wide temperature range (-20°C to +70°C, Derating is required) Harmonic attenuator (Complies with IEC61000-3-2 class A) Universal input (AC85 - 264V, Derating is required) Low power consumption at no load

Safety agency approvals

ANSI/AAMI ES60601-1, EN60601-1 3rd

5-year warranty (See Instruction Manual)

CE marking

Low Voltage Directive RoHS Directive

EMI

Complies with FCC-B, CISPR32-B, EN55011-B, EN55032-B, VCCI-B

(PJMA1500F: Class A. In conducted noise, it can meet class B by additional EMI/EMC filter.)

EMS Compliance : EN61204-3, EN61000-6-2

IEC60601-1-2 (2014), IEC60601-1-2 (2015)

EN61000-4-2

EN61000-4-3

EN61000-4-4

EN61000-4-5

EN61000-4-6

EN61000-4-8

EN61000-4-11

PJMA300F

PJM

300





Example recommended EMI/EMC filter NAC-06-472



High voltage pulse noise type : NAP series Low leakage current type : NAM series

*A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply.

- ①Series name
 ②Single output
 ③Output wattage
 ④Universal input
 ⑤Output voltage
 ⑥Optional *6
 C: with Coating
 G: Low leakage current
 V: External potentiometer for output voltage adjustment
 R: Remote on/off
 《Required external power source
- (Required external power source) F4: Low speed fan

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL		PJMA300F-12	PJMA300F-24	PJMA300F-36	PJMA300F-48					
	VOLTAGE[V]		AC85 - 264 1 φ (Output dera	ting is required at AC85V - 10	0V. Refer to "Derating" and ins	truction manual 1.1)					
		ACIN 100V	/ 3.9typ (lo=100%)								
	CURRENT[A] ACIN		V 3.3typ (Io=100%)								
		ACIN 230V	1.7typ (lo=100%)								
	FREQUENCY[Hz]		50 / 60 (47 - 63)								
		ACIN 100V	79typ (lo=100%)	82typ (Io=100%)	83typ (Io=100%)	82typ (lo=100%)					
	EFFICIENCY[%]	ACIN 115V	80typ (lo=100%)	83typ (lo=100%)	83typ (lo=100%)	83typ (lo=100%)					
INPUT		ACIN 230V	82typ (lo=100%)	86typ (Io=100%)	87typ (lo=100%)	86typ (lo=100%)					
		ACIN 100V	0.99typ (lo=100%)								
	POWER FACTOR	ACIN 115V	0.98typ (lo=100%)								
		ACIN 230V	0.95typ (lo=100%)								
		ACIN 100V	20typ (Io=100%) TA=25°C at	cold start							
	INRUSH CURRENT[A]	ACIN 115V	20typ (Io=100%) TA=25°C at	cold start							
		ACIN 230V	40typ (lo=100%) TA=25℃ at cold start								
	LEAKAGE CURRENT	[mA]	0.3max (ACIN 240V, 60Hz, Id	o=100%)							
	VOLTAGE[V]		12	24	36	48					
	CURRENT[A]	ACIN 85-100V	Output derating is required a	t ACIN 100V or less (Refer to	"Derating")						
	CURRENT[A]	ACIN 100V-264V	25	12.5	8.4	6.3					
	WATTACEIMI	ACIN 85-100V	Output derating is required a	t ACIN 100V or less (Refer to	"Derating")						
	WATTAGE[W]	ACIN 100V-264V	300	300	302.4	302.4					
	LINE REGULATION[r	nV] *3	48max	96max	144max	192max					
	LOAD REGULATION	[mV] *3	100max	150max	150max	300max					
	RIPPLE[mVp-p] *1 RIPPLE NOISE[mVp-p] *1 TEMPERATURE REGULATION[mV]	0 to +50°C	120max	120max	150max	150max					
OUTPUT		-10 to 0°C	160max	160max	160max	400max					
DOIPUI		0 to +50°C	150max	150max	200max	200max					
		-10 to 0℃	180max	180max	240max	500max					
		0 to +50°C	120max	240max	360max	480max					
		-10 to +50°C	180max	290max	440max	600max					
	DRIFT[mV]	*2	48max	96max	144max	192max					
	START-UP TIME[ms]		300typ (ACIN 100V, Io=100%)								
	HOLD-UP TIME[ms]		20typ (ACIN 100V, Io=100%)								
	OUTPUT VOLTAGE ADJUSTME	NT RANGE[V]	10.80 to 13.20	21.60 to 26.40	32.40 to 39.60	43.20 to 52.80					
	OUTPUT VOLTAGE SET	TING[V]	12.00 to 12.48	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92					
	OVERCURRENT PROTI		Works over 105% of rating ar	nd recovers automatically							
PROTECTION	OVERVOLTAGE PROTE	CTION[V]		27.60 to 33.60	41.40 to 50.40	55.20 to 67.20					
CIRCUIT AND	OPERATING INDICAT	TION	LED (Green)								
OTHERS	REMOTE SENSING		Not provided								
	REMOTE ON/OFF		Optional (Required external power source. Option -R)								
	INPUT-OUTPUT • RC	*9									
ISOLATION	INPUT-FG		AC2,000V 1minute, Cutoff=20mA, 1MOPP DC500V 50M Ω min (At room temperature)								
	OUTPUT • RC-FG	*9		0mA, 1MOPP DC500V 50M							
	OUTPUT-RC	*9	AC500V 1minute, Cutoff=20mA, DC500V 50MΩmin (At room temperature)								
	OPERATING TEMP.,HUMID.AND		(), (), (), ()								
ENVIRONMENT	STORAGE TEMP., HUMID. AN	DALTITUDE	-20 to +75℃, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max								
	VIBRATION			ninutes period, 60 minutes eac	ch along X, Y and Z axes						
	IMPACT		196.1m/s² (20G), 11ms, once								
SAFETY AND	AGENCY APPROVAL	.s	ANSI/AAMI ES60601-1, EN6								
NOISE	CONDUCTED NOISE			B, CISPR22-B, EN55011-B, E	N55022-B						
REGULATIONS	HARMONIC ATTENU	ATOR *8	Complies with IEC61000-3-2 class A								






OTHERS	CASE SIZE/WEIGHT		02×41×190mm [4.02×1.61×7.48 inches] (Excluding terminal block and screw) (W×H×D) / 1.0kg max				
	COOLING METHOD	*7	Forced cooling (internal fan)				
WARRANTY	WARRANTY WARRANTY *5 5 yea		5 years (subject to the operating conditions)				

- *1 This is the result of measurement of the testing board with capacitors of 22 µF and 0.1 µF placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku Giken R104 See 1.6 of Instruction Manual for more details.
- Drift is the change in DC output for an eight hour period after a half-hour warm-up at $25\,^{\circ}\mathrm{C}$.
- Consult us about dynamic load and input response
- Output power derating is required. Refer to "Derating". See 4 in Instruction Manual for more details
- Consult us about safety agency approvals for the models with optional functions.
- The fan speed slows down at no load. Consult us about other classes
- *9 The RC terminal is added to option -R models. The RC terminal is
- isolated from input, output, and FG.
- Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged
 - Parallel operation is not possible with this mode.
- Sound noise may be heard from the power supply when used for pulse load.

Features


- · 4kV isolation
- · Economical design
- · Suitable for BF application (Output-FG: 1MOPP, Input-Output: 2MOPP)
- · Wide temperature range (-20°C to +70°C, Refer to "Derating")
- · Harmonic attenuator (Complies with IEC61000-3-2 class A)
- · Universal input (AC85 264V, Refer to "Derating")
- · Low power consumption at no load

Block diagram



External view

The external size of -V option and -R option models is different from the standard model. See "5. Options and Others" in Instruction Manual for more details.



Ordering information

PJMA600F

600 **PJM**



Example recommended EMI/EMC filter NAC-16-472



High voltage pulse noise type : NAP series Low leakage current type : NAM series

*A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply.

- ①Series name
 ②Single output
 ③Output wattage
 ④Universal input
 ⑤Output voltage
 ⑥Optional *6
 C: with Coating
 G: Low leakage current
 V: External potentiometer for output voltage adjustment
 WI: LV alarm and Remote sensing
 R: Remote on/off

 - R : Remote on/off (Required external power source) F4: Low speed fan

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL		PJMA600F-12	PJMA600F-24	PJMA600F-36	PJMA600F-48				
	VOLTAGE[V]		AC85 - 264 1 φ (Output dera	ting is required at AC85V - 100	V. Refer to "Derating" and instr	uction manual 1.1)				
		ACIN 100V	7 7.5typ (lo=100%)							
	CURRENT[A]	ACIN 115V	6.5typ (lo=100%)							
	ACIN 230V		3.2typ (lo=100%)							
	FREQUENCY[Hz]		50 / 60 (47 - 63)							
		ACIN 100V	81typ (lo=100%)	84typ (Io=100%)	85typ (Io=100%)	85typ (Io=100%)				
	EFFICIENCY[%]	ACIN 115V	82typ (lo=100%)	85typ (lo=100%)	86typ (Io=100%)	85typ (lo=100%)				
INPUT		ACIN 230V	84typ (lo=100%)	88typ (lo=100%)	88typ (Io=100%)	88typ (Io=100%)				
		ACIN 100V	0.99typ (lo=100%)			, , , ,				
	POWER FACTOR	ACIN 115V	0.98typ (lo=100%)							
		ACIN 230V	0.95typ (lo=100%)							
		ACIN 100V	20/40typ (Io=100%) (Primary	inrush current /Secondary inru	ush current) (More than 3sec t	o re-start)				
	INRUSH CURRENT[A]	ACIN 115V	20/40typ (Io=100%) (Primary	inrush current /Secondary inru	ush current) (More than 3sec t	o re-start)				
		ACIN 230V	40/40typ (Io=100%) (Primary	40/40typ (lo=100%) (Primary inrush current /Secondary inrush current) (More than 3sec to re-start)						
	LEAKAGE CURRENT	[mA]	0.3max (ACIN 240V,60Hz,Io=	=100%)		· · · · · · · · · · · · · · · · · · ·				
	VOLTAGE[V]		12	24	36	48				
		ACIN 85-100V	Output derating is required at	t ACIN 100V or less (Refer to "	Derating")					
	CURRENT[A]	ACIN 100V-264V	50	25	16.7	12.5				
		ACIN 85-100V	Output derating is required at	t ACIN 100V or less (Refer to "	Derating")	•				
	WATTAGE[W]	ACIN 100V-264V	600	600	601.2	600				
	LINE REGULATION[r	nV] *7	48max	96max	144max	192max				
	LOAD REGULATION	[mV] *7	100max	150max	150max	300max				
	RIPPLE[mVp-p]	0 to +50°C	120max	120max	150max	150max				
	*1	-20 to 0°C	160max	160max	160max	400max				
OUTPUT	RIPPLE NOISE[mVp-p]	0 to +50°C	150max	150max	200max	200max				
	*1	-20 to 0°C	180max	180max	240max	500max				
	TEMPERATURE REQUILATIONS AND	0 to +50°C	120max	240max	360max	480max				
	TEMPERATURE REGULATION[mV]	-20 to +50°C	180max	290max	440max	600max				
	DRIFT[mV] *2		48max	96max	144max	192max				
	START-UP TIME[ms]		300typ (ACIN 100V, Io=100%)							
	HOLD-UP TIME[ms]		20typ (ACIN 100V, Io=100%)							
	OUTPUT VOLTAGE ADJUSTME	NT RANGE[V]	10.80 to 13.20	21.60 to 26.40	32.40 to 39.60	43.20 to 52.80				
	OUTPUT VOLTAGE SET	TING[V]	12.00 to 12.48	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92				
	OVERCURRENT PROT	ECTION	Works over 105% of rating ar	nd recovers automatically						
PROTECTION	OVERVOLTAGE PROTE	CTION[V]	13.80 to 16.80	27.60 to 33.60	41.40 to 50.40	55.20 to 67.20				
CIRCUIT AND	OPERATING INDICA	TION	LED (Green)							
OTHERS	REMOTE SENSING		Optional (Option -W1)							
	REMOTE ON/OFF		Optional (Required external power source. Option -R)							
	INPUT-OUTPUT • RC	*3	AC4,000V 1minute, Cutoff=20mA, 2MOPP DC500V 50MΩmin (At room temperature)							
SOLATION	INPUT-FG		AC2,000V 1minute, Cutoff=20mA, 1MOPP DC500V 50M Ω min (At room temperature)							
ISOLATION	OUTPUT • RC-FG	*3	AC1,500V 1minute, Cutoff=20mA, 1MOPP DC500V 50M Ω min (At room temperature)							
	OUTPUT-RC	*3								
	OPERATING TEMP.,HUMID.AND	ALTITUDE *4								
ENVIRONMENT	STORAGE TEMP.,HUMID.AN	D ALTITUDE	(3), ()							
EINNINONNEN I	VIBRATION		10 - 55Hz, 19.6m/s² (2G), 3m	ninutes period, 60minutes each	along X, Y and Z axes					
	IMPACT		196.1m/s² (20G), 11ms, once	e each X, Y and Z axes						
SAFETY AND	AGENCY APPROVAL	.s	ANSI/AAMI ES60601-1, EN6	0601-1 3rd						
NOISE	CONDUCTED NOISE		Complies with FCC-B, VCCI-	B, CISPR32-B, EN55011-B, E	N55032-B					
REGULATIONS	HARMONIC ATTENU	ATOR *9	Complies with IEC61000-3-2	class A						

PJMA-4 March 15, 2023





OTHERS	CASE SIZE/WEIGHT	120×61×215mm [4.72×2.40×8.46 inches] (Excluding terminal block and screw) (W×H×D) / 2.0kg max
	COOLING METHOD *8	Forced cooling (internal fan)
WARRANTY	WARRANTY *5	5 years (subject to the operating conditions)


- This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM104
- See 1.6 of Instruction Manual for more details. Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25 °C.
- The BC terminal is added to option -R models. The BC terminal is
- isolated from input, output, and FG. Output power derating is required. Refer to "Derating"
- See 3 in Instruction Manual for more details
- Consult us about safety agency approvals for the models with optional functions.
- Consult us about dynamic load and input response.
- *8 The fan speed slows down at no load.

- Consult us about other classes
- Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.
- Sound noise may be heard from the power supply when used for pulse load.

Features


- · 4kV isolation
- · Economical design
- · Suitable for BF application (Output-FG: 1MOPP, Input-Output: 2MOPP)
- · Wide temperature range (-20°C to +70°C, Refer to "Derating")
- · Harmonic attenuator (Complies with IEC61000-3-2 class A)
- · Universal input (AC85 264V, Refer to "Derating")
- · Low power consumption at no load

Block diagram



External view

The external size of -V option, -W1 option and -R option models is different from the standard model. See "5. Options and Others" in Instruction Manual for more details.



Ordering information

PJMA1000F

1000 **PJM**





High voltage pulse noise type : NAP series Low leakage current type : NAM series

- ①Series name ②Single output ③Output wattage ④Universal input ⑤Output voltage ⑥Optional *8
 - C: with Coating
 - G: Low leakage current
- V : External potentiometer for output voltage adjustment
- W: Parallel operation, LV alarm and Remote sensing W1: LV alarm and Remote sensing
- R: Remote on/off (Required external power
- source) F4: Low speed fan

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL		PJMA1000F-12	PJMA1000F-24	PJMA1000F-36	PJMA1000F-48					
	VOLTAGE[V]		AC85 - 264 1 φ (Output dera	ting is required at AC85V - 11	5V. Refer to "Derating" and	d instruction manual 1.1)					
		ACIN 100V	/ 12.5typ (Io=90%)								
	CURRENT[A]		/ 11.0typ (lo=100%)								
			/ 5.5typ (Io=100%)								
	FREQUENCY[Hz]		50 / 60 (47 - 63)								
		ACIN 100V	81typ (Io=90%)	84typ (Io=90%)	84typ (lo=90%)	84typ (Io=90%)					
	EFFICIENCY[%]		82typ (Io=100%)	85typ (lo=100%)	85typ (Io=100%)	85typ (Io=100%)					
INPUT			85typ (Io=100%)	88typ (Io=100%)	88typ (Io=100%)	88typ (Io=100%)					
		_	0.98typ (Io=90%)	00typ (10=10070)	Cotyp (IO=10070)	COLYP (10=10070)					
	POWER FACTOR		0.98typ (10=90%)								
	T OWENT ACTON		0.95typ (Io=100%)								
			15/30typ (Io=90%) (Primary i	nrush current /Secondary inr	ich current) (More than 10	Deac to re-start)					
	INRUSH CURRENT[A]		71 \ 7 \ 7								
	INNOSTI CONNENT[A]	ACIN 115V	71 7 7 7	15/30typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start) 30/30typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start)							
	LEAVACE CURRENT	1	0.3max (ACIN 240V, 60Hz, Ic		rusii current) (More than	10sec to re-start)					
	VOLTAGE[V]	[IIIA]	12	24	36	48					
	VOLTAGE[V]	ACINI OF 11FV	· -	1=:		40					
	CURRENT[A]	ACIN 85-115V ACIN 115V-264V	Output derating is required at	, , , , , , , , , , , , , , , , , , , ,		01					
				84 42 28 21 Output derating is required at ACIN 115V or less (Refer to "Derating")							
	WATTAGE[W]	ACIN 85-115V ACIN 115V-264V	1008	1008	"Derating")	1008					
	LINE DECLI ATION										
	LINE REGULATION[r		48max	96max	144max	192max					
	LOAD REGULATION		100max	150max	150max	300max					
	RIPPLE[mVp-p]	0 to +50℃		120max	150max	200max					
DUTPUT	*1	+	240max	160max	200max	500max					
	RIPPLE NOISE[mVp-p] *1	0 to +50°C	210max	150max	200max	300max					
		-20 to 0℃	270max	180max	240max	600max					
	TEMPERATURE	0 to +50℃	120max	240max	360max	480max					
	REGULATION[mV]	-20 to +50°C	180max	290max	440max	600max					
	DRIFT[mV]	*3	48max	96max	144max	192max					
	START-UP TIME[ms]		800typ (ACIN 115V, Io=100%)								
	HOLD-UP TIME[ms]		20typ (ACIN 115V, Io=100%)								
	OUTPUT VOLTAGE ADJUSTME	NT RANGE[V]	10.80 to 13.50	20.40 to 28.50	30.60 to 40.80	40.80 to 55.20					
	OUTPUT VOLTAGE SET	TING[V]	12.00 to 12.48	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92					
	OVERCURRENT PROT	ECTION	Works over 105% of rating ar	nd recovers automatically							
PROTECTION	OVERVOLTAGE PROTE	CTION[V]	14.40 to 17.40	28.80 to 34.80	43.20 to 52.20	57.00 to 67.20					
CIRCUIT AND	OPERATING INDICA	TION	LED (Green)								
THERS	REMOTE SENSING		Optional (Option -W, -W1)								
	REMOTE ON/OFF	-	Optional (Required external power source. Option -R)								
	INPUT-OUTPUT		AC4,000V 1minute, Cutoff=20mA, 2MOPP DC500V 50MΩ min (At room temperature)								
	INPUT-FG		AC2,000V 1minute, Cutoff=20mA, 1MOPP DC500V 50M Ω min (At room temperature)								
SOLATION	OUTPUT • RC-FG	*3	AC1,500V 1minute, Cutoff=20								
	OUTPUT-RC		AC500V 1minute, Cutoff=20mA, DC500V 50M Ω min (At room temperature)								
	OPERATING TEMP.,HUMID.AND	ALTITUDE *4									
	STORAGE TEMP.,HUMID.AN		-20 to +75°C, 20 - 90%RH (N	• /-	• • • • • • • • • • • • • • • • • • • •	,					
ENVIRONMENT	VIBRATION		10 - 55Hz, 19.6m/s² (2G), 3m								
	IMPACT		196.1m/s² (20G), 11ms, once		a.og //, r and 2 a/co						
SAFETY AND	AGENCY APPROVAL	S	ANSI/AAMI ES60601-1, EN6								
					-NICEOOO A						
NOISE	CONDUCTED NOISE		Complies with FCC-A, VCCI-A, CISPR32-A, EN55011-A, EN55032-A Complies with IEC61000-3-2 class A								

PJMA-6 March 15, 2023



OTHERS	CASE SIZE/WEIGHT	150×61×240mm [5.91×2.40×9.45 inches] (Excluding terminal block and screw) (W×H×D) / 2.8kg max
OTHERS	COOLING METHOD	*6 Forced cooling (internal fan)
WARRANTY	WARRANTY	*7 5 years (subject to the operating conditions)

Drift is the change in DC output for an eight hour period after a half-hour

This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM104 See 1.6 of Instruction Manual for more details.

Consult us about dynamic load and input response

- warm-up at 25℃ Output power derating is required. Refer to "Derating".
- Consult us about safety agency approvals for the models with optional functions.


- - Consult us about other classes
- Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.
 - The fan speed slows down or stops at no load.
 - See 3 in Instruction Manual for more details.
- Parallel operation is not possible with this mode. Audible noise may be heard from the power supply when used for pulse load.




Features

- · 4kV isolation
- · Economical design
- · Suitable for BF application (Output-FG: 1MOPP, Input-Output: 2MOPP)
- · Wide temperature range (-20°C to +70°C, Refer to "Derating")
- · Harmonic attenuator (Complies with IEC61000-3-2 class A)
- · Universal input (AC85 264V, Refer to "Derating")
- · Low power consumption at no load

Block diagram




External view



Ordering information

PJMA1500F

1500 **PJM**





High voltage pulse noise type : NAP series Low leakage current type : NAM series

- ①Series name ②Single output ③Output wattage ④Universal input ⑤Output voltage ⑥Optional *8
 - C: with Coating
 - G: Low leakage current
 - V : External potentiometer for output voltage adjustment
- W: Parallel operation, LV alarm and Remote sensing (Except 48V)
- W1: LV alarm and Remote sensing
- R: Remote on/off (Required external power source)
- F4: Low speed fan

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL		PJMA1500F-12	PJMA1500F-24	PJMA1500F-36	PJMA1500F-48					
	VOLTAGE[V]		AC85 - 264 1 φ (Output derating is required at AC85V - 115V. Refer to "Derating" and instruction manual 1.1)								
		ACIN 100V	18typ (Io=90%)								
	CURRENT[A]	ACIN 115V	16typ (lo=100%)								
		ACIN 230V	8typ (lo=100%)								
	FREQUENCY[Hz]		50 / 60 (47 - 63)								
			81typ (Io=90%)	84typ (Io=90%)	84typ (Io=90%)	84typ (lo=90%)					
	EFFICIENCY[%]		82typ (Io=100%)	85typ (Io=100%)	85typ (Io=100%)	84typ (Io=100%)					
NPUT			85typ (Io=100%)	88typ (Io=100%)	88typ (Io=100%)	87typ (Io=100%)					
0.			0.98typ (Io=90%)	cotyp (i.e. 1007s)	cotyp (i.e. 1007s)	o r typ (10 100 / 0)					
	POWER FACTOR		9.98typ (Io=30%)								
	T OWENT ACTON		0.95typ (Io=100%)								
			71 \ /	inrush current /Secondary inrus	sh current) (More than 10sec t	o re-ctart)					
	INRUSH CURRENT[A]		**	r inrush current /Secondary inru							
	INNUSTI CONNENT[A]	ACIN 113V	71 \ /\ /	inrush current /Secondary inru							
	LEAKAGE CURRENT				distribution (More than Tosec	to re-start)					
	LEAKAGE CURRENT	[mA]	0.3max (ACIN 240V, 60Hz, Id		100	40					
	VOLTAGE[V]	ACIN OF 115V		24	36	48					
_	CURRENT[A]	ACIN 85-115V		t ACIN 115V or less (Refer to "		00					
		ACIN 115V-264V	125	64	42	32					
	WATTAGE[W]	ACIN 85-115V		t ACIN 115V or less (Refer to "		1					
		ACIN 115V-264V	1500	1536	1512	1536					
	LINE REGULATION[n		48max	96max	144max	192max					
	LOAD REGULATION		100max	150max	150max	300max					
	RIPPLE[mVp-p]	0 to +50°C		120max	150max	200max					
UTPUT	*1	-20 to 0°C		160max	200max	500max					
011 01	RIPPLE NOISE[mVp-p]		210max	150max	200max	300max					
	*1			270max	240max	600max					
	TEMPERATURE REGULATION[mV]	0 to +50°C	120max	240max	360max	480max					
	TEMPERATORE REGULATION[IIIV]	-20 to +50°C	180max	290max	440max	600max					
	DRIFT[mV]	*3	48max	96max	144max	192max					
	START-UP TIME[ms]		800typ (ACIN 115V, Io=100%)								
	HOLD-UP TIME[ms]		20typ (ACIN 115V, Io=100%)								
	OUTPUT VOLTAGE ADJUSTMEN	NT RANGE[V]	10.80 to 13.50	20.40 to 28.50	30.60 to 40.80	40.80 to 55.20					
	OUTPUT VOLTAGE SE	TTING[V]	12.00 to 12.48	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92					
	OVERCURRENT PROTE	ECTION	Works over 105% of rating ar	nd recovers automatically							
ROTECTION	OVERVOLTAGE PROTE	CTION[V]	14.40 to 17.40	28.80 to 34.80	43.20 to 52.20	57.00 to 67.20					
IRCUIT AND	OPERATING INDICAT	TION	LED (Green)								
THERS	REMOTE SENSING		Optional (Option -W, -W1)								
	REMOTE ON/OFF		Optional (Required external power source. Option -R)								
	INPUT-OUTPUT		AC4,000V 1minute, Cutoff=20mA, 2MOPP DC500V 50MΩ min (At room temperature)								
	INPUT-FG		AC2,000V 1minute, Cutoff=20mA, 1MOPP DC500V 50MΩ min (At room temperature)								
SOLATION	OUTPUT • RC-FG	*3									
	OUTPUT-RC		AC500V 1minute, Cutoff=20mA, DC500V 50M Ω min (At room temperature)								
	OPERATING TEMP.,HUMID.AND	ALTITUDE *4		ing"), 20 - 90%RH (Non conde		iax					
	STORAGE TEMP.,HUMID.ANI		,	lon condensing), 9,000m (30,0							
NVIRONMENT	VIBRATION			ninutes period, 60minutes each							
	IMPACT		196.1m/s² (20G), 11ms, once		g, = a						
AFETY AND	AGENCY APPROVAL	.s	ANSI/AAMI ES60601-1, EN	<u> </u>							
OISE	CONDUCTED NOISE			A, CISPR32-A, EN55011-A, E	N55032-A						
EGULATIONS	HARMONIC ATTENU	ATOR *	Complies with IEC61000-3-2	· · · · · · · · · · · · · · · · · · ·	1100002 /1						
		- 1 O 11 **3	Compiles with 1200 1000-3-2	JIGOS FI							





OTHERS	CASE SIZE/WEIGHT	178×61×268mm [7.01×2.40×10.55 inches] (Excluding terminal block and screw) (W×H×D) / 3.5kg max
OTHERS	COOLING METHOD	*6 Forced cooling (internal fan)
WARRANTY	WARRANTY	*7 5 years (subject to the operating conditions)

This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103 See 1.6 of Instruction Manual for more details.


Consult us about dynamic load and input response

- warm-up at 25℃.
- Drift is the change in DC output for an eight hour period after a half-hour *8 Consult us about safety agency approvals for the models with optional functions. Do not use the power supply in overcurrent conditions or in unspecified
- Output power derating is required. Refer to "Derating".
- Consult us about other classes
- The fan speed slows down or stops at no load. See 3 in Instruction Manual for more details.
- input voltage ranges. Otherwise the internal components may be damaged. Parallel operation is not possible with this mode.
- Audible noise may be heard from the power supply when used for pulse load.


Features

- · 4kV isolation
- · Economical design
- · Suitable for BF application (Output-FG: 1MOPP, Input-Output: 2MOPP)
- · Wide temperature range (-20°C to +70°C, Refer to "Derating")
- · Harmonic attenuator (Complies with IEC61000-3-2 class A)
- · Universal input (AC85 264V, Refer to "Derating")
- · Low power consumption at no load

Block diagram




External view




COSEL | PJMA-series


Assembling and Installation Method


■Do not insert a screw more than 6mm from the outside of a power supply to keep enough insulation distance between the screw and internal components.




PJMA300F













●PJMA600F








●PJMA1000F, PJMA1500F





	PJMA1000F	PJMA1500F
а	More than 30mm	More than 50mm


Assembling and Installation Method

- ■When mounting the power supply with screws, it is recommended that this be done as shown above. If other methods are used, be sure the weight of the power supply is taken into account.
- ■Avoid the not allowed installation method as it gives excessive stress to the mounting holes.
- ■Do not block air flow of the built-in fan (terminal block and ventilation hole).
- ■If the power supply is used in a dusty environment, use an airfilter. Make sure air flow is not blocked.
- ■If the built-in fan stops, thermal protection will work and the output will stop.
- ■The life expectancy (R(t)=90%) of the built-in fan varies depending on the operating condition.




Derating

Input voltage Derating Curve



Ambient temperature Derating Curve



- ■In the hatched area, the specification of Ripple, Ripple Noise is different from other area.
- ■The ambient temperature is defined as the temperature of the air (at the terminal block side) that the built-in cooling fan blows into the power supply. Please pay attention to the heat generated by the input and output wires. Please consult us for more details.

Instruction Manual

♦It is neccessary to read the "Instruction Manual" and "Before using our product" before you use our product.

Instruction Manual https://en.cosel.co.jp/product/powersupply/PJMA/ Before using our product https://en.cosel.co.jp/technical/caution/index.html





Basic Characteristics Data

Model	Circuit method	Switching frequency [kHz]	Input current [A]	Rated input fuse	Inrush current	PCB/	'Patterr	Series/Parallel operation availability		
Model	Circuit method				protection circuit	Material	Single sided	Double sided	Series operation	Parallel operation
PJMA300F	Active filler	60	20 *1	250V 10A	TI	ED 4	R-4	V	Yes	No
PJIVIASUUF	Forward converter	140	3.9 *1	250V TUA	Thermistor	Γ Π- 4		res		INO
D IMAGOOF	Active filler	60	7.5 *1	050)/104	SCR	FR-4 Ye FR-4 Ye		Vaa	Vac	No
PJMA600F	Forward converter	220		250V 16A	SUN		res	Yes	No	
D IMA1000E	Active filter	65	12.5 *2	250V 20A	TRIAC	FR-4		Voc	Yes	*3
PJMA1000F	Forward converter	210	12.5 *2	250V 20A				res	ies	~ 3
PJMA1500F	Active filter	65	18.0 *1	250V 30A	TRIAC	- FD 4		\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	Yes	* 4
	Forward converter	210	10.0 🛧 1	250 V 30A	INIAC	FR-4		Yes	res	~ 4

- *1 The input current shown is at ACIN 100V and 100% load.
- *2 The input current shown is at ACIN 100V and 90% load.
- *3 Parallal operation is possible with -W option. see "5. Option and Other" is Instruction Manual.
- *4 Parallal operation is possible with -W option. (Except 48V) see "5. Option and Other" is Instruction Manual.