




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G2		REMOVED SEMKO LOGO	ECN-21-117018	13-SEP-21	G-R K-T
G2		OBSOLETE THE DRAWING	ECN-22-177091	12-Oct-22	WQ.Y K.T

- NOTE:
- 1.TERMINAL DIMENSIONS WITHOUT TINNING.
 - 2.LOT NO. SYSTEM AS FOLLOWING:

 - 3.FOR THE TIN-PLATING OF THE PINS:
 +0.1mm FOR WIDTH, THICKNESS AND DIAMETER
 +0.5mm FOR LENGTH





CONNECTION DIAGRAM(BOTTM VIEW)




OBSOLETE

DRILLING DIAGRAM(BOTTM VIEW)



TOLERANCE

Diagram dimension	Tolerance
max. 1mm	±0.1mm
1 - 3mm	±0.2mm
min. 3mm	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.SASAKI	 TE Connectivity Ltd.		
DIMENSIONS: mm		CHK Y.OIKAWA			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.NAGAI	PRODUCT SPEC		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC	RESTRICTED TO		
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO G- 3-1419124-9
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 2	REV G2

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


OBSOLETE

①	8-1440001-4	OSA-SH-224DM5	24V	OSA-SH-224DM5	n
①	8-1440001-2	OSA-SH-212DM5	12V	OSA-SH-212DM5	m
①	8-1440001-1	OSA-SH-212DM5	12V	OSA-SH-212DM5	L
①	7-1440001-9	OSA-SH-209DM5	9V	OSA-SH-209DM5	k
①	7-1440004-7	OSA-SH-205DM5	5V	OSA-SH-205DM5	j
①	1461020-7	OSA-SH-205DM5	5V	OSA-SH-205DM5	i
	1461388-6	OSA-SH-248DM5	48V	OSA-SH-248DM5	h
	1461388-4	OSA-SH-224DM5	24V	OSA-SH-224DM5	g
	1461388-3	OSA-SH-206DM5	6V	OSA-SH-206DM5	f
	4-1419124-9	OSA-SH-224DM5	24V	OSA-SH-224DM5	e
	4-1419124-0	OSA-SH-212DM5	12V	OSA-SH-212DM5	d
	3-1419124-9	OSA-SH-212DM5	12V	OSA-SH-212DM5	c
	7-1440001-8	OSA-SH-209DM5	9V	OSA-SH-209DM5	b
	7-1440004-6	OSA-SH-205DM5	5V	OSA-SH-205DM5	a
	TE CONNECTIVITY PART NO	DESCRIPTION	PART B	PART A	ITEM

RELAY TYPE

		UV RESIN	UV SEAL	15
		EPOXY RESIN	SEAL	14
94V-0		PBT	CASE	13
94V-0		PA66	CARD	12
		Ag ALLOY	STATIONARY CONTACT	11
		Cu ALLOY	STATIONARY TERMINAL	10
		Ag ALLOY	MOVABLE CONTACT	9
		Cu ALLOY	MOVABLE SPRING	8
	Cu-Ni PLATED	STEEL	ARMATURE	7
	Cu-Ni PLATED	STEEL	CORE	6
		PBS	HINGE SPRING	5
	Ni PLATED	STEEL	YOKE	4
		UEW	MAGNETIC WIRE	3
		CP WIRE	COIL TERMINAL	2
94V-0		PBT	BOBBIN	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

NOTE: 1. LOT NO. SYSTEM AS FOLLOWING:



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-	 TE Connectivity Ltd.											
DIMENSIONS: mm		CHK	-												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-												
<table border="0"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC	± -			1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -
0 PLC	± -														
1 PLC	± -														
2 PLC	± -														
3 PLC	± -														
4 PLC	± -														
ANGLES	± -														
MATERIAL		APPLICATION SPEC	-	NAME											
FINISH		WEIGHT	-	OSA-SH-DM5,000 ,000M											
		CUSTOMER DRAWING		SIZE	A3										
				CAGE CODE	00779										
				DRAWING NO	G- 3-1419124-9										
				RESTRICTED TO	-										
				SCALE	4:1										
				SHEET	2 OF 2										
				REV	G2										