



Technical Data Sheet

PEWAN062-10NF

Features

- 12.4 GHz to 18 GHz
- · WR-62 Waveguide Band

- 10 dBi Nominal Gain
- N Female Connector

Applications

- Antenna Measurements
- Wireless Communication
- Laboratory Use

- Microwave Radio Systems
- · Radome Testing
- Automotive Antenna Test

Solutions

- · Radar Cross Section
- Satellite Antenna Testing

Description

The PEWAN062-10NF standard gain horn antenna (also known as waveguide horn) from Pasternack is part of our comprehensive selection of waveguide antennas. This standard gain horn is mated with a WR-62 to N Female waveguide to coaxial adapter and operates from 12.4 GHz to 18 GHz.

Our PEWAN062-10NF standard gain horn antenna has a nominal gain of 10 dBi with a Horizontal and Vertical HPBW (Half Power Beam Width) of 52.1 dB and 51.6 dB respectively. Pasternack's N Female to WR-62 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and connectorized input.

Waveguide antennas, such as the PEWAN062-10NF are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our WR-62 waveguide antennas with N Female interface is part of over 40,000 RF, microwave and millimeter wave components from Pasternack available worldwide and Ship same day.

Configuration

Design Coaxial Interface WR-62 Standard Gain Horn

N Female

Electrical Specifications

	Typical	Maximum	Units
12.4		18	GHz
	10		dBi
	52.1		Degrees
	51.6		Degrees
		1.4:1	
	12.4	10 52.1	10 52.1 51.6

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-62 Standard Gain Horn with 10 dBi gain, N Female connector PEWAN062-10NF

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





Technical Data Sheet

PEWAN062-10NF

Mechanical Specifications

Size

 Length
 2.575 in [65.41 mm]

 Width
 1.31 in [33.27 mm]

 Height
 1.31 in [33.27 mm]

 Weight
 0.1715 lbs [77.79 g]

RF Connector

Type N Female

Waveguide Interface

Waveguide Size WR-62

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:






Technical Data Sheet

PEWAN062-10NF

Typical Performance Data








Technical Data Sheet

PEWAN062-10NF








Technical Data Sheet

PEWAN062-10NF








Technical Data Sheet

PEWAN062-10NF



WR-62 Standard Gain Horn with 10 dBi gain, N Female connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-62 Standard Gain Horn with 10 dBi gain, N Female connector PEWAN062-10NF

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWAN062-10NF CAD DrawingWR-62 Standard Gain Horn with 10 dBi gain, N Female connector

