



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: NONE
6. "XX" REFERS TO THE NUMBER OF CIRCUITS.

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
5	XX	SCREW, 6-32 THD, WITH WASHER (OPT .50)	STEEL	CLEAR/CHROMATE
4	XX	SCREW, BINDING HD, 6-32 THD, (OPT .49)	BRASS	NICKEL
3	XX	SCREW, BINDING HD, 6-32 THD,	STEEL	CLEAR/CHROMATE
2	XX	TERMINAL	BRASS	TIN
1	1	BARRIER	THERMOPLASTIC	BLACK

EC NO. 3414	DRWN: VH 12/18/03	QUALITY SYMBOLS
CHK: [ ]	APPR: [ ]	MAJOR
REV A		CRITICAL
		SPEC

GENERAL TOLERANCES (UNLESS SPECIFIED)	
MM	INCH
1 PLACES	±.0015
3 PLACES	±.005
2 PLACES	±.01
1 PLACE	±.3
ANGULAR: ±2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

SCALE 2:1	DESIGN UNITS [ ] MM [X] INCH
DRAWN BY & DATE V. HOWARD 10-18-03	
CHECKED BY & DATE	
APPROVED BY & DATE	
CAD FILENAME 712XX-C	

PROJECT NO.	-	-
DIMENSIONS:	MM	INCH
	INCH	MM
	TIN	ONLY
REVISE ON CAD ONLY		
SHEET REV		
TITLE: SR, BTS, TT ASSY		
MOLEX INCORPORATED		
MATERIAL NO. SEE TABLE	DRAWING NO. SD-38710-001	SHEET NO. 1 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		
		SIZE B

MATERIAL NO. (OPT -C, -50)	MATERIAL NO. (OPT -C, -49)	MATERIAL NO. (OPT -C)	NUMBER OF CIRCUITS "XX"	DIM. "A"	DIM. "B"
38710-3902	38710-3602	38710-3302	02	21.1 (1.83)	9.53 (1.375)
38710-3903	38710-3603	38710-3302	03	30.7 (1.21)	19.05 (1.750)
38710-3904	38710-3604	38710-3302	04	40.1 (1.58)	28.58 (1.125)
38710-3905	38710-3605	38710-3302	05	49.8 (1.96)	38.10 (1.500)
38710-3906	38710-3606	38710-3302	06	59.2 (2.33)	47.6 (1.875)
38710-3907	38710-3607	38710-3302	07	68.8 (2.71)	57.15 (2.250)
38710-3908	38710-3608	38710-3302	08	78.3 (3.08)	66.68 (2.625)
38710-3909	38710-3609	38710-3302	09	87.8 (3.46)	76.20 (3.000)
38710-3910	38710-3610	38710-3302	10	97.3 (3.83)	85.71 (3.375)
38710-3911	38710-3611	38710-3302	11	106.9 (4.21)	95.25 (3.750)
38710-3912	38710-3612	38710-3302	12	116.3 (4.58)	104.78 (4.125)
38710-3913	38710-3613	38710-3302	13	126.0 (4.96)	114.30 (4.500)
38710-3914	38710-3614	38710-3302	14	135.3 (5.33)	123.83 (4.875)
38710-3915	38710-3615	38710-3302	15	145.0 (5.71)	133.35 (5.250)
38710-3916	38710-3616	38710-3302	16	154.4 (6.08)	142.88 (5.625)
38710-3917	38710-3617	38710-3302	17	164.1 (6.46)	152.40 (6.000)
38710-3918	38710-3618	38710-3302	18	173.5 (6.83)	161.93 (6.375)
38710-3919	38710-3619	38710-3302	19	183.1 (7.21)	171.45 (6.750)
38710-3920	38710-3620	38710-3302	20	192.5 (7.58)	180.98 (7.125)
38710-3921	38710-3621	38710-3302	21	202.2 (7.96)	190.50 (7.500)
38710-3922	38710-3622	38710-3302	22	211.6 (8.33)	200.03 (7.875)
38710-3923	38710-3623	38710-3302	23	221.2 (8.71)	209.55 (8.250)
38710-3924	38710-3624	38710-3302	24	230.6 (9.08)	219.08 (8.625)
38710-3925	38710-3625	38710-3302	25	240.3 (9.46)	228.60 (9.000)
38710-3926	38710-3626	38710-3302	26	249.6 (9.83)	238.13 (9.375)

EC NO. SEE SHT) DRAWN: CH'K: APPR: A	DESCRIPTION MAJOR CRITICAL SPC S	GENERAL TOLERANCES (UNLESS SPECIFIED)	SCALE N/A	DESIG. UNITS <input type="checkbox"/> MM <input checked="" type="checkbox"/> INCH	THIRD ANGLE PROJECTION	DIMENSIONS: <input checked="" type="checkbox"/> MM <input type="checkbox"/> INCH <input type="checkbox"/> MIN ONLY	PROJECT NO.: - -	SHT REV
		4 PLACES ±.038 ±.0015 3 PLACES ±.038 ±.005 2 PLACES ±.13 ±.01 1 PLACE ±.3	DRAWN BY & DATE W. HOWARD 12-18-03	TITLE: SR, BTS, TT ASSY			REVISE ON CAD ONLY	
		ANGULAR: ±2°	CHECKED BY & DATE	MOLEX INCORPORATED				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	APPROVED BY & DATE	CAD FILENAME 712XX-C	MATERIAL NO. SEE TABLE	DRAWING NO. SD-38710-001	SHEET NO. 2 OF 2	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.						SIZE B		