



enetSEAL+ | DEUTSCH Common Contact

TE Internal #: 1062-20-0322

Automotive Terminals, Socket, Pin Diameter 1.02 mm [.04 in], 22 – 16 AWG Wire Size, .35 – 1.5 mm<sup>2</sup> Wire Size, DEUTSCH Common Contact

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals



Terminal Type: **Socket**

Mating Pin Diameter: 1.02 mm [.04 in]

Terminal Transmits: 0 – 24 A (Low Power)

Wire Size: .35 – 1.5 mm<sup>2</sup>

**Features**

**Product Type Features**

Sealable	No
Primary Locking Feature	On the Terminal

**Contact Features**

Contact Size	Size 20
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Nickel
Typical Current Rating	7.5 A
Crimp Type	F-Crimp
Terminal Type	Socket
Mating Pin Diameter	1.02 mm [.04 in]
Interface Plating	Nickel (Ni)

**Termination Features**

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

**Dimensions**

Compatible Insulation Diameter Range	1.91 – 3.18 mm [.075 – .125 in]
Wire Size	.35 – 1.5 mm <sup>2</sup>
Wire Size Search	15 AWG, 16 AWG, 18 AWG, 20 AWG, 22 AWG



**Usage Conditions**

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]

**Operation/Application**

Compatible With Wire Base Material	Copper
------------------------------------	--------

**Packaging Features**

Packaging Quantity	4000
Packaging Method	Reel

**Other**

Customer Preferred Contact	Yes
Terminal Transmits	0 – 24 A (Low Power)

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



TE Part # CAT-H3930-CH8172  
DEUTSCH HD30 Housings




TE Part # CAT-H396-CH8172  
DEUTSCH HDP20 Housings




TE Part # CAT-D485-CH8172  
DEUTSCH DTM Housings



TE Part # CAT-D799-CH8172  
DEUTSCH DRC Housings



TE Part # CAT-ST858-CH8172  
DEUTSCH Strike Housings



TE Part # CAT-D781-CH8172  
DEUTSCH DRB Housings



TE Part # CAT-D48-ST273  
DEUTSCH Solid Contacts



TE Part # DTMH06-4SA  
PLG, 4P, BLK, N, HI TEMP, A



TE Part # DRC26-24SB  
PLG, 24P, BLK, N, B



TE Part # DRC26-50S09  
PLG, 50P, BLK, N, 09



TE Part # DRC26-60S01  
PLG, 60P, BLK, N, 01



TE Part # DRC26-60S04  
PLG, 60P, BLK, N, 04



TE Part # DRCP28-86SB  
PLG, 86P, BLK, 12/20, B



TE Part # DTMH06-2SD  
PLG, 2P, BLK, N, HI TEMP, D



TE Part # DTMH06-4SB  
PLG, 4P, BLK, N, HI TEMP, B



TE Part # DTMH06-4SC  
PLG, 4P, BLK, N, HI TEMP, C



TE Part # DRCP28-86SA  
PLG, 86P, BLK, 12/20, A



TE Part # 1060-20-0622  
PIN, SF, SIZE 20, 14-16, NI/NI




TE Part # 1060-20-0222  
PIN, SF, SIZE 20, 16-22, NI/NI




TE Part # 1060-20-0122  
PIN, SF, SIZE 20, 16-22, NI/NI

Also in the Series | **DEUTSCH Common Contact**



Automotive Terminals(91)



Insertion & Extraction Tools(8)

Customers Also Bought



TE Part #DTM04-12PC  
REC, 12P, GRN, N, C



TE Part #DTP04-2P-C015  
REC, 2P, GRY, E



TE Part #DT06-3S-CL08  
PLG, 3P, BLK, E, FLANGE CAP



TE Part #2-35112-2  
PIDG Ring Tongue Terminals



TE Part #WM-12S-B026  
WEDGE LOCK, 12P, PLG, GRN, DTM



TE Part #085193P002  
ES1000-NO.4-B7-X-75MM



TE Part #DTM12S-BT-BK  
BOOT, 12P, PLG, ST, BLK



TE Part #EK5194-000  
ES2000-NO.6-H2-0-39MM

Documents

Product Drawings

SOC, SF, SIZE 20, 16-22, SLEWLESS, NI/NI

English

CAD Files

3D PDF

3D



**Customer View Model**

[ENG\\_CVM\\_CVM\\_1062-20-0322\\_H.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1062-20-0322\\_H.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1062-20-0322\\_H.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

[CONNECTOR SELECTOR](#)

English

---

**Product Specifications**

[Application Specification](#)

English