



ANTENNA TECHNOLOGIES LIMITED COMPANY

# Model ADP24D51SBFRTM

ADP Plus

## Key Features

- Dipole Element Design
- Spring base and/or Fiberglass radome
- Excellent mechanical integrity and electrical performance
- Ruggedized construction for field durability
- ADP-ATLC Dipole Omni



Electrical Specifications	ADP24D51SBFRTM
Frequency Range, MHz	2200-2700 MHz 4100-6000 MHz
Impedance	50 ohm nominal
VSWR	<2.0:1
Gain	<2 dBi
Polarization	Vertical

Mechanical Specifications	ADP24D51SBFRTM
Connector Style	TNC Male
Material	Fiberglass radome
Operation Temp.	-20c to +65c
Storage Temp.	-30c to +75c