SIEMENS

Data sheet

US2:14IP32WA81



Non-reversing motor starter, Size 3 1/2, Three phase full voltage, Amb. compensate bimetal OLR, Contactor amp rating 115A, Non-combination type, Encl. type 4X 304 S. Steel, Water/dust tight noncorrosive

| FIG | ure | sim | nar |
|-----|-----|-----|-----|
| - | | | |

| product brand name | Class 14 & 22 |
|--|--|
| design of the product | Full-voltage non-reversing motor starter |
| special product feature | Half-size starter; Dual voltage coil |
| General technical data | |
| weight [lb] | 36 lb |
| Height x Width x Depth [in] | 26 × 13 × 8 in |
| touch protection against electrical shock | NA for enclosed products |
| installation altitude [ft] at height above sea level maximum | 6560 ft |
| ambient temperature [°F] | |
| during storage | -22 +149 °F |
| during operation | -4 +104 °F |
| ambient temperature | |
| during storage | -30 +65 °C |
| during operation | -20 +40 °C |
| country of origin | USA |
| Horsepower ratings | |
| yielded mechanical performance [hp] for 3-phase AC motor | |
| at 200/208 V rated value | 30 hp |
| at 220/230 V rated value | 40 hp |
| at 460/480 V rated value | 75 hp |
| at 575/600 V rated value | 75 hp |
| Contactor | _ |
| size of contactor | Controller half size 3 1/2 |
| number of NO contacts for main contacts | 3 |
| operating voltage for main current circuit at AC at 60 Hz maximum | 600 V |
| operational current at AC at 600 V rated value | 115 A |
| mechanical service life (switching cycles) of the main contacts typical | 500000 |
| Auxiliary contact | |
| number of NC contacts at contactor for auxiliary contacts | 0 |
| number of NO contacts at contactor for auxiliary contacts | 1 |
| number of total auxiliary contacts maximum | 7 |
| contact rating of auxiliary contacts of contactor according to UL | 10A@600VAC (A600), 5A@600VDC (P600) |
| Coil | |
| type of voltage of the control supply voltage | AC |
| control supply voltage | |

| at AC at 60 Hz rated value | 110 240 V |
|--|--|
| holding power at AC minimum | 14 W |
| apparent pick-up power of magnet coil at AC | 310 VA |
| apparent holding power of magnet coil at AC | 26 VA |
| operating range factor control supply voltage rated value of magnet coil | 0.85 1.1 |
| percental drop-out voltage of magnet coil related to the input voltage | 50 % |
| ON-delay time | 26 41 ms |
| OFF-delay time | 14 19 ms |
| Overload relay | |
| | |
| product function | Yes |
| overload protection | |
| test function | Yes |
| external reset | Yes |
| reset function | Manual and automatic |
| adjustment range of thermal overload trip unit | 0.85 1.15 |
| number of NC contacts of auxiliary contacts of overload relay | 3 |
| number of NO contacts of auxiliary contacts of overload relay | 0 |
| operational current of auxiliary contacts of overload relay | |
| • at AC at 600 V | 5 A |
| • at DC at 250 V | 5 A |
| contact rating of auxiliary contacts of overload relay according to UL | 5A@600VAC (B600), 5A@250VDC (P300) |
| Enclosure | |
| degree of protection NEMA rating | 4X, 304 stainless steel |
| design of the housing | dustproof, waterproof & resistant to corrosion |
| Mounting/wiring | |
| mounting position | Vertical |
| fastening method | Surface mounting and installation |
| type of electrical connection for supply voltage line-side | Box lug |
| tightening torque [lbf·in] for supply | 120 120 lbf·in |
| temperature of the conductor for supply maximum permissible | 75 °C |
| material of the conductor for supply | AL or CU |
| type of electrical connection for load-side outgoing feeder | Screw-type terminals |
| tightening torque [lbf·in] for load-side outgoing feeder | 35 50 lbf in |
| type of electrical connection of magnet coil | Screw-type terminals |
| tightening torque [lbf·in] at magnet coil | 5 12 lbf·in |
| type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded | 2x (16 12 AWG) |
| temperature of the conductor at magnet coil maximum permissible | 75 °C |
| material of the conductor at magnet coil | CU |
| type of electrical connection for auxiliary contacts | Screw-type terminals |
| tightening torque [lbf·in] at contactor for auxiliary contacts | 10 15 lbf·in |
| type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded | 1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG) |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible | 75 °C |
| material of the conductor at contactor for auxiliary contacts | CU |
| type of electrical connection at overload relay for auxiliary contacts | Screw-type terminals |
| tightening torque [lbf·in] at overload relay for auxiliary contacts | 5 12 lbf·in |
| type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded | 2x (16 12 AWG) |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible | 75 °C |

| material of the conductor at overload relay for auxiliary | CU | | |
|---|---|--|--|
| contacts | | | |
| Short-circuit current rating | | | |
| design of the fuse link for short-circuit protection of the main circuit required | 10kA@600V (Class H or K); 100kA@600V (Class R or J) | | |
| design of the short-circuit trip | Thermal magnetic circuit breaker | | |
| breaking capacity maximum short-circuit current (Icu) | | | |
| • at 240 V | 14 kA | | |
| • at 480 V | 10 kA | | |
| • at 600 V | 10 kA | | |
| certificate of suitability | NEMA ICS 2; UL 508; CSA 22.2, No.14 | | |

Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:14IP32WA81

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/US/en/ps/US2:14IP32WA81


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:14IP32WA81&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:14IP32WA81/certificate





D46590001

last modified:

1/25/2022 🖸