

## CTH7RF Series

From 3.9 $\mu$ H to 22,000 $\mu$ H



### CHARACTERISTICS

**Description:** Radial leaded power line inductor (UL sleeved)

**Applications:** Used in switching regulators, power amplifiers, power supplies, SCR and Triac controls, speaker crossover networks, RFI suppression and filters. Various applications.

**Operating Temperature:** -55°C to +125°C

**Inductance Tolerance:**  $\pm 10\%$

**Testing:** Inductance is tested on an HP4284A at 1.0kHz

**Packaging:** Bulk pack standard

**Marking:** Coils are sleeved in heat resistant polyolefin and labeled with the part number

**Saturation Current:** Lowers inductance by 10%

**Bobbin:** High saturation, allows for high inductance with low DC resistance

**Miscellaneous:** **RoHS Compliant.** Higher current parts available upon request

**Samples available. See website for ordering information**

### SPECIFICATIONS

Parts are marked to indicate inductance tolerance available.

K =  $\pm 10\%$

Part Number	Inductance ( $\mu$ H)	L Test Freq. (kHz)	SRF Min. (MHz)	DCR Max. ( $\Omega$ )	Saturation DC (A)	Rated AC (A)
CTH7RF-3R9K	3.9	1.0	38	.02	7.3	1.3
CTH7RF-4R7K	4.7	1.0	26	.02	6.3	1.3
CTH7RF-5R6K	5.6	1.0	25	.02	5.6	1.3
CTH7RF-6R8K	6.8	1.0	25	.03	5.3	1.3
CTH7RF-8R2K	8.2	1.0	22	.03	4.5	1.3
CTH7RF-100K	10	1.0	17	.03	4.1	1.3
CTH7RF-120K	12	1.0	16	.04	3.6	1.3
CTH7RF-150K	15	1.0	12	.04	3.3	1.3
CTH7RF-180K	18	1.0	11	.04	3.0	1.3
CTH7RF-220K	22	1.0	10	.05	2.7	1.3
CTH7RF-270K	27	1.0	7.0	.06	2.5	1.3
CTH7RF-330K	33	1.0	7.0	.08	2.2	1.0
CTH7RF-390K	39	1.0	7.0	.09	2.0	.80
CTH7RF-470K	47	1.0	6.0	.11	1.8	.80
CTH7RF-560K	56	1.0	6.0	.13	1.7	.80
CTH7RF-680K	68	1.0	7.0	.14	1.5	.80
CTH7RF-820K	82	1.0	4.0	.15	1.4	.80
CTH7RF-101K	100	1.0	3.0	.21	1.2	.63
CTH7RF-121K	120	1.0	3.0	.28	1.1	.51
CTH7RF-151K	150	1.0	3.0	.34	1.0	.51
CTH7RF-181K	180	1.0	3.0	.36	.95	.51
CTH7RF-221K	220	1.0	3.0	.43	.86	.51
CTH7RF-271K	270	1.0	2.0	.56	.77	.40
CTH7RF-331K	330	1.0	2.0	.67	.70	.40
CTH7RF-391K	390	1.0	2.0	.77	.64	.40
CTH7RF-471K	470	1.0	2.0	1.2	.59	.32
CTH7RF-561K	560	1.0	1.0	1.3	.54	.32
CTH7RF-681K	680	1.0	1.0	1.6	.49	.25
CTH7RF-821K	820	1.0	1.0	2.0	.44	.20
CTH7RF-102K	1000	1.0	1.0	2.3	.40	.20
CTH7RF-122K	1200	1.0	1.0	2.7	.35	.20
CTH7RF-152K	1500	1.0	.85	3.5	.33	.16
CTH7RF-182K	1800	1.0	.67	4.0	.29	.16
CTH7RF-222K	2200	1.0	.65	4.5	.27	.16
CTH7RF-272K	2700	1.0	.65	5.4	.24	.13
CTH7RF-332K	3300	1.0	.60	6.6	.22	.13
CTH7RF-392K	3900	1.0	.60	8.6	.20	.10
CTH7RF-472K	4700	1.0	.50	9.7	.18	.10
CTH7RF-562K	5600	1.0	.60	14	.16	.08
CTH7RF-682K	6800	1.0	.40	16	.15	.08
CTH7RF-822K	8200	1.0	.35	21	.13	.07
CTH7RF-103K	10000	1.0	.30	26	.12	.07
CTH7RF-123K	12000	1.0	.25	30	.11	.05
CTH7RF-153K	15000	1.0	.30	43	.10	.04
CTH7RF-183K	18000	1.0	.30	48	.09	.04
CTH7RF-223K	22000	1.0	.30	49	.085	.04

### PHYSICAL DIMENSIONS

