

Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

| COUNT | DESCRIPTION OF REVISIONS | BY | CHKD | DATE | COUNT | DESCRIPTION OF REVISIONS | BY | CHKD | DATE |
|---|-----------------------------|--|------|----------------------------|--|---|------------------------|----------|------|
| △ | | | | | △ | | | | |
| △ | | | | | △ | | | | |
| APPLICATION STANDARD | | | | | | | | | |
| RATING | OPERATING TEMPERATURE RANGE | -55 °C TO 85 °C | | | STORAGE TEMPERATURE RANGE | -10 °C TO 60 °C | | | |
| | VOLTAGE | AC 50 V | | | OPERATING HUMIDITY RANGE | RELATIVE HUMIDITY : 95 % MAX (NO DEW CONDENSATION IS PERMITTED) | | | |
| | CURRENT | 0.3 A | | | | | | | |
| SPECIFICATIONS | | | | | | | | | |
| ITEM | | TEST METHOD | | | REQUIREMENT | | | QT | AT |
| CONSTRUCTION | | | | | | | | | |
| GENERAL EXAMINATION | | VISUALLY AND BY MEASURING INSTRUMENT. | | | ACCORDING TO DRAWING | | | X | X |
| MARKING | | CONFIRMED VISUALLY. | | | | | | X | X |
| ELECTRICAL CHARACTERISTICS | | | | | | | | | |
| CONTACT RESISTANCE | | 100 mA (DC OR 1000 Hz). | | | 70 mΩ MAX. | | | X | X |
| INSULATION RESISTANCE | | 100 V DC. | | | 100 MΩ MIN. | | | X | - |
| VOLTAGE PROOF | | 150 V AC FOR 1 min. | | | NO FLASHOVER OR BREAKDOWN. | | | X | X |
| MECHANICAL CHARACTERISTICS | | | | | | | | | |
| INSERTION AND WITHDRAWAL FORCES | | MEASURED BY APPLICABLE CONNECTOR. | | | INSERTION FORCE: 60 N MAX. WITHDRAWAL FORCE: 2.5 N MIN. | | | X | - |
| MECHANICAL OPERATION | | 50 TIMES INSERTION AND EXTRACTIONS. | | | 1)CONTACT RESISTANCE: 80 mΩ MAX. 2) NO DAMAGE. CRACK AND LOOSENESS OF PART. | | | X | - |
| VIBRATION | | FREQUENCY: 10 TO 55 Hz. SINGLE AMPLITUDE: 0.75 mm. m/s^2 AT 10 CYCLES FOR 3 DIRECTIONS. | | | 1)NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. 2)NO DAMAGE. CRACK AND LOOSENESS OF PART. | | | X | - |
| SHOCK | | 490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS. | | | | | | X | - |
| ENVIRONMENTAL CHARACTERISTICS | | | | | | | | | |
| DAMP HEAT (STEADY STATE) | | EXPOSED AT 40±2 °C, 90~95 %, 96 h. | | | 1)CONTACT RESISTANCE: 80 mΩ MAX. 2)INSULATION RESISTANCE: 100 MΩ MIN. | | | X | - |
| RAPID CHAGE OF TEMPERTURE | | TEMPERTURE -55→15~35→ 85→15~35°C TIME 30→ 2~ 3→ 30→ 2~ 3min. UNDER 5 CYCLES. | | | 3)NO DAMAGE, CRACK AND LOOSENESS OF PART. | | | X | - |
| DRY HEAT | | EXPOSED AT 85 °C, 96 h. | | | 1)CONTACT RESISTANCE: 80 mΩ MAX. | | | X | - |
| COLD | | EXPOSED AT -55 °C, 96 h. | | | 2)NO DAMAGE, CRACK AND LOOSENESS OF PART. | | | | |
| CORROSION SALT MIST | | EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h. | | | NO HEAVY CORROSION | | | X | - |
| SULPHUR DIOXIDE | | EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JIS C 0090) | | | 1)CONTACT RESISTANCE: 80 mΩ MAX. 2)NO HEAVY CORROSION. | | | X | - |
| RESISTANCE TO SOLDERING HEAT | | REFLOW RECOMMENDED TEMPERATURE PROFILE <p>25°C (150 S) 150°C 160°C (30 S) (20~30 S) 240°C 5 S MAX 200°C</p> | | | NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT | | | X | - |
| SOLDRABILITY | | SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR IMMERSION DURATION, 2 s. | | | NO PINHOLE OR DEWETTING ON SOLDERED SURFACE. | | | X | - |
| REMARKS | | | | DRAWN | DESIGNED | CHECKED | APPROVED | RELEASED | |
| | | | | <i>J. Matsukawa</i> | <i>J. Matsukawa</i> | <i>M. Ishida</i> | <i>T. Yoshimura</i> | | |
| UNLESS OTERWISE SPECIFIED ,REFER TO JIS C 5402. | | | | 00.01.15 | 00.01.15 | 00.01.17 | 00.01.17 | | |
| NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST | | | | | | | | | |
| HRS HIROSE ELECTRIC CO.,LTD | | | | SPECIFICATION SHEET | | | PART NO. | | |
| CODE NO.(OLD) | | | | DRAWING NO. | | | CODE NO. | | |
| CL | | | | ELC4 - 152623 - 02 | | | CL 573 - 0643 - 1 - 22 | | |
| | | | | | | | 1 1 | | |

TO
PCK