

NAKAGAWA ELECTRONICS LIMITED

QUARTZ CRYSTAL UNIT SPECIFICATION

NKG PART NUMBER

S5M12.0000F20E35

DESCRIPTION

Quartz Crystal in 5.0x3.2 ceramic seam seal SMD package, 12.0MHz, 20pF, 30/50ppm; –20°C to +70°C

CUSTOMER

CUSTOMER P/N

	CUSTOMER APPROVAL
Please sign and chop for approval of the provided specification sheet and return us this cover page to us, thank you.	
	Signature(s) and stamp here please.

TABLE OF CONTENTS

1.	ELECTRICAL PARAMETERS AND ENVIRONMENTAL CONDITIONS	Page	2
2.	PRODUCT MARKING	Page	2
3.	PACKAGE DIMENSIONS	Page	3
4.	ENVIRONMENTAL COMPLIANCE INFORMATION	Page	3
5.	RELIABILITY TEST INFORMATION	Page	5
6.	PACKAGING INFORMATION	Page	6

REVISION TABLE

REV.	DESCRIPTION	PREPARED	APPROVED	DATE
А	Original release	R. 40	N. Wong	2010-08-06
В	Change form, add unreeling info	Rita	M. Bruech	2012-03-22
С	Change form; reduce ESR limit	Jiang Y.B.	M. Bruech	2012-12-12
D	Rev. form, upd. date code table, add T _{OPAB}	Jiang Y.B.	M. Bruech	2021-10-12

ADDRESS: Block A, Flat 1-2 7/F., Hoi Luen Ind. Centre, 55 Hoi Yuen Rd., Kwun Tong, Kln., Hong Kong, Tel: (852) 2389 9201, Fax: (852) 2341 0001, E-mail: info@nkg.com.hk, Web: www.nkg.com.hk



PRODUCT SPECIFICATION SHEET

1. ELECTRICAL PARAMETERS AND ENVIRONMENTAL CONDITIONS

PACKAGE TYPE (SEE NEXT PAGE FOR DETAILS)	CX-5M (5.0x3.2 p4h09)
NOMINAL FREQUENCY (F_N)	12.000MHz
MODE OF OSCILLATION	FUNDAMENTAL
CRYSTAL CUT	AT-Cut
LOAD CAPACITANCE (CL)	20pF
FREQUENCY TOLERANCE ($\Delta f/F_N$ at +25°C)	±30ppm
FREQUENCY STABILITY (NOTE 2)	±50ppm
OPERATING TEMPERATURE (T _{OP}) (NOTE 2)`	–20°C to +70°C
OPERABLE TEMPERATURE (T _{OPAB}) (NOTE 2)	–40°C to +85°C
AGING FIRST YEAR (($\Delta f/F_N$)/y ₁ at +25°C)	±3ppm
EQUIVALENT SERIES RESISTANCE (ESR)	60Ω MAX
DRIVE LEVEL (DL)	100μW TYP; 300μW MAX
SHUNT CAPACITANCE (C ₀)	5.0pF MAX
INSULATION RESISTANCE (IR @100V _{DC})	500MΩ MIN
STORAGE TEMPERATURE (T _{ST})	–55°C to +125°C
TEST IMPEDANCE METER (NOTE 3)	IEC-444 COMPLIANT
REFLOW SOLDERING CONDITIONS	10s MAX AT +260°C±5°C

NOTE 1: Frequency stability is the frequency deviation over operating temperature in reference to the frequency reading at +25°C.

NOTE 2: Parameter limits are guaranteed over the operating temperature range. The unit operates correctly over the operable temperature range, but may exceed one or more specified parameter limit.

NOTE 3: Test impedance meter such as S&A 250B, KOLINKER KH series or other IEC-444 compliant equipment.

2. PRODUCT MARKING

NKG = NAKAGAWA logo and DATE CODE "Yww" [Y] = alpha YEAR CODE per table below

NKG Yww 12.000

[ww] = WEEK number of manufacturing

FREQUENCY in MHz (2+3 digits or 3+2 for OT mode units)

YEAR	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031
CODE	v	w	х	Y	Z	Α	В	С	D	Е	F



PRODUCT SPECIFICATION SHEET

3. PACKAGE DIMENSIONS



4. ENVIRONMENTAL COMPLIANCE INFORMATION

The product consists of the following parts and materials:

NO.	PART	MATERIAL(S)	REMARKS		
1	BASE (PACKAGE)	Ceramic (Al ₂ O ₃)	Terminals gold plated		
2	CRYSTAL BLANK	Quartz (SiO ₂)	Synthetic material, pure		
3	ELECTRODE PLATING	Silver (Ag)	High purity metal		
4	CONDUCTIVE ADHESIVE	Silver filled epoxy type	Conductive cement		
5	LID (COVER)	Metal alloy (Kovar)	Surface Nickel coated		
ļ					
[1	(S Lid	CONDUCTIVE ADHESIVE		
A		₽ <u>\</u> /	CRYSTAL BLAN		
-*			1		
-					



RoHS COMPLIANCE

We can certify herewith that the product is fully RoHS complaint according the "DIRECTIVE 2011/65/EU OF THE EURPPEAN COUNCIL and DIRECTIVE 2015/863 (RoHS 2/3 or also called RoHS 10) for electrical and electronic equipment and its amendments.

No exemptions are applicable for this product.

This product is considered LEAD-FREE, Lead (Pb) contamination guaranteed to be below 500ppm.

In regards of RoHS CE marking directive for finished products, we can provide RoHS test reports and MDS to show compliance, but since our product is not a final application we cannot provide a CE mark.

HALOGEN FREE

We can certify that this product is Halogen-Free per IEC 61249-2-21:2003 meeting the threshold limits given by the standard.

REACH (SVHC) COMPLIANCE

We have verified and continue monitoring the usage of substances (SVHC) listed by REACH, Registration, Evaluation, Authorization and Restriction of Chemicals, a European Community Regulation on chemicals and their safe use (Regulation (EC) No 1907/2006) entered into force on June 1st 2007. We keep continuously monitoring the ongoing updates made by REACH and verify that the products stay compliant; please feel free to request our CoC for compliance confirmation.

The product does comply as well with the substance prohibitions and restrictions defined in Annex XVII of Regulation 1907/2006 (REACH), none of the listed substances being contained. (As of today, the release date of this document.)

PFOS / PFOA FREE

We can certify that the product as specified is being FREE of any PFOS and PFOA.

ELECTROSTATIC DISCHARGE (ESD) SENSITIVTY

This product is NOT sensitive to ELECTROSTATIC DISCHARGE (ESD), no specific precautions for handling and storage are required.

MOISTURE SENSITIVTY (MSL) CLASSIFICATION [J-STD-020C]

This product in a hermetically sealed package, does NOT fall under the classification of moisture sensitivity per above stated standard (standard is for non-hermetically sealed components).

If customer's system requires an entry in this regard we suggest using LEVEL 1.



PRODUCT SPECIFICATION SHEET

5. RELIABILITY TEST INFORMATION

NO.	TEST ITEM	TEST CONDITIONS	CRITERIA
1	High Temperature Storage MIL-STD-202 Method 108	1,000 hours ±12 hours; @85°C ±2°C 24±2 hours rest before electrical test	ΔFr=±10ppm ΔRs=±5ohm
2	Biased Humidity MIL-STD-202 Method 103	1,000 hours ±12 hours; @85°C ±2°C and RH=85% 24±2 hours rest before electrical test	ΔFr=±10ppm ΔRs=±5ohm
3	Low Temperature Storage IEC-60068-2-1	1,000 hours ±12 hours @-40°C ±2°C 24±2 hours rest before electrical test	ΔFr=±10ppm ΔRs=±5ohm
4	Temperature Cycling JESD22 Method JA-104	 @-55°C and +125°C; 1000 cycles Transfer time 5min, dwell time 30min 24±2 hours rest before electrical test 	ΔFr=±10ppm ΔRs=±5ohm
5	Shock Test (Drop Test) IEC-60068-2-32	3 times drop from 100cm height onto 3cm thick hard wood plate	ΔFr=±5ppm ΔRs=±2ohm
6	Shock Test (Mechanical) MIL-STD-202 Method 213	Devices are shocked with 100G, half since wave in three perpendicular axis for three times each direction	ΔFr=±5ppm ΔRs=±2ohm
7	Vibration MIL-STD-202 Method 204	Frequency range 10~2,000Hz Amplitude 5g Sweep time 20 min 12 cycles of each direction (3 axis)	ΔFr=±5ppm ΔRs=±2ohm
8	Resistance to Soldering Heat J-STD-020C	Pre-heat temp.+150~200°CPre-heat time60~180sTest temperature +260°C ±5°CTest time20~40s, 2 times	ΔFr=±5ppm ΔRs=±2ohm Visually good, no rusting
9	Solderability J-STD-002	Pre-conditioned @+155°C, 4 hours dry heat, subject to soldering by applying SMD method B: 260°C±5°C	≥95% solder coverage
10	Terminal Strength (SMD) JISC60068-2-21	1.8kg tangential thrust (60 seconds) and 1.8kg of vertical tension (60 seconds)	No rupture of solder pads

For more details you may request our Reliability Test procedure or the bi-annual test reports.



6. PACKAGING INFORMATION

ALL NON-SPECIFIED DIMENSIONS AND T&R PARAMETERS ARE IN COMPLIANCE TO EIA-481.

CARRIER TAPE



Symbol	A0	BO	B1	D0	D1	E1	F	КО	P0	P1	P2	т	W
Dim.	3.6	5.4	8.0	1.5	1.5	1.75	7.5	1.4	4.0	8.0	2.0	0.3	12.0±0.2

ALL DIMENSIONS [mm]; ALL TOLERANCES ± 0.1 IF NOT STATED OTHERWISE.

REEL

Symbol

QTY per reel: 1,000pcs



Dim.	Ø178±1.0 (altern. 180mm)
ALL DIM	ENSIONS [mm]

UNREELING AND PRODUCT ORIENTATION

А

Quartz crystal units are non-polarized components; there is no pin identification or specific orientation in the carrier tape required. Products may insert in the carrier tape with their marking all in same direction for cosmetic reasons only.

PACKAGING BOX (Pizza box)

Box size: 185x185x25 MAX QTY per box: 1 Reel

END OF DOCUMENT

S5M12.0000F20E35_RevD