

DATASHEET

SMD B B EASV1003GA1



Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

Description

- The SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General



Device Selection Guide

Chip Materials	Emitted Color	Resin Color
InGaN	Brilliant Green	Water Clear

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	
Reverse Voltage	V_R	5	V	
Forward Current	l _F	25	mA	
Peak Forward Current (Duty 1/10 @1KHz)	I _{FP}	100	mA	
Power Dissipation	Pd	95	mW	
Operating Temperature	T_{opr}	-40 ~ +85	$^{\circ}\mathbb{C}$	
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}$ C	
Electrostatic Discharge	ESD _{HBM}	150	V	
Soldering Temperature	T _{sol}	Reflow Soldering : 260 $^\circ\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!\!$		

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	lv	225		565	mcd	
Viewing Angle	201/2		125		deg	
Peak Wavelength	λр		518		nm	
Dominant Wavelength	λd	515		530	nm	I _F =20mA
Spectrum Radiation Bandwidth	$\triangle \lambda$		35		nm	
Forward Voltage	VF	2.7		3.7	V	
Reverse Current	IR			50	μΑ	V _R =5V

Note:

1.Tolerance of Luminous Intensity: ±11%

2.Tolerance of Dominant Wavelength ±1nm

3. Tolerance of Forward Voltage: ±0.05V



Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
S2	225	285		
T1	285	360	mod	IF =20mA
T2	360	450	——— mcd	IF =ZUIIA
U1	450	565		

Bin Range Of Dom. Wavelength

Group	Bin Code	Min.	Max.	Unit	Condition
	W	515	520		
X	X	520	525	nm	IF =20mA
	Υ	525	530	_	

Bin Range Of Luminous Voltage


211 1111130 01 2411111040 + 0111130						
Group	Bin Code	Min.	Max.	Unit	Condition	
	10	2.7	2.9			
	11	2.9	3.1			
N	12	3.1	3.3	V	IF =20mA	
	13	3.3	3.5			
	14	3.5	3.7			


Note:


- 1.Tolerance of Luminous Intensity: ±11%
- 2.Tolerance of Dominant Wavelength ±1nm
- 3. Tolerance of Forward Voltage: ±0.05V





Typical Electro-Optical Characteristics Curves



















Package Dimension








Suggested pad dimension is just for reference only. Please modify the pad dimension based on individual need.

Note: Tolerances unless mentioned ±0.1mm. Unit = mm




Moisture Resistant Packing Materials

Label Explanation



- CPN: Customer's Product Number
- P/N: Product NumberQTY: Packing Quantity
- · CAT: Luminous Intensity Rank
- · HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- · LOT No: Lot Number


Reel Dimensions



Note: The tolerances unless mentioned is $\pm 0.1 \text{mm}$, Unit = mm




Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Moisture Resistant Packaging





Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage


- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30°C or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 1 year under 30℃ or less and 60% RH or less.

If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment: $60\pm5^{\circ}$ C for 24 hours.

3. Soldering Condition

3.1 Pb-free solder temperature profile




- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.





Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.