

51943 ✓ ACTIVE




TERMI-FOIL

TE Internal #: 51943

Foil Terminals, End Tap, Type 13, Mating Tab Width 6.35 mm [.25 in], Tin Plating, Box, 150 °C [302 °F], TERMI-FOIL

[View on TE.com >](#)

Terminals & Splices > Foil Terminals



Foil Terminal Type: **End Tap**

Foil Terminal Body Type: **Type 13**

Mating Tab Width: **6.35 mm [.25 in]**

Accepts Foil Thickness (Max): **.76 mm [.03 in]**

Terminal Plating Material: **Tin**

**Features**

**Body Features**

Foil Terminal Body Type	Type 13
-------------------------	---------

**Contact Features**

Foil Terminal Type	End Tap
Mating Tab Width	6.35 mm [.25 in]
Terminal Plating Material	Tin

**Termination Features**

Accepts Foil Thickness (Max)	.76 mm [.03 in]
------------------------------	-----------------

**Usage Conditions**

Insulation Option	Uninsulated
Operating Temperature Range	150 °C [302 °F]

**Packaging Features**

Packaging Quantity	100
Packaging Method	Box

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




Also in the Series | [TERMI-FOIL](#)



Foil Terminals(23)

## Customers Also Bought

TE Part #1-487547-1  
FFC,RCPT CONTACT,.050" CNTRLINTE Part #1-487526-6  
017 HOUSING FFC RCPT 100CL SRTE Part #487923-1  
FFC SDR TAB 100 FULL SN-PBTE Part #487576-9  
17 ZIF LINE 50 ASSYTE Part #53645-2  
TERMINAL,TERMI-FOIL 16-14TE Part #1-103673-6  
17 MTE HDR SRRA LATCH W/HLDWNTE Part #1676480-2  
CRG0402 1% 100RTE Part #329860  
TERMINAL,TERMI-FOIL 16-14TE Part #4-2176422-7  
TLRP 2512 3.0W R003 1% 50PPM 4K RL

## Documents

### Product Drawings

[TAB, TERMI-FOIL END TAP TERMINAL](#)

English

### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_51943\\_G.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_51943\\_G.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_51943\\_G.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Instruction Sheets

[PRE-SET HAND TOOL,TERMI-FOIL](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese