



ITEM NO	DESCRIPTION	COLOUR	MATERIAL
1	RECEPTACLE HOUSING Buchsengehäuse	BLACK schwarz	PBT-GF30 / V-0
2	6POS. CAVITY BLOCK, CODE, "A" Spot, Kammerblock, Kodierung, "A"	BLACK schwarz	PBT-GF30 / V-0
2	6POS. CAVITY BLOCK, CODE, "B" Spot, Kammerblock, Kodierung, "B"	GREEN grün	PBT-GF30 / V-0
2	6POS. CAVITY BLOCK, CODE, "C" Spot, Kammerblock, Kodierung, "C"	BLUE blau	PBT-GF30 / V-0
3	6POS. CAVITY BLOCK, CODE, "D" Spot, Kammerblock, Kodierung, "D"	YELLOW gelb	PBT-GF30 / V-0
4	U-SLIDE U-Schieber	WHITE weiss	MVO
5	SEAL Dichtung	WHITE weiss	MVO

REV.	NO. OF POS. Polzahl	QTY Stueck	CODE Kodierung	COLOR OF CAVITY BLOCK Farbe des Kammerblocks	QUANTITY Stueck	ITEM NO ASSY
1	6	1	D	BLUE blau	1	4
1	6	1	C	GREEN grün	1	3
1	6	1	B	GREY grau	1	2
1	6	1	A	BLACK schwarz	1	1

4-1418437-1	J	6	1	D	BLUE	1	4
3-1418437-1	J	6	1	C	GREEN	1	3
2-1418437-1	J	6	1	B	GREY	1	2
1-1418437-1	J	6	1	A	BLACK	1	1

TE ORDER-NO. TE Bestell-Nr.	REV.	NO. OF POS. Polzahl	QTY Stueck	CODE Kodierung	COLOR OF CAVITY BLOCK Farbe des Kammerblocks	QUANTITY Stueck	ITEM NO ASSY
-----------------------------	------	---------------------	------------	----------------	--	-----------------	--------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN Shilpa Bhavikatti	11FEB2009
OTHERS: DIMENSIONS: MASSENHABEN: DIMM		CHK J.Grandzow	12FEB2009
TOLERANCES: UNLESS OTHERWISE SPECIFIED: ACC. TO DIN 9130-10		APVD L. Berwein	12FEB2009
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		NAME	6POS. AMP MCP 2.8, REC HSG. ASSY
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		PRODUCT SPEC	6pos. AMP MCP 2.8, Buchsengehäuse
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		PRODUCT SPEC	HEAVY DUTY SEALED CONNECTOR SERIES - GROUP C
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		APPLICATION SPEC	
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		WEIGHT 17.8 g	RESTRICTED TO OUR PUR
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		SCALE 2:1	
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		SHEET 1 OF 1	
FINISHES: UNLESS OTHERWISE SPECIFIED: SEE TABLE		Customer Drawing	REV J2

LOC	DIST	REV	DATE	BY	APPV
A1	-	H2	23AUG2011	Ho	Krauss
		J	24MAY2012	MN	SKR
		J1	15MAY2015	SK	Krauss
		J2	28FEB2022	NS	AW

- NOTES
Bemerkungen
- TE LOGO
TE Logo
 - ASSY PN, PRODUCTION DATE (CALENDAR DAY/YEAR):
MARKING OPTIONAL AS LASER ENGRAVING OR
LASER WITH COLOR CHANGE
Assy PN, Produktionsdatum (Kalendertag/Jahr):
Beschriftung wahlweise als Lasergravur oder Laser mit Farbumschlag
 - BULK PACKAGING IN CORRUGATED BOX
Schuetztgut im Versandkarton
 - CAVITY NUMBERING
Kammer Bezeichnung
 - CAVITIES MATED WITH AMP MCP 2.8
SEE PRODUCT GROUP DRAWING
TE NO: 1355036
MAX. WIRE SIZE: 2.5mm² FLR (AWG 12 TXL)
Kontaktkammern passend fuer AMP MCP 2.8
siehe Produktgruppenzeichnung
TE Nr: 1355036
max. Drahtgrossenbereich: 2.5mm² FLR (AWG 12 TXL)
 - SUITABLE COVERS SEE DRAWING: 1670057, 1670364
Passende Kappen siehe Zeichnung: 1670057, 1670364
 - SLIDING DISTANCE OF SECONDARY LOCKING
Verschiebeweg der 2. Kontaktsicherung
 - FITS TO TE INTERFACE DRAWING 114-18740-1
Passend zur Ausfuehrungsvorschrift 114-18740-1
 - 10 MALFUNCTION CAUSED BY LACQUER IS NOT
COVERED BY TYCO ELECTRONICS WARRANTY.
Funktionsbeeintraechtigung durch Lackieren liegt nicht im
Einfluss- und Gewährleistungsumfang von Tyco Electronics.