



Crystal Part No.: RFX-11-24.0M30IL

Issue 2: 17th November 2022

Features

- Frequency 24.0MHz fundamental
- Calibration tolerance ±10ppm
- Temperature stability ±20ppm
- Temperature range (-40 to +85)°C
- The flexible nature of the design, means that variations to suit almost any application can be developed to meet individual customer requirements
- Drive level 100mW
- Series Resistance 150Ω
- Shunt capacitance C₀ 3.0 pF max.
- Load capacitance CL (8 50)pF or series
- Ageing ±3 x 10⁻⁶ /year

Environmental

- Electrostatic-Sensitive Device (ESD)
- Storage Temperature Range: (-40 to +125)°C
- Mechanical shock: MIL standard 202F, method 213 condition J
- Thermal shock: MIL standard 202F, method 107, condition A
- Vibration: MIL standard 202F, method 204, condition B
- Solderability: 5 seconds maximum at 230°C
- 3 seconds maximum at 350°C

Compliance

- RoHS Status (2011/65/EU) Compliant
- **REACH Status Compliant**


Packaging

Pack Style: tape and reel: 3000 pieces

Ordering Information


Crystal model: RFX-11 series

Crystal Part No.: RFX-11-24.0M30IL[xx] Where [xx] is the required load e.g. RFX-11-24.0M30IL30 for 30pF RFX-11-24.0M30ILS for series




Dimensions (mm)





pads viewed from bottom pad size (0.47 x 0.37)mm

1.60 top view crystal pads - 1 & 3 metal lid - 2 & 4



Part number examples by load

Load condition	Part number
10pF	RFX-11-24.0M30IL10
20pF	RFX-11-24.0M30IL20
30pF	RFX-11-24.0M30IL30
Series	RFX-11-24.0M30ILS

Europe & Asia: +44 1506 439 222 Email: sales@rfx.co.uk Web: www.rfx.co.uk Page: 1 of 1

Americas: +1 289 481 2019 Email: sales@laptech.com