

Crystal Part No.: RFX-53T-16.0M40IL

Issue 1; 6th July 2022

Features

- Frequency 16.0MHz fundamental
- Calibration tolerance ± 10 ppm
- Temperature stability ± 30 ppm
- Temperature range (-40 to +85) $^{\circ}$ C
- The flexible nature of the design, means that variations to suit almost any application can be developed to meet individual customer requirements
- Drive level 100uW
- Series Resistance 50 Ω
- Shunt capacitance C_0 7 pF max.
- Load capacitance CL (8 - 50)pF or series [to order]
- Ageing $\pm 3 \times 10^{-6}$ /year

Environmental

- Electrostatic-Sensitive Device (ESD)
- Storage Temperature Range: (-55 to +125) $^{\circ}$ C
- Mechanical shock: MIL standard 202F, method 213 condition J
- Thermal shock: MIL standard 202F, method 107, condition A
- Vibration: MIL standard 202F, method 204, condition B
- Solderability: 5 seconds maximum at 230 $^{\circ}$ C
- 3 seconds maximum at 350 $^{\circ}$ C

Compliance


- RoHS Status (2011/65/EU) Compliant
- REACH Status - Compliant

Packaging


- Pack Style: tape and reel: 1000 pieces, 3K pieces

Ordering Information

- Crystal model: RFX-53T series
- Crystal Part No.: RFX-53T-16.0M40IL[xx]
Where [xx] is the required load
e.g. RFX-53T-16.0M40IL30 for 30 pF
RFX-53T-16.0M40ILS for series



Dimensions (mm)



Part number examples by load

Load condition	Part number
10pF	RFX-53T-16.0M40IL10
20pF	RFX-53T-16.0M40IL20
30pF	RFX-53T-16.0M40IL30
Series	RFX-53T-16.0M40ILS