## **SPECIFICATIONS**

	DA032-01-01/HD-I								SILC		0110			
	DA032-01-01/11D-1	MODEL		HWS1000	HWS1000	HWS1000	HWS1000	HWS1000	HWS1000	HWS1000	HWS1000	HWS1000	HWS1000	
	ITEMS	MODEL		-3/HD	-5/HD	-6/HD	-7/HD	-12/HD	-15/HD	-24/HD	-36/HD	-48/HD	-60/HD	
1	Nominal Output Voltage		V	3.3	5	6	7.5	12	15	24	36	48	60	
2	Maximum Output Current		А	200	200	167	134	88	70	46	30.7	23	18.4	
3	Peak output Current (*13)	at 200VAC	А	-	-	-	160	100	80	58.5	39	29.2	23.4	
4	Maximum Output Power	1	W	660	1000	1002	1005	1056	1050	1104	1104	1104	1104	
5	Peak Output Power (*13)	at 200VAC	W	-	-	-	1200	1200	1200	1404	1404	1404	1404	
6	Efficiency (Typ) (*1)	at 100VAC	%	71	76	79	80	82	83	85	85	86	85	
		at 200VAC	%	73	78	81	82	85	85	87	88	88	88	
7	Input Voltage Range	(*2)	-				85 - 26	5VAC (47 - 63	3Hz) or 120 - 3	30VDC		•		
8	Input Current (100/200VAC)(Typ)	(*1)	Α	9.6/5.0					13.5/7.0					
9	Inrush Current (100/200VAC)(Typ)	(*3)	Α					20	/40					
10	PFHC		-				Ι	Designed to me	et IEC6100-3-	-2				
11	Power Factor (100/200VAC)(Typ)	(*1)	-	0.98/0.95										
12	Output Voltage Range	-	V	2.64-3.96	4.0-6.0	4.8-7.2	6.0-9.0	9.6-14.4	12.0-18.0	19.2-28.8	28.8-43.2	38.4-52.8	48.0-66.0	
13	Maximum Ripple & Noise			120	120	150	150	150	150	150	200	200	400	
	(*4			160	160	180	180	180	180	180	240	500	600	
14	Maximum Line Regulation	(*5)	mV	20	20	36	36	48	60	96	144	192	240	
15	Maximum Load Regulation	(*6)	mV	40	40	60	60	100	120	150	150	300	360	
16	Temperature Coefficient		-					Less than	0.02% / °C					
17	Over Current Protection	(*7)	-	-	laximum Outp	-				(Peak Output	-			
18	Over Voltage Protection	(*8)	V	4.12-4.62	6.25-7.0	7.5-8.4	9.37-10.5	15.0-17.4	18.7-21.8	30.0-34.8	45.0-49.7	55.2-60.0	69.0-75.0	
19	Hold-up Time (Typ)	(*9)	-						ms					
20	Leakage Current	(*10)	-				1.21		00VAC / 240V	VAC				
21	Remote Sensing		-	Possible										
22	Remote ON/OFF control		-	Possible										
23	Monitoring Signal		-	PF(Open Collector Output)										
24	Output Voltage External Control		-	Possible										
25	Parallel Operation		-	Possible										
26	Series Operation	(*1.1)	-	Possible -10 - + 71°C, Guarantee Start up -4010°C										
27	Operating Temperature	(*11)	-				-10 - +			10°C				
		-10 - +40°C	%	0.2	3.9			10	00	00				
		+50°C +71°C	%		5.9					0				
28	Operating Humidity	+/I C	-	J	0			10 00%PH0	No Condensing					
28	Storage Temperature		-					-	+85°C	3)				
30	Storage Humidity		-						No Condensing	n)				
31	Cooling		-					,	y Blower Fan	<i>⊳/</i>				
32	Withstand Voltage		-			In	put - FG : 2kV		5	3kVAC (20m	A)			
					Output - FG	-	00mA), (60V 1				-	A) for 1min		
33	Isolation Resistance		-			(***			Output - FG	-	(			
						More					0%RH			
34	Vibration (*14)			More than 10Mohm Output - CNT 100VDC at 25°C and 70%RH At no operating, 10 - 55Hz (Sweep for 1min.)										
	(*15)						-	-	nt, X,Y,Z 1h ea					
						Designed to	meet MIL-ST				, category 10			
35	Shock (In package)	(*15)	-			-			196.1m/s <sup>2</sup>					
							Designed to		D-810F 516.5	Procedure I				
36	Safety	(*12)	-		Apj	proved by UL6	62368-1, CSA6				950-1, EN6095	50-1		
							(Expire da	te of 60950-1	: 20/12/2020),	EN50178.				
								Designed to r	neet DENAN.					
37	Line DIP		-	Designed to meet SEMI-F47 (200VAC Line only)										
38	Conducted Emission		-											
39	Radiated Emission		- Designed to meet EN55011/EN55032-B, FCC-ClassB, VCCI-ClassB, CISPR-ClassB.											
40	Immunity		-			Desig	ned to meet IE	EC61000-4-2(I	Level 2,3), -3(I	Level 3), -4(Lev	vel 3),			
								-5(Level 3,4)	, -6(Level 3), -	8(Level 4), -1	1			
41	Weight		g					MAX	3200					
42	Size (W x H x D)		mm				126.5 x	82 x 240 ( Ref	er to Outline I	Drawing )				
43	Other		-				PCB Coat	ing on solder s	side and comp	onent side.				

\*Read instruction manual carefully, before using the power supply unit. =NOTES=

- \*1. At Ta=25°C and maximum output power.
- input voltage range will be 100 240VAC (50/60Hz).
- into the power supply noise filter.
- \*5. 85 265VAC, constant load.
- \*6. No load-Full load, constant input voltage.
- will cause the output to shutdown. will result to output shutdown.

- \*11. Ratings Derating at standard mounting.
- \*12. As for DENAN, designed to meet at 100VAC.

# **TDK-Lambda**

\*2. For cases where conformance to various safety specs (UL, CSA,EN) are required,

\*3. First in-rush current. Not applicable to the first 0.2ms in-rush current flowing

\*4. Measure with JEITA RC-9131A probe, Bandwidth of scope :100MHz.

(at 100uF electric capacitor and 0.47uF film capacitor on the test fixture board.)

\*7. Constant current limit with automatic recovery. Over current condition for more than 5 seconds

Output current exceeding maximum rated output current for more than 10 seconds continuously

For peak current capable model, over current protection triggers at 105% of

maximum output current or more with 100VAC input line.

\*8. OVP circuit will shut down output, manual reset (Power cycle) or ON/OFF CNT signal reset.

\*9. At 100/200VAC, nominal output voltage and maximum output current.

\*10. Measured by the each measuring method of UL, CSA, EN and DENAN (at 60Hz), Ta=25°C.

- Load (%) is percent of maximum output power or maximum output current, whichever is greater. - As for other mountings, refer to derating curve ( DA032-01-02/HD-\_).

- For conditions of start up at -40°C - -10°C, refer to derating curve ( DA032-01-03/HD-\_ ).

\*13. Peak output current is less than 10 seconds, and duty 35% max.(200VAC Line only)


\*14. Category 4 exposure levels : Truck transportation over U.S. highways.

\*15. It is compulsory to fix BRACKET onto product for MIL-STD-810F 514.5

and MIL-STD-810F 516.5. Refer to DA032-01-04/HD-\_.


DA032-01-02/HD

		OUTPUT DERATING					
3, 5V	6-60V	LOAD(%)					
Ta(°C)	Ta(°C)	MOUNTING A,B,C,D					
		85V	90V~				
-10 ~+40	-10 ~+50	80	100				
71	71	40	50				



## **TDK-Lambda**

#### DA032-01-03/HD-A



==NOTES==

\*1. Input voltage : Not gradual start up.

\*2. No condensing.

DA032-01-04/HD-A

#### POWER SUPPLY MOUNTING FOR MIL-STD

When MIL vibration(MIL-STD-810F 514.5 Category 4 figure 514.5C-1, Category 10) & MIL shock(MIL-STD-810F 516.5 Procedure I) specification is necessary, mount the power supply using the BRACKET or equivalent.

Fix one set of BRACKET to the power supply with sixteen M4 screws when mounting the power supply.

Two pieces of BRACKET is considered as one set.

The M4 screw is 8mm in length, washer and spring washer are also required.

Screw must not penetrate into power supply by more than 6mm.

