

Customer Part:

Description

- Surface mount Temperature Compensated Crystal Oscillator (TCXO) in a miniature 1.6 x 1.2mm surface mount package.
- Model IQXT-350
- Model Issue number 2

Frequency Parameters

- Frequency 26.0MHz
- Frequency Tolerance $\pm 1.50\text{ppm}$
- Tolerance Condition @ 25°C $\pm 2^\circ\text{C}$
- Frequency Stability $\pm 0.50\text{ppm}$
- Operating Temperature Range -30.00 to 85.00°C
- Ageing $\pm 1\text{ppm max per year @ } 25^\circ\text{C}$
 $\pm 3^\circ\text{C}$
- Supply Voltage Variation ($\pm 5\%$ change @ 25°C): $\pm 0.1\text{ppm max}$
- Load Variation ($\pm 10\%$ change @ 25°C): $\pm 0.1\text{ppm max}$
- IR Reflow Resistance (referred to frequency before reflow): $\pm 1\text{ppm max}$

Electrical Parameters

- Supply Voltage 1.8V $\pm 5\%$
- Current Draw 1.500mA
- Absolute Maximum Supply Voltage: -0.6V to 4.6V

Output Details

- Output Compatibility Clipped Sine
- Drive Capability 10k Ω /10pF
- Output Voltage Level: 0.8V pk-pk min
- Output: DC coupled
- Start Up Time ($V_{out} \geq 90\%V_{pk-pk}$): 2ms max

Noise Parameters

- Harmonic distortion: -5.0dBc max
- Phase Noise @ 25°C: -135dBc/Hz @ 1kHz typ

Environmental Parameters

- Storage Temperature Range: -40 to 85°C

Manufacturing Details




- Reflow Process
Preheating: 170°C $\pm 10^\circ\text{C}$ for 1 to 2 minutes.
Maximum reflow: 250°C $\pm 10^\circ\text{C}$ for 10secs.
- A DC-cut capacitor is not built in to the oscillator; a 1000pF DC-cut capacitor is therefore required in the output line.
- RoHS Terminations AuNi
- RoHS Reflow Temp Maximum reflow: 250°C $\pm 10^\circ\text{C}$ for

Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details

- Pack Style: Reel Tape and reel in accordance with
- Pack Size: 5,000 EIA-481-D

Outline (mm)

Pad Connections

1. GND
2. GND
3. Output
4. +Vs

Solder Pad Layout

Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1 760 668 8935

 Email: info@iqdfrequencyproducts.com

 Web: www.iqdfrequencyproducts.com



TCXO Specification

Part No. + Packaging: *LFTCXO073004Reel*

Customer Part:

- *Alternative packing option available*

Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1 760 668 8935

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com