

SERIES: VMS-450B-CFS | **DESCRIPTION:** AC-DC POWER SUPPLY
FEATURES

- up to 450 W continuous power
- universal input voltage range
- power factor correction
- 12 Vdc Fan output
- 5 Vdc AUX output
- certified to IEC/EN/UL 60601-1
- over voltage, over current, over temperature and short circuit protections



MODEL	output voltage	output current	output power	ripple and noise ¹	efficiency
	(Vdc)	max (A)	max (W)	max (mVp-p)	typ (%)
VMS-450B-12	12	37.5	450	240	89
VMS-450B-15	15	30.0	450	225	89
VMS-450B-19	19	23.7	450	190	91
VMS-450B-24	24	18.8	450	240	91
VMS-450B-36	36	12.5	450	360	90
VMS-450B-48	48	9.4	450	480	91
VMS-450B-54	54	8.3	450	540	92
VMS-450B-56	56	8.0	450	560	92

Notes: 1. Ripple and noise is measured with 20 MHz bandwidth with a 0.1 μ F ceramic capacitor and a low ESR 47 μ F electrolytic capacitor at output connector terminals.

PART NUMBER KEY

VMS - 450B - XX - CFS

Base Number

Output Voltage

CFS = enclosed with side fan

INPUT

parameter	conditions/description	min	typ	max	units
voltage		90	100~240	264	Vac
frequency		47	50~60	63	Hz
current	at 115 Vac, full load at 230 Vac, full load		5.3 2.2		A A
inrush current	at 230 Vac, cold start at 25 °C, full load			100	A
power factor	at full load	0.9			

OUTPUT

parameter	conditions/description	min	typ	max	units
regulation			±5		%
fan drive	12 Vdc / 600 mA for external fan		±5		%
aux	5 Vdc / 1 A Max		±5		%
remote on/off	on: open or short to 5 V off: short to DC RTN				

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	shut down			150	%
over current protection	automatically recovers			130	%
short circuit protection	automatically recovers after short-circuit fault is removed				
over temperature protection	shut down				


SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output, one minute input to ground, one minute	4,000 1,500			Vac Vac
certified to	IEC / EN / UL 60601-1				
safety class	class I				
conducted emissions	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0				
radiated emissions	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0				
harmonic current emissions	EN 61000-3-2:2014				
voltage fluctuation and flicker	EN 61000-3-3: 2013				
ESD	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0, IEC 61000-4-2:2008				
radiated immunity	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0, IEC61000-4-3:2006+A1: 2007+A2: 2010				
EFT/Burst	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0, IEC 61000-4-4: 2012				
surge	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0, IEC 61000-4-5:2014+A1: 2017				
conducted immunity	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0, IEC 61000-4-6: 2013				
magnet field measurement	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0, IEC 61000-4-8: 2009				
voltage dips and interruptions	EN 60601-1-2:2015 and IEC 60601-1-2 ed 4.0, IEC 61000-4-11:2004+A1: 2017				
MTBF	Telcordia SR-332, 250 W, 25 °C		300,000		hrs
RoHS	yes				

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature		-20		70	°C
storage temperature		-20		80	°C
operating humidity	non-condensing	20		80	%
storage humidity	non-condensing	10		90	%

DERATING CURVE



MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	148.2 x 80 x 40.6 (5.83 x 3.15 x 1.6 inch)				mm
weight			660		g


MECHANICAL DRAWING (12 ~ 24 V models)

units: mm [inches]

CN1	
PIN	Function
1	Line
2	Neutral


Mounting holes	
FG	Ground

CN2	
PIN	Function
1	VO+
2	VO+
3	VO+
4	DC RTN
5	DC RTN
6	VO+
7	VO+
8	DC RTN
9	DC RTN
10	DC RTN




Measuring the screw protrusion: limit 2.5mm

CN3	
PIN	Function
1	12 V for Fan
2	DC RTN



CN202	
PIN	Function
1	5 V for standby
2	DC RTN
3	Remote on / off



	CONNECTOR	MATE
CN 1:	JST, S2P3-VH, or equivalent	JST, VAR-2, or equivalent
CN 2:	Joint Tech, C4255WVA-F2-2X05, or equivalent	Molex, 39-01-2100, or equivalent
CN 3:	Cherng Weei, CP-W20-02, or equivalent	JST, PHR-2, or equivalent
CN 202:	Cherng Weei, CP-W20-03, or equivalent	JST, PHR-3, or equivalent

MECHANICAL DRAWING (36 ~ 56 V models)

units: mm [inches]

CN1	
PIN	Function
1	Line
2	Neutral


Mounting holes	
FG	Ground

CN2	
PIN	Function
1	VO+
2	VO+
3	DC RTN
4	DC RTN

CN3	
PIN	Function
1	12 V for Fan
2	DC RTN

CN202	
PIN	Function
1	5 V for standby
2	DC RTN
3	Remote on / off

CN4	
PIN	Function
1	sense+
2	sense- (DC RTN)



	CONNECTOR	MATE
CN 1:	JST, S2P3-VH, or equivalent	JST, VAR-2, or equivalent
CN 2:	Cherng Weei, CV-W3961-04, or equivalent	JST, VHR-4N, or equivalent
CN 3:	Cherng Weei, CP-W20-02, or equivalent	JST, PHR-2, or equivalent
CN 202:	Cherng Weei, CP-W20-03, or equivalent	JST, PHR-3, or equivalent
CN 4:	Cherng Weei, CP-W20-02, or equivalent	JST, PHR-2, or equivalent

REVISION HISTORY

rev.	description	date
1.0	initial release	02/14/2020
1.01	updated derating curve	06/15/2020
1.02	added FCC mark	07/08/2020
1.03	derating curves updated	04/20/2021
1.04	input voltage updated	01/18/2023
1.05	derating curve removed	05/23/2023
1.06	mechanical drawings updated	06/16/2023

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.