## **Data sheet**



## SITOP PSU8200/3AC/48VDC/10A

SITOP PSU8200 48 V/10 A stabilized power supply input: 400-500 V 3 AC output: 48 V DC/10 A \*Ex approval no longer available\*

Input		
type of the power supply network	3-phase AC	
supply voltage at AC		
minimum rated value	400 V	
<ul> <li>maximum rated value</li> </ul>	500 V	
• initial value	320 V	
• full-scale value	575 V	
design of input wide range input	Yes	
operating condition of the mains buffering	at Vin = 400 V	
buffering time for rated value of the output current in the event of power failure minimum	15 ms	
operating condition of the mains buffering	at Vin = 400 V	
line frequency		
• 1 rated value	50 Hz	
2 rated value	60 Hz	
line frequency	47 63 Hz	
input current		
<ul> <li>at rated input voltage 400 V</li> </ul>	1.2 A	
at rated input voltage 500 V	1 A	
current limitation of inrush current at 25 °C maximum	16 A	
I2t value maximum	0.8 A <sup>2</sup> ·s	
fuse protection type	none	
• in the feeder	Required: 3-pole connected miniature circuit breaker 6 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)	
Output		
voltage curve at output	Controlled, isolated DC voltage	
output voltage at DC rated value	48 V	
output voltage		
at output 1 at DC rated value	48 V	
relative overall tolerance of the voltage	3 %	
relative control precision of the output voltage		
on slow fluctuation of input voltage	0.1 %	
on slow fluctuation of ohm loading	0.2 %	
residual ripple		
• maximum	100 mV	
voltage peak		
maximum	200 mV	
adjustable output voltage	42 56 V	
product function output voltage adjustable	Yes	

type of output voltage setting  display version for normal operation  type of signal at output  behavior of the output voltage when switching on  response delay maximum  voltage increase time of the output voltage  maximum  output current  via potentiometer; max. 480 W  Green LED for 48 V OK  Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 48 V  No overshoot of Vout (soft start)  2.5 s  voltage increase time of the output voltage  maximum  500 ms	OK
type of signal at output  behavior of the output voltage when switching on  response delay maximum  voltage increase time of the output voltage  maximum  maximum  maximum  solution  Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 48 V  No overshoot of Vout (soft start)  2.5 s  voltage increase time of the output voltage  maximum  500 ms	OK
behavior of the output voltage when switching on response delay maximum 2.5 s  voltage increase time of the output voltage  • maximum 500 ms	OK
response delay maximum  2.5 s  voltage increase time of the output voltage  • maximum  500 ms	
voltage increase time of the output voltage  ● maximum 500 ms	
• maximum 500 ms	
output current	
40.4	
• rated value 10 A	
• rated range 0 10 A; +60 +70 °C: Derating 2%/K	
supplied active power typical 480 W	
short-term overload current	
at short-circuit during operation typical  30 A	
duration of overloading capability for excess current	
• at short-circuit during operation 25 ms	
constant overload current	
• on short-circuiting during the start-up typical 11 A	
product feature	
• bridging of equipment Yes; switchable characteristic	
number of parallel-switched equipment resources for increasing the power 2	
Efficiency	
efficiency in percent 94 %	
power loss [W]	
• at rated output voltage for rated value of the output  31 W	
current typical	
Closed-loop control	
relative control precision of the output voltage with rapid 0.1 %	
fluctuation of the input voltage by +/- 15% typical	
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	
setting time	
• load step 50 to 100% typical 0.2 ms	
● load step 100 to 50% typical 0.2 ms	
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	
setting time	
• load step 10 to 90% typical 0.2 ms	
• load step 90 to 10% typical 0.2 ms	
• maximum 10 ms	
Protection and monitoring	
design of the overvoltage protection < 60 V	
response value current limitation typical 11 A	
property of the output short-circuit proof  Yes	
design of short-circuit protection  Alternatively, constant current characteristic approx. 11 A of shutdown	or latching
enduring short circuit current RMS value	
• typical 11 A	
overcurrent overload capability in normal operation overload capability 150 % lout rated up to 5 s/min	
display version for overload and short circuit  LED yellow for "overload", LED red for "latching shutdown"	
Safety	
galvanic isolation between input and output  Yes	
<u> </u>	0-1
galvanic isolation  Safety extra low output voltage Vout according to EN 60950  operating resource protection class  Class I	U-1
leakage current	
• maximum 3.5 mA	
• typical 0.9 mA	
protection class IP IP20	
protection class IP IP20 Approvals	
protection class IP IP20	

UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
CSA approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
• cCSAus, Class 1, Division 2	No
• ATEX	No
certificate of suitability	
• IECEx	No
NEC Class 2	No
ULhazloc approval	No
FM registration	No
type of certification CB-certificate	Yes
certificate of suitability	
EAC approval	Yes
certificate of suitability shipbuilding approval	Yes
shipbuilding approval	ABS, DNV GL
Marine classification association	· ·
<ul> <li>American Bureau of Shipping Europe Ltd. (ABS)</li> </ul>	Yes
French marine classification society (BV)	No
• DNV GL	Yes
Lloyds Register of Shipping (LRS)	No
Nippon Kaiji Kyokai (NK)	No
EMC	
standard	
for emitted interference	EN 55022 Class B
for mains harmonics limitation	EN 61000-3-2
for interference immunity	EN 61000-6-2
,	EN 01000-0-2
environmental conditions	
ambient temperature	25 170 °C) with natural convention
during operation	-25 +70 °C; with natural convection
during transport	-40 +85 °C
during storage	-40 +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 95% no condensation
Mechanics	
type of electrical connection	screw-type terminals
at input	L1, L2, L3, PE: 1 screw terminal each for 0.2 4 mm <sup>2</sup> single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.2 4 mm <sup>2</sup>
for auxiliary contacts	13, 14 (alarm signal): 1 screw terminal each for 0.14 1.5 mm²; 15, 16 (Remote): 1 screw terminal each for 0.14 1.5 mm²
width of the enclosure	70 mm
height of the enclosure	125 mm
depth of the enclosure	125 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
net weight	1.2 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

