
# **mole**x

# PRODUCT SPECIFICATION



**SERIES 71308** 

## **C-GRID® SMT** .100" GRID DUAL ROW HEADERS **SERIES 71308**

- 1.0 **SCOPE**
- 2.0 PRDUCT DESCRIPTION
  - PRODUCT NAME AND SERIES NUMBERS
  - 2.2 **DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS**
  - **SAFETY AGENCY APPROVALS** 2.3
- 3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS
  - **MOLEX DOCUMENTS** 3.1
  - 3.2 **OTHER DOCUMENTS**
- 4.0 **RATINGS** 
  - 4.1 **VOLTAGE**
  - 4.2 **CURRENT**
  - 4.3 **TEMPERATURE**
- 5.0 **PERFORMANCE** 
  - 5.1 **ELECTRICAL REQUIREMENTS**
  - 5.2 **MECHANICAL REQUIREMENTS**
  - 5.3 **ENVIRONMENTAL REQUIREMENTS**
- **PACKAGING** 6.0

D5	ECR/ECN INFORMATION: EC No: UCP2013-0050  DATE: 2012/07/09		RID VERTICAL DU SURFACE MOUN HEADERS		1 of 4
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:	
PS-71308		MMSTROH	MKIPPER	FSMITH	
TEMPLATE FILENAME: PRODUCT SPECISIZE AIV. 1). DOC					

## PRODUCT SPECIFICATION

## 1.0 SCOPE:

**mole**x

This specification covers C-Grid® dual row surface mount headers. They utilize a gull wing design for surface mounting. The mating pins are .025in (0.64mm) square on a .100in (2.54mm) grid.

#### 2.0 PRODUCT DESCRIPTION:

## 2.1 PRODUCT NAME AND SERIES NUMBER(S)

2.1.1 SERIES 71308: Low profile vertical surface mount header.

### **DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS**

C-Grid® series 71308 is available in circuit sizes of 4 through 100 circuits and is end to end stackable. The wafer is made from glass filled Liquid Crystal Polymer, (LCP) having a UL 94V-0 flammability rating. Mating pin lengths are .240in (6.0mm), and .320in (8.1mm) with gold or tin plating. Integral mounting pegs are offered in two lengths for each series as an option to aid assembly and/or retention during soldering. For further details, refer to sales document in section 3.1.

### 2.2 SAFETY AGENCY APPROVALS

- 2.2.1 UNDERWRITERS' LABORATORIES (UL) FILE NUMBER: E29179
- 2.2.2 CANADIAN STANDARDS ASSOCIATION (CSA) FILE NUMBER: LR19980

### 3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

#### 3.1 MOLEX DOCUMENTS

SD--71308-001 SALES DRAWING FOR LOW PROFILE C-GRID® SMT HEADER PK-70873-0353 PACKAGING SPECIFICATION FOR BULK PACKAGED PRODUCT (CIRCUIT SIZES 4-8)

713080000-PK PACKAGING SPECIFICATION FOR TAPE AND REEL ALL

**OPTIONS** 

713080001-PK PACKAGING SPECIFICATION FOR TUBE PACK 6.1 MATE WITH

OR WITHOUT PEGS NO CAPS

713080002-PK PACKAGING SPECIFICATION FOR TUBE PACK 6.1 MATE WITH

OR WITHOUT PEGS WITH CAPS

713080003-PK PACKAGING SPECIFICATION FOR TUBE PACK 8.0 -11.0 MATE

WITH OR WITHOUT SHORT PEGS WITH CAPS

PS-45499-002 COSMETIC SPECIFICATION

#### 3.2 OTHER DOCUMENTS

MIL STD 202F

#### 4.0 RATINGS

4.1 VOLTAGE: 250 Volts DC

**4.2 CURRENT:** 3.0 Amps (DC) max

4.3 TEMPERATURE

4.3.1 PROCESSING TEMPERATURE: 245°C max. intermittent for bright tin plating

260°C max. intermittent for select gold plating.

4.3.2 OPERATING TEMPERATURE: -40°C to +120°C


ROW	SURFACE MOUN HEADERS	Т	<b>2</b> of <b>4</b>
CREATED / REVISED BY:	D BY: CHECKED BY: APPROVED BY		/ED BY:
MMSTROH	MKIPPER	FSM	ITH
_	CREATED / REVISED BY:	HEADERS  CREATED / REVISED BY: CHECKED BY:	CREATED / REVISED BY: CHECKED BY: APPROV

TEMPLATE FILENAME: PRODUCT\_SPEC[SIZE\_A](V.1).DOC

# **mole**x®

# PRODUCT SPECIFICATION

#### 4.4 **REFLOW SOLDERING PROFILE \***



Description	Requirement
Average Ramp Rate	3°C/sec Max
Preheat Temperature	150°C Min to 200°C Max
Preheat Time	60 to 180 sec
Ramp to Peak	3°C/sec Max
Time over Liquidus (217°C)	60 to 150 sec
Peak Temperature	260 +0/-5°C
Time within 5°C of Peak	20 to 40 sec
Ramp - Cool Down	6°C/sec Max
Time 25°C to Peak	8 min Max

NOTE: Reflow soldering profile for select gold plating and Reflow tin plating

REVISION: <b>D5</b>	ECR/ECN INFORMATION: EC No: <b>UCP2013-0050</b>	.100" GRID VERTICAL DUAL ROW SURFACE MOUNT		3 of 4	
DS	DATE: <b>2012/07/09</b>	HEADERS			
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:	
PS-71308		MMSTROH	MKIPPER	FSM	ITH
TEMPI ATE FILENAME: PRODUCT SPECISIZE AVV 1) DOC					

# **mole**x

## PRODUCT SPECIFICATION

#### 5.0 **PERFORMANCE**

- **ELECTRICAL REQUIREMENTS** 
  - 5.1.1 INSULATION RESISTANCE: Greater than 1000MΩ
  - 5.1.2 DIELECTRIC WITHSTANDING VOLTAGE: Greater than 600Volts at sea level.
  - 5.1.3 TEMPERATURE RISE: 30°C max at rated current
- 5.2 **MECHANICAL REQUIREMENTS** 
  - 5.2.1 RETENTION PEGS (Optional Item)
    - INSERTION FORCE: 8.0 lbs average per peg (.062in PCB hole) 5.2.1.1
    - RETENTION FORCE: 4.0 lbs average per peg (.062in PCB hole) 5.2.1.2
- **ENVIRONMENTAL REQUIREMENTS** 5.3
  - THERMAL SHOCK 5.3.1
    - 10 Cycles from -40°C to105°C, ½ hour at each temperature setting.
  - 5.3.2 CHEMICAL RESISTANCE

Per Mil. Std. 202F, Method 215A.

#### 5.4 **ENVIRONMENTAL PERFORMANCE**

DESCRIPTION	TEST CONDITION	REQUIREMENT
5.4.1 Solderability	Steam age 8 hours +/- 15 min Solder Time: 5 ± 0.5 sec. Solder Temperature: 245 ±5 °C	Solder tail should have 95% continuous new solder coating coverage

#### 6.0 **PACKAGING**

DEVISION: ECD/ECN INFORMATION: TITLE:

Product is available in bulk pack, tube pack and tape and reel. Tape and reel packaging include a pick-n-place cap, ideal for high volume robotic placement. The pick-n-place cap is optional for tube packaged product. Refer to section 3.1 for applicable packaging document.

D5	EC No: UCP2013-0050  DATE: 2012/07/09	ROW SURFACE MOUNT HEADERS		4 of 4	
DOCUMENT NUMBER:		CREATED / REVISED BY:	ISED BY: CHECKED BY: APPROVED B		
PS-71308		MMSTROH	MKIPPER  TEMPI ATE EII ENA	FSM	

CHEET NO