SIEMENS

Data sheet 3RM1107-2AA04



Fail-safe direct starter, 3RM1, 500 V, 0.55 - 3 kW, 1.6 - 7 A, 24 V DC, spring-type terminals

product category product designation	Motor starter
product designation	
	Fail-safe direct starter
design of the product	With electronic overload protection and safety-related disconnection
product type designation	3RM1
General technical data	
trip class	CLASS 10A
equipment variant according to IEC 60947-4-2	3
product function	fail-safe direct starter
 intrinsic device protection 	Yes
 for power supply reverse polarity protection 	Yes
suitability for operation device connector 3ZY12	Yes
insulation voltage rated value	500 V
overvoltage category	III
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
 between main and auxiliary circuit 	500 V
 between control and auxiliary circuit 	250 V
shock resistance	6g / 11 ms
vibration resistance	1 6 Hz, 15 mm; 20 m/s², 500 Hz
operating frequency maximum	1 1/s
mechanical service life (switching cycles) typical	15 000 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	03/01/2017
product function	
direct start	Yes
reverse starting	No
product function short circuit protection	No
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	Class A
conducted interference	
 due to burst according to IEC 61000-4-4 	3 kV / 5 kHz
 due to conductor-earth surge according to IEC 61000-4-5 	4 kV signal lines 2 kV
 due to conductor-conductor surge according to IEC 61000-4-5 	2 kV
	10 V
 due to high-frequency radiation according to IEC 61000-4-6 	

electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
conducted HF interference emissions according to	Class B for the domestic, business and commercial environments
CISPR11	
field-bound HF interference emission according to CISPR11	Class B for the domestic, business and commercial environments
Safety related data	
safety device type according to IEC 61508-2	Туре В
Safety Integrity Level (SIL) according to IEC 61508	3
SIL Claim Limit (subsystem) according to EN 62061	SILCL 3
performance level (PL) according to EN ISO 13849-1	е
category according to EN ISO 13849-1	4
stop category according to EN 60204-1	0
Safe failure fraction (SFF)	99.4 %
average diagnostic coverage level (DCavg)	99 %
diagnostics test interval by internal test function maximum	600 s
function test interval maximum	1 y
failure rate [FIT]	T y
 at rate of recognizable hazardous failures (λdd) 	1 400 FIT
 at rate of recognizable flazardous failures (λdu) at rate of non-recognizable hazardous failures (λdu) 	16 FIT
PFHD with high demand rate according to EN 62061	0.00000002 1/h
PFDavg with low demand rate according to EN 02001	0.000018
MTTFd	75 y
hardware fault tolerance according to IEC 61508	1
safe state	Load circuit open
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe
hardware fault tolerance according to IEC 61508 relating to ATEX	0
PFDavg with low demand rate according to IEC 61508 relating to ATEX	0.0005
PFHD with high demand rate according to EN 62061 relating to ATEX	0.00000005 1/h
Safety Integrity Level (SIL) according to IEC 61508 relating to ATEX	SIL2
T1 value for proof test interval or service life according to IEC 61508 relating to ATEX	3 y
Main circuit	
number of poles for main current circuit	3
design of the switching contact	Hybrid
adjustable current response value current of the current-dependent overload release	1.6 7 A
minimum load [%]	20 %; from set rated current
type of the motor protection	solid-state
operating voltage rated value	48 500 V
relative symmetrical tolerance of the operating voltage	10 %
operating frequency 1 rated value	50 Hz
operating frequency 2 rated value	60 Hz
relative symmetrical tolerance of the operating frequency	10 %
operational current	
at AC at 400 V rated value	7 A
• at AC-3 at 400 V rated value	7 A
 at AC-53a at 400 V at ambient temperature 40 °C rated value 	7 A
ampacity when starting maximum	56 A
operating power for 3-phase motors at 400 V at 50 Hz	0.55 3 kW
derating temperature	40 °C
nputs/ Outputs	
input voltage at digital input	04.1/
at DC rated value	24 V

with signal <0> at DC	0 5 V
• for signal <1> at DC	15 30
input current at digital input	
for signal <1> at DC	8 mA
• with signal <0> at DC	1 mA
number of CO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15 at 230 V maximum	3 A
operational current of auxiliary contacts at DC-13 at 24 V maximum	1 A
Control circuit/ Control	
type of voltage of the control supply voltage	DC
control supply voltage at DC rated value	19.2 30 V
relative negative tolerance of the control supply voltage at DC	20 %
relative positive tolerance of the control supply voltage at DC	25 %
control supply voltage 1 at DC rated value	24 V
operating range factor control supply voltage rated value at DC	
• initial value	0.8
• full-scale value	1.25
control current at DC	
in standby mode of operation	13 mA
when switching on	150 mA
during operation	57 mA
inrush current peak	
• at DC at 24 V	300 mA
at DC at 24 V at switching on of motor	130 mA
duration of inrush current peak	100 110 1
• at DC at 24 V	80 ms
	20 ms
at DC at 24 V at switching on of motor power loss [W] in auxiliary and control circuit	
in switching state OFF with bypass circuit.	0.35 W
— with bypass circuit	0.35 W
in switching state ON with hypers circuit.	4 27 14/
— with bypass circuit	1.37 W
Response times	
ON-delay time	65 76 ms
OFF-delay time	30 43 ms
Power Electronics	
operational current	
 at 40 °C rated value 	7 A
• at 50 °C rated value	6.1 A
• at 55 °C rated value	5.2 A
at 60 °C rated value	4.6 A
Installation/ mounting/ dimensions	
mounting position	vertical, horizontal, standing (observe derating)
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
height	100 mm
width	22.5 mm
depth	141.6 mm
required spacing	
with side-by-side mounting	
— forwards	0 mm
— backwards	0 mm
— upwards	50 mm
— downwards	50 mm
— at the side	0 mm
for grounded parts	• ·····
— forwards	0 mm
— IOI Walus	U IIIIII

— backwards	0 mm
— upwards	50 mm
— at the side	3.5 mm
— downwards	50 mm
Ambient conditions	
installation altitude at height above sea level maximum	4 000 m; For derating see manual
ambient temperature	
during operation	-25 +60 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
environmental category during operation according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
relative humidity during operation	10 95 %
air pressure according to SN 31205	900 1 060 hPa
Communication/ Protocol	
protocol is supported	N-
PROFINET IO protocol PROFINET PROTOCOL	No No
PROFIsafe protocol product function bus communication	No No
product function bus communication protocol is supported AS-Interface protocol	No No
Connections/ Terminals	110
	spring-loaded terminals (push-in) for main circuit, spring-loaded
type of electrical connection	terminals (push-in) for control circuit
for main current circuit	spring-loaded terminals (push-in)
 for auxiliary and control circuit 	spring-loaded terminals (push-in)
wire length for motor unshielded maximum	100 m
type of connectable conductor cross-sections	
 for main contacts 	
— solid	1x (0.5 4 mm²)
 finely stranded with core end processing 	1x (0.5 2.5 mm²)
 finely stranded without core end processing 	1x (0.5 4 mm²)
at AWG cables for main contacts	1x (20 12)
connectable conductor cross-section for main contacts	
 solid or stranded 	0.5 4 mm²
finely stranded with core end processing	0.5 2.5 mm ²
finely stranded without core end processing	0.5 4 mm²
connectable conductor cross-section for auxiliary contacts	
solid or stranded	0.5 1.5 mm ²
finely stranded with core end processing	0.5 1 mm²
finely stranded without core end processing	0.5 1.5 mm²
type of connectable conductor cross-sections	
for auxiliary contacts	1x (0.5 1.5 mm²), 2x (0.5 1.5 mm²)
— solid— finely stranded with core end processing	1x (0.5 1.5 mm²), 2x (0.5 1.5 mm²) 1x (0,5 1,0 mm²), 2x (0,5 1,0 mm²)
— finely stranded with core end processing — finely stranded without core end processing	1x (0.5 1.0 mm²), 2x (0.5 1.0 mm²) 1x (0.5 1.5 mm²), 2x (0.5 1.5 mm²)
at AWG cables for auxiliary contacts	1x (20 16), 2x (20 16)
AWG number as coded connectable conductor cross section	7X (20 10), 2X (20 10)
for main contacts	20 12
for auxiliary contacts	20 16
UL/CSA ratings	
yielded mechanical performance [hp]	
for single-phase AC motor	
— at 110/120 V rated value	0.25 hp
— at 230 V rated value	0.5 hp
 for 3-phase AC motor 	
 at 200/208 V rated value 	1 hp
— at 220/230 V rated value	1.5 hp
— at 460/480 V rated value	3 hp

operating voltage at AC

- according to UL rated value
- according to CSA rated value

480 V 400 V

Certificates/ approvals

General Product Approval

EMC



Confirmation









For use in hazardous locations

Functional Safety/Safety of Machinery

Declaration of Conformity

Test Certificates

other

Railway



Type Examination Certificate



Type Test Certificates/Test Report

Confirmation

Special Test Certific-<u>ate</u>

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RM1107-2AA04

Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RM1107-2AA04


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RM1107-2AA04

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RM1107-2AA04&lang=en





last modified: 6/21/2022 🖸