
OPERATING CHARACTERISTICS AT 25°C AMBIENT							ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT									
DIALIGHT PART NUMBER	COLOR		TY(mcd)	FORW VOLTA © <sup>01</sup> F <sup>=</sup>	GE(V)	REVERSE CURRENT (mA) @V <sub>R</sub> = 5 V	DOM I WAVEL	NANT ENGTH	VIEWING ANGLE (DEG)	POWER DISS. (mW)	DC FORWARD CURRENT (mA)	ELECTRO- STATIC DISCHARGE (HBM)	REVERSE VOLTAGE (V)		OPERATING TEMP. (C)	SOLDERING TEMP. (1/10 SEC)
		MIN	MAX	MIN	MAX	MAX	MIN MAX TY	ΤΥΡ								
598-8810-302F 598-8810-307F	RED	35	100	1.8	2.4	10	630	640	160	48		1000	5			
	GREEN	200	560	2.7	3.5		515	530		68	20			-40 TO +100		
	BLUE	60	200	2.7	3.5		465	475		68						260 °C
598-8820-302F 598-8820-307F	RED-ORANGE	70	200	1.8	2.4	10	600	6   0	160	48	20 100		00 5	- 40 -	TO +100	
	GREEN	200	560	2.7	3.5		515	530		68		1000				
	BLUE	60	200	2.7	3.5		465	475		68						
598-8830-302F 598-8830-307F	YELLOW	70	200	1.8	2.4	10	587	597	160	48	20	1000	5	- 40 T	TO + 00	
	GREEN	200	560	2.7	3.5		515	530		68						
	BLUE	60	200	2.7	3.5		465	475		68						


300 -

0 -











0

LED SCHEMATICS





598-8830-307F



NOTES:

- I. LED CHIP:InGaN AND ALLnGaP 2. LEADS ARE GOLD (Au) PLATED FINISH.
- 3. PACKAGING: 8mm TAPE, 7" REEL AND 20 PCS STRIP
- 5. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND STORAGE IN ACCORDANCE WITH IPC-A-610.

- MOISTURE SENSITIVITY LEVEL 3.
  TAPE AND REEL LEDS MAY REQUIRE RE-TAPING AFTER TWELVE MONTHS.
  PIN NUMBERS FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART.

RECOMMENDED SOLDER PAD LAYOUT

REV	REVISIONS	DRN	CKD	APP	DATE
A	NEW RELEASE	ΒP	—	SK	- 5- 6
В	ADDED 302F PART NUMBERS	LD		NO	2- 9- 9
260°C-	10 sec. Max 5°C /sec.Max. Above 220°C 120 sec. Max. 150 sec Max. 90 180 240		S 30	00	

### RECOMMENDED RoHS SOLDER PROFILE

# RECOMMENDED DIMENSIONS OF TAPE AND REEL

## RoHS COMPLIANT 598-88XX-30XF

Part Numbers with the "F" suffix ending are RoHS Compliant. For example: 597-7725-60XF Packaging is marked with "RoHS Compliant" label or equivalent

markings. These parts can be used with RoHS reflow profile. Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp for 5 sec.

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.

SCALE: 15.000	DRAWING NUMBER	REV				
ALL DIM´s: INCH (mm)						
TOLERANCES: UNLESS OTHERWISE SPECIFIED	C-18301	В				
FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005	SM LED 1208 TRI COLOR					
DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	MATERIAL -					
FINISH -		E 34 SOUTH E, NJ 07727 919-3119 Light.com				
FSCM 83330	SHEET I OF I FAMILY TABLE:	- girt.com				