
AFS14A34-1588.66-T3

Moisture Sensitivity Level (MSL) = 3





FEATURES:

- 1.4 x 1.1 x 0.7 mm low profile SMT package
- Low Insertion loss
- Excellent selectivity with high out-of-band rejection

> APPLICATIONS:

- •Wireless Communication
- Remote Control
- Cellular Phones

ELECTRICAL SPECIFICATIONS:


Maximum Ratings

| Item | Value | | | |
|-----------------------------|-----------------|--|--|--|
| Input Power Level | +10 dBm max. | | | |
| DC Permissive Voltage | 3.0V DC max. | | | |
| Operating Temperature Range | -30°C to + 85°C | | | |
| Storage Temperature Range | -40°C to +85°C | | | |

| Parameters | Minimum | Typical | Maximum | Units | Notes |
|--|---------|---------|---------|--------|---------------------|
| Center Frequency (f _c) | | 1588.66 | | MHz | |
| Insertion Loss (IL) | | 1.25 | 1.70 | dB | 1573.42~1577.42 MHz |
| Insertion Loss (IL) | | 1.7 | 2.5 | dB | 1571.42~1605.89 MHz |
| Effective Bandwidth | | 34 | | MHz | |
| Amplitude Ripple | | 0.25 | 0.8 | dB | 1573.42~1577.42 MHz |
| Amplitude Ripple | | 0.7 | 1.5 | dB | 1571.42~1605.89 MHz |
| Worst-Case Input / Output Return Loss | 9.54 | 20.8 | | dB | 1573.42~1577.42 MHz |
| Worst-Case Input / Output Return Loss | 12.7 | 20.8 | | dB | 1571.42~1605.89 MHz |
| Stop-band Attenuation (Referenced to 0.0 dB) | 32 | 35 | | | D.C~824 MHz |
| | 32 | 35 | | | 824~849 MHz |
| | 32 | 34.5 | | | 849~880 MHz |
| | 32 | 34.5 | | | 880~915 MHz |
| | 30 | 34 | | dB | 915~1452 MHz |
| | 32 | 37 | | | 1452~1525 MHz |
| | 32 | 36 | | | 1710~1785 MHz |
| | 32 | 36 | | | 1785~1850 MHz |
| | 25 | 36 | | | 1850~6000 MHz |
| Temperature Coefficient of frequency | | -36 | | ppm/°C | |
| Source Impedance (Z _S) | | 50 | | Ω | See note # 1 |
| Load Impedance (Z _L) | | 50 | | Ω | See note # 1 |

Note #1: No matching network required for operation into 50Ω 's

TEST CIRCUIT:






5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 02-8-19


ABRACON IS ISO9001-2015 CERTIFIED

AFS14A34-1588.66-T3






OUTLINE DIMENSIONS:



| C: | Input |
|----------|--------|
| A: | Output |
| B, D, E: | Ground |

Recommended Land Pattern:



: Land Pattern


Unit : mm

*All Dimensions are in mm





AFS14A34-1588.66-T3






▶ FREQUENCY CHARACTERISTICS:





Filter Frequency Response (Wideband)



REFLECTION FUNCTIONS:








5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 02-8-19


ABRACON IS ISO9001-2015 CERTIFIED

AFS14A34-1588.66-T3






REFLOW PROFILE:



PACKAGING: 3000 Units/Reel "-T2" parts (2k/reel) are no longer available effective 01/01/2013



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

