

# PACT RCP-D190-10M - Coil



2910324

<https://www.phoenixcontact.com/us/products/2910324>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

600 mm long Rogowski coil. The measuring coil diameter when installed is 190 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



## Commercial data

Item number	2910324
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CK4A12
Catalog page	Page 219 (C-5-2019)
GTIN	4055626437569
Weight per piece (including packing)	401.66 g
Weight per piece (excluding packing)	395 g
Customs tariff number	90309000
Country of origin	IT

## Technical data

### Product properties

Product type	Rogowski coil
--------------	---------------

### Insulation characteristics

Pollution degree	2
------------------	---

### Electrical properties

#### Measuring coil

Conductor structure signal line	2x 0.22 mm (Signal (tinned))
	1x 0.22 mm (Shielding (tinned))
Insulation	double insulation
Rated insulation voltage	1000 V AC (rms CAT III)
	600 V AC (rms CAT IV)
Test voltage	10.45 kV DC (60 s)
Basic accuracy	<± 0.2 %

#### General

Converter type	Rogowski coil
----------------	---------------

### Input data

#### Frequency

Designation	Measuring coil
Frequency measuring range	40 Hz ... 20000 Hz
Position error	<± 0.1 % (typical)
Linearity error	< 0.1 %

#### Current transformers

Converter type	Rogowski coil
----------------	---------------

### Output data

#### Signal

Designation	Measuring coil
Output signal (at 50 Hz)	100 mV (no load, at 1,000 A)
Output voltage (in no-load operation)	$V_{OUT} = M \cdot dI/dt$
Output voltage (sinusoidal, in no-load operation)	100 mV ( $V_{OUT} = 2 \cdot \pi \cdot M \cdot f \cdot I$ (M = 0.318 µH; example: At 50 Hz; I = 1,000 A))

### Dimensions

#### Measuring coil

Length	600 mm
Diameter	8.3 mm ±0.2 mm

# PACT RCP-D190-10M - Coil



2910324

<https://www.phoenixcontact.com/us/products/2910324>

## Measuring coil when installed

Diameter	190 mm
----------	--------

## Signal line

Length	10 m
--------	------

## Material specifications

Coil material	Elastollan
Housing material	PC

## Environmental and real-life conditions

### Ambient conditions

Measuring coil degree of protection	IP67 (not assessed by UL)
Ambient temperature (operation)	-30 °C ... 80 °C (Measuring coil)
Ambient temperature (storage/transport)	-40 °C ... 80 °C (Measuring coil)
Altitude	< 2000 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

## Approvals

### UKCA

Certificate	UKCA-compliant
-------------	----------------

### CMIM

Certificate	CMIM-compliant
-------------	----------------

### UL, USA/Canada

Identification	UL 61010 Recognized
Note	Measuring coil

## Standards and regulations

Standards/regulations	IEC 61010-1
	IEC 61010-2-032

# PACT RCP-D190-10M - Coil



2910324

<https://www.phoenixcontact.com/us/products/2910324>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2910324>



**cUL Recognized**  
Approval ID: FILE E 357804



**UL Recognized**  
Approval ID: FILE E 357804

**cULus Recognized**

# PACT RCP-D190-10M - Coil



2910324

<https://www.phoenixcontact.com/us/products/2910324>

## Classifications

### ECLASS

ECLASS-11.0	27210992
ECLASS-12.0	27210992
ECLASS-13.0	27210992

### ETIM

ETIM 9.0	EC002498
----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>



## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>




## Accessories

### PACT RCP-CLAMP - Holder

2904895

<https://www.phoenixcontact.com/us/products/2904895>



The optional holding device ensures the Rogowski coil is securely seated on busbars with a thickness of 10 ... 15 mm. During installation, the coil housing is pushed onto the flange of the holding device and snaps in automatically.

---

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)