


Data sheet for SINAMICS G120X

Article No.: 6SL3220-1YE10-0AB0

Client order no. : Order no. : Offer no. : Remarks :



Overload	capabi	lity
----------	--------	------

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

 $150\%\,x$ base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.70 0.85	
Offset factor $\cos\phi$	0.96	
Efficiency η	0.96	
Sound pressure level (1m)	55 dB	
Power loss 3)	0.043 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without	
_		

Communication

Communication USS, Modbus RTU, BACnet MS/TP



Item no. : Consignment no. : Project :

Innuts	Outnuts		
Inputs / outputs Standard digital inputs			
Number	6		
Switching level: 0 → 1	11 V		
Switching level: $1 \rightarrow 0$	5 V		
Max. inrush current	15 mA		
Fail-safe digital inputs			
Number	1		
Digital outputs			
Number as relay changeover contact	2		
Output (resistive load)	DC 30 V, 5.0 A		
Number as transistor	0		
Analog / digital inputs			
Number	2 (Differential input)		
Resolution	10 bit		
Switching threshold as digital input			
0 → 1	4 V		
1 → 0	1.6 V		
Analog outputs			
Number	1 (Non-isolated output)		

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5\,^{\circ}\text{C}$

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	




Data sheet for SINAMICS G120X

Article No.: 6SL3220-1YE10-0AB0

Ambient conditions				
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002			
Cooling	Air cooling using an integrated fan			
Cooling air requirement	0.005 m³/s (0.177 ft³/s)			
Installation altitude	1,000 m (3,280.84 ft)			
Ambient temperature				
Operation	-20 45 °C (-4 113 °F)			
Transport	-40 70 °C (-40 158 °F)			
Storage	-25 55 °C (-13 131 °F)			
Relative humidity				
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible			
Conn	ections			
Signal cable				
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)			
Line side				
Version	screw-type terminal			
Conductor cross-section	1.50 2.50 mm ² (AWG 16 AWG 14)			
Motor end				
Motor end				
Motor end Version	Screw-type terminals			
	Screw-type terminals 1.50 2.50 mm² (AWG 16 AWG 14)			
Version	1.50 2.50 mm²			
Version Conductor cross-section	1.50 2.50 mm²			
Version Conductor cross-section DC link (for braking resistor)	1.50 2.50 mm ² (AWG 16 AWG 14)			

Mechanical data				
Degree of protection		IP20 / UL open type		
Frame size		FSA		
Net weight		3.4 kg (7.50 lb)		
Dimensions				
	Width	73 mm (2.87 in)		
	Height	232 mm (9.13 in)		
	Depth	218 mm (8.58 in)		
Standards				
Compliance with standards		UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH		
CE marking		EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC		





The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

 $^{^{1)}}$ The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.