

## **MLFB-Ordering data**

6SL3220-3YE56-0CF0



Client order no. : Order no. : Offer no. : Item no. : Consignment no. : Project :

Offer no. : Remarks :

Rated data		General tech. specifications		
Input			Power factor λ	0.75 0.93
Number of phases	3 AC		Offset factor cos φ	0.96
Line voltage	380 480 V	+10 % -10 %	Efficiency η	0.98
Line frequency	47 63 Hz		Sound pressure level (1m)	74 dB
Rated voltage	400V IEC	480V NEC	Power loss	6.791 kW
Rated current (LO)	597.00 A	486.00 A	Filter class (integrated)	RFI suppression filter for Category C3
Rated current (HO)	477.00 A	397.00 A		
Output			EMC category (with accessories)	Category C3
Number of phases	3 AC		Ahia.at	
Rated voltage	400V IEC	480V NEC	Ambient	conditions
Rated power (LO)	315.00 kW	400.00 hp	Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002
Rated power (HO)	250.00 kW	300.00 hp		
Rated current (LO)	570.00 A	477.00 A	Cooling	Air cooling using an integrated fan
Rated current (HO)	477.00 A	390.00 A		0.262 31 (42.704631)
Rated current (IN)	585.00 A		Cooling air requirement	0.362 m³/s (12.784 ft³/s)
Max. output current	770.00 A		Installation altitude	1000 m (3280.84 ft)
Pulse frequency	4 kHz		Ambient temperature	
Output frequency for vector control	0 100 Hz		Operation	0 45 °C (32 113 °F)
			Transport	-40 70 °C (-40 158 °F)
Output frequency for V/f control	0 100 Hz		Storage	-25 55 °C (-13 131 °F)
			Relative humidity	
			Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible

### **Overload capability**

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time



### **MLFB-Ordering data**

#### 6SL3220-3YE56-0CF0



			Figure simila		
Mechanical data		Closed-loop contr	Closed-loop control techniques		
Degree of protection	IP20 / UL open type	V/f linear / square-law / parameterizak	<b>ole</b> Yes		
Size	FSH				
Net weight	151 kg (332.90 lb)	V/f with flux current control (FCC)	Yes		
Width	548 mm (21.57 in)	V/f ECO linear / square-law	Yes		
Height	1695 mm (66.73 in)	Sensorless vector control	Yes		
Depth	393 mm (15.47 in)	Vector control, with sensor	No		
Inputs / out	puts	Encoderless torque control	Yes		
Standard digital inputs		Torque control, with encoder	No		
Number	6	Communication			
Switching level: 0→1	11 V				
Switching level: 1→0	5 V				
Max. inrush current	15 mA	Connections			
Fail-safe digital inputs		Signal cable			
Number	1	I OUGHICTOR CROSS-SOCTION	.15 1.50 mm² AWG 24 AWG 16)		
Digital outputs		Line side			
Number as relay changeover contact	2	Version N	112 screw		
Output (resistive load)	DC 30 V, 5.0 A		40.00 mm² MCM 2 x 500 MCM 4 x 500)		
Number as transistor	0	Motor end			
Analog / digital inputs		Version M	112 screw		
Number	2 (Differential input)		40.00 mm² MCM 2 x 500 MCM 4 x 500)		
Resolution	10 bit	DC link (for braking resistor)	MCM 2 X 300 MCM 1 X 300,		
Switching threshold as digital in	out		112 screw		
0→1	4 V	Max. motor cable length	IIZ SCIEVV		
1→0	1.6 V	_	50 m (492.13 ft)		
Analog outputs		Siliciaca	55 m (152.15 m)		

# PTC/ KTY interface

Number

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy  $\pm 5~^{\circ}\text{C}$ 

1 (Non-isolated output)




### **MLFB-Ordering data**

#### 6SL3220-3YE56-0CF0



Converter	losses to	EN	50598-2*
-----------	-----------	----	----------

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-39.30 %



Standards

Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

CE marking EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

# Operator panel: Intelligent Operator Panel (IOP-2)

S	creen	Ambie	ent conditions
Display design	LCD colors	Ambient temperature durin	g
		Operation	0 50 °C (32 122 °F)
Screen resolution	320 x 240 Pixel		55 °C only with door mounting kit
Mech	anical data	Storage	-40 70 °C (-40 158 °F)
Degree of protection	IP55 / UL type 12	Transport	-40 70 °C (-40 158 °F)
Net weight	0.13 kg (0.30 lb)	Relative humidity at 25°C di	uring
Width	70.0 mm (2.76 in)	Max. operation	95 %
Height	106.85 mm (4.21 in)		
Depth	19.65 mm (0.77 in)	Approvals	
<b>r</b>		Certificate of suitability	CE, cULus, EAC, KCC, RCM

<sup>\*</sup>converted values