



20V P-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

V _{(BR)DSS}	$R_{DS(ON) max}$	Package	I _{D max} T _A = +25°C	
-20V	$60m\Omega @ V_{GS} = -4.5V$	SOT-23	-4.0A	
-200	$90m\Omega @ V_{GS} = -2.5V$	501-23	-3.3A	

Description and Applications

This new generation MOSFET is designed to minimize the on-state resistance ($R_{DS(on)}$) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Features


- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen- and Antimony-Free. "Green" Device (Note 3)
- The DMP2065UQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Case: SOT23
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Solderable per MIL-STD-202, Method 208 3
- Lead-Free Plating (Matte Tin Finish Annealed over Alloy 42 Lead-Frame).
- Terminal Connections: See Diagram
- Weight: 0.006 grams (Approximate)





Pin Configuration



Equivalent Circuit

Ordering Information (Note 4)

Top View

Part Number	Case	Packaging
DMP2065UQ-7	SOT23	3000/Tape & Reel
DMP2065UQ-13	SOT23	10,000/Tape & Reel

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

Notes:

Date Code Key			65U	MX	= M <u>Y</u> M Y = `	= Product 1 Date Code Year (ex: H Month (ex: 1	e Marking = 2020)	-				
Year	202	0	2021		2022	20	23	2024		2025	2	2026
Code	Н				J		〈	L		М		Ν
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Maximum Ratings (@ T_A = +25°C unless otherwise specified.)

Characteristi	•		Symbol	Value	Units
Drain-Source Voltage			V _{DSS}	-20	V
Gate-Source Voltage		V _{GSS}	±12	V	
Drain Current (Note 6) Vgs= -4.5V	T _A = +25°C T _A = +70°C	ID	-4.0 -3.0	A	
Pulsed Drain Current (Pulse width ≤10µS, Du	y Cycle ≤1%)		IDM	-15	А

Thermal Characteristics

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)		PD	0.9	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	$R_{ ext{ heta}JA}$	138	°C/W
Total Power Dissipation (Note 6)		PD	1.5	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{ ext{ heta}JA}$	83	°C/W
Operating and Storage Temperature Range		T _{J,} T _{STG}	-55 to +150	°C

Electrical Characteristics (@ T_A = +25°C unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)						
Drain-Source Breakdown Voltage	BV _{DSS}	-20	_	_	V	$V_{GS} = 0V, I_D = -250\mu A$
Zero Gate Voltage Drain Current $T_J = +25^{\circ}C$	I _{DSS}	_		-1.0	μA	$V_{DS} = -20V, V_{GS} = 0V$
Gate-Source Leakage	I _{GSS}	_	_	±50	nA	$V_{GS} = \pm 8V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	V _{GS(th)}	-0.5		-0.9	V	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$
			41	60		V _{GS} = -4.5V, I _D = -4.2A
Static Drain-Source On-Resistance	R _{DS (ON)}	—	53	90	mΩ	$V_{GS} = -2.5V, I_D = -3.4A$
			72	113		V _{GS} = -1.8V, I _D = -2.0A
Diode Forward Voltage	V _{SD}	_	-0.7	-1.1	V	$V_{GS} = 0V, I_{S} = -1A$
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	Ciss	—	808		pF	
Output Capacitance		_	85		pF	─V _{DS} = -15V, V _{GS} = 0V ─f = 1.0MHz
Reverse Transfer Capacitance	Crss	_	77	—	pF	
Gate Resistance	R _G	_	15.2	_	Ω	$V_{GS} = 0V, V_{DS} = 0V, f = 1.0MHz$
Total Gate Charge	Qg	_	10.2	_	nC	
Gate-Source Charge	Q _{gs}	_	1.3	_	nC	$V_{GS} = -4.5V, V_{DS} = -4V, I_{D} = -3.5A$
Gate-Drain Charge	Q _{gd}	_	2.2		nC	
Turn-On Delay Time	t _{D(on)}		10.8		ns	
Turn-On Rise Time	tr	_	13.7		ns	$V_{DS} = -4V, V_{GS} = -4.5V,$
Turn-Off Delay Time	t _{D(off)}	_	79.3		ns	$R_L = 4\Omega, R_G = 6\Omega, I_D = -1A$
Turn-Off Fall Time	t _f		34.7		ns	

Notes:

5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.


6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1in. square copper plate.


7. Short duration pulse test used to minimize self-heating effect.

8. Guaranteed by design. Not subject to production testing.


DMP2065UQ















DMP2065UQ Document number: DS42542 Rev. 2 - 2








Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



	SOT23							
Dim	Min	Max	Тур					
Α	0.37	0.51	0.40					
В	1.20	1.40	1.30					
С	2.30	2.50	2.40					
D	0.89	1.03	0.915					
F	0.45	0.60	0.535					
G	1.78	2.05	1.83					
Н	2.80	3.00	2.90					
J	0.013	0.10	0.05					
ĸ	0.890	1.00	0.975					
K1	0.903	1.10	1.025					
L	0.45	0.61	0.55					
L1	0.25	0.55	0.40					
М	0.085	0.150	0.110					
а	0°	8°						
All	All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT23

Dimensions	Value (in mm)			
С	2.0			
Х	0.8			
X1	1.35			
Y	0.9			
Y1	2.9			

SOT23



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com