# SIEMENS

Data sheet for SINAMICS G120X

### Article No. :

### 6SL3230-1YH32-0UF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rate	d data	
Input		
Number of phases	3 AC	
Line voltage	500 690 V +10 9	% -20 %
Line frequency	47 63 Hz	
Rated voltage	690V IEC	600V NEC
Rated current (LO)	25.00 A	25.00 A
Rated current (HO)	23.40 A	23.40 A
Output		
Number of phases	3 AC	
Rated voltage	690V IEC	600V NEC <sup>1)</sup>
Rated power (LO)	22.00 kW	25.00 hp
Rated power (HO)	18.50 kW	20.00 hp
Rated current (LO)	27.00 A	27.00 A
Rated current (HO)	23.00 A	23.00 A
Rated current (IN)	28.00 A	
Max. output current	37.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Overlaged equability		

### **Overload capability**

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech	a. specifications
Power factor $\lambda$	0.90 0.95
Offset factor $\cos \phi$	0.99
Efficiency η	0.98
Sound pressure level (1m)	70 dB
Power loss 3)	0.617 kW
Filter class (integrated)	Unfiltered
EMC category (with accessories)	without
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)
Comm	unication

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Inputs /	outputs
Standard digital inputs	
Number	6
Switching level: $0 \rightarrow 1$	11 V
Switching level: $1 \rightarrow 0$	5 V
Max. inrush current	15 mA
Fail-safe digital inputs	
Number	1
Digital outputs	
Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0
Analog / digital inputs	
Number	2 (Differential input)
Resolution	10 bit
Switching threshold as digital input	
0 → 1	4 V
$1 \rightarrow 0$	1.6 V
Analog outputs	
Number	1 (Non-isolated output)
PTC/ KTY interface	
1 motor temperature sensor input, ser Thermo-Click, accuracy ±5 °C	nsors that can be connected PTC, KTY and

Closed-loop cor	ntrol techniques
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

# SIEMENS

## Data sheet for SINAMICS G120X

### Article No. :

### 6SL3230-1YH32-0UF0

Ambier	nt conditions
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.055 m³/s (1.942 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Con	inections
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)
Motor end	
Version	Screw-type terminals
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)
DC link (for braking resistor)	
PE connection	Screw-type terminals
Max. motor cable length	
Shielded	200 m (656.17 ft)
Unshielded	300 m (984.25 ft)

Me	chanical data	
Degree of protection	IP20 / UL open	type
Frame size	FSD	
Net weight	16.6 kg (36.60	) lb)
Dimensions		
Width	200 mm (7.87	in)
Height	472 mm (18.5	8 in)
Depth	248 mm (9.76	in)
	Standards	
Compliance with standards	UL, cUL, CE, C- SEMI F47, REA	Tick (RCM), EAC, KCC, CH
CE marking	EMC Directive Voltage Direct	2004/108/EC, Low- ive 2006/95/EC
Converter lo	osses to IEC61800-	9-2*
Converter lo	USSES to IEC61800-	9-2*
		9-2*
Efficiency class Comparison with the reference	IE2	9-2*
Efficiency class Comparison with the reference	IE2	9-2* 614.0 W (1.9 %)
Efficiency class Comparison with the reference converter (90% / 100%)	IE2 39.0 %	
Efficiency class Comparison with the reference converter (90% / 100%)	IE2 39.0 %	
Efficiency class Comparison with the reference converter (90% / 100%)	IE2 39.0 %	
Efficiency class Comparison with the reference converter (90% / 100%) 501.0 W (1.6 %) 100%	IE2 39.0 %	
Efficiency class Comparison with the reference converter (90% / 100%) 501.0 W (1.6 %)	IE2 39.0 %	● 614.0 W (1.9 %)
Efficiency class Comparison with the reference converter (90% / 100%) 501.0 W (1.6 %) 100%	IE2 39.0 %	● 614.0 W (1.9 %)

The percentage values show the losses in relation to the rated apparent power of the converter.

90% **f** 

50%

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 550V-600V

<sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.