


Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YE16-0AB0

Client order no. : Order no. : Offer no. : Remarks :



Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

Communication

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.70 0.85	
Offset factor $\cos\phi$	0.96	
Efficiency η	0.97	
Sound pressure level (1m)	55 dB	
Power loss 3)	0.091 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without	

Communication

Item no. : Consignment no. : Project :



Figure similar

Inputs /	outputs	
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTV interface		

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5\,^{\circ}\text{C}$

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

USS, Modbus RTU, BACnet MS/TP




Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YE16-0AB0

Ambient conditions	
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.005 m ³ /s (0.177 ft ³ /s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Connections	
Signal cable	
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	1.50 2.50 mm ² (AWG 16 AWG 14)
Motor end	
Version	Screw-type terminals
	4.50 0.50 3
Conductor cross-section	1.50 2.50 mm² (AWG 16 AWG 14)
Conductor cross-section DC link (for braking resistor)	
DC link (for braking resistor)	(AWG 16 AWG 14)
DC link (for braking resistor) PE connection	(AWG 16 AWG 14)

Mechanical data			
Degree of prot	ection	IP20 / UL open type	
Frame size		FSA	
Net weight		3.4 kg (7.50 lb)	
Dimensions			
Width		73 mm (2.87 in)	
Height		232 mm (9.13 in)	
Depth		218 mm (8.58 in)	
Standards			
Compliance w	ith standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking		EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	33.3 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

 $^{^{1)}}$ The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YE16-0AB0

	Operator pane	l: Basic Operator Panel (BOP-2)
	Screen	
Display design	LCD, monochrome	Ambient temperature
	Mechanical data	Operation
Degree of protection	IP55 / UL type 12	Storage
Net weight	0.140 kg (0.31 lb)	Transport Relative humidity at 25
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	iviax. Operation
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	Certificate of suitability

Ambient conditions Ambient temperature		
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	