EXLA1V04

Automotive high current molded inductor





Product features

- · High current carrying capacity
- AEC-Q200 qualified
- Low DCR, high efficiency
- · Magnetically shielded, low EMI
- Soft saturation
- Inductance range from 0.47 μH to 4.7 μH
- Current range from 3.5 A to 13.2 A
- 4.6 mm x 4.6 mm footprint surface mount package in a 2.1 mm height
- Alloy powder core material
- Moisture Sensitivity Level (MSL) 1

Applications

- · LED lighting
- Advanced driver assistance systems (ADAS)
- Adaptive cruise control (ACC)
- · Collision avoidance
- Infotainment and cluster electronics
- · Battery management systems (BMS)
- · Electric pumps, motor control and auxiliaries
- Powertrain control module (PCU)/Engine control module (ECM)
- Electronic Control Units (ECU)

Environmental compliance and general specifications

- Operating temperature range: -55 °C to +155 °C (ambient plus self-temperature rise)
- Storage temperature range (component): -55 °C to +155 °C
- Solder reflow temperature:
 J-STD-020 (latest revision) compliant










Product specifications

Part number ⁴	Part marking designator	OCL ¹ (µH) ± 20%	I _{rms} ² (A)	I _{sat} ³ (A)	DCR (mΩ) typical @ +25 °C	DCR (m Ω) maximum @ +25 °C
EXLA1V0402-R47-R	А	0.47	13.2	12.5	6.0	6.8
EXLA1V0402-R56-R	В	0.56	12.6	11.3	6.9	7.8
EXLA1V0402-R60-R	С	0.6	12.4	11.1	6.9	7.8
EXLA1V0402-R68-R	D	0.68	12	10.0	7.3	8.2
EXLA1V0402-R82-R	Е	0.82	11.5	9.0	8.6	9.5
EXLA1V0402-1R0-R	F	1.0	11	8.0	10.6	11.7
EXLA1V0402-1R2-R	G	1.2	9.5	7.5	12.2	13.4
EXLA1V0402-1R5-R	Н	1.5	9.1	6.7	14.4	15.8
EXLA1V0402-2R0-R	I	2.0	8.2	5.0	21.15	23.3
EXLA1V0402-2R2-R	J	2.2	8.0	4.8	21.35	23.5
EXLA1V0402-3R3-R	K	3.3	5.5	4.4	34.2	38.3
EXLA1V0402-4R7-R	L	4.7	5.1	3.5	52	57.2


- 1. Open circuit inductance (OCL) test parameters: 100 kHz, 0.1 $V_{\rm ms}$, 0.0 Adc, +25 °C
- 2. I_{max}- Heat rated current (I_{max}) will cause the part temperature rise approximately ΔT of 40 °C. Circuit design, component, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application. The part temperature (ambient + temp rise) should not exceed +155 °C under worst case operating conditions.
- 3. I_{sat}: Peak current for approximately 30% rolloff @ +25 °C
- 4. Part Number Definition: EXLA1V0402-xxx-R
 EXLA1V0402 = Product code and size
 xxx= inductance value in µH, R= decimal point,
 If no R is present then third digit equals the number of zeros
 -R suffix = RoHS compliant

Note: Rated operating voltage (across inductor) 15 V ref.


Mechanical parameters, schematic, pad layout (mm)



Recommended pad layout



Schematic



Part number	Α	В	С	D	E	F	G
EXLA1V0402-xxx-R	4.4 ± 0.20	4.4 ± 0.20	1.9 ± 0.20	3.4 ± 0.30	0.88 ± 0.20	1.6 ± 0.25	3.36 typ

Part marking

1st digit = Inductance value per the "Part marking designator" letter code in specification table

2nd digit = Revision level

V= vehicle

All soldering surfaces to be coplanar within 0.1 millimeters

Tolerances are \pm 0.3 millimeters unless stated otherwise

Dimensions of recommended PCB layout are reference only.


Pad layout tolerances are \pm 0.1 millimeters unless stated otherwise

Traces or vias underneath the inductor is not recommended.

Packaging information (mm)

Drawing not to scale

Supplied in tape and reel packaging, 3000 parts per 7" diameter reel (EIA-481 compliant)









W ± 0.30	12.00
F ± 0.10	5.50
E1 ± 0.10	1.75
E2 min	10.25
P0 ± 0.10	4.00
P1 ± 0.10	8.00
P2 ± 0.05	2.00
D0 + 0.10/-0	1.50
D1 + 0.10/-0	1.50
A0 ± 0.10	4.70
B0 ± 0.10	4.70
K0 ± 0.10	2.30
T ± 0.05	0.35


Inductance and temperature rise vs. current




Inductance and temperature rise vs. current, continued



Inductance & impedance vs. frequency Curve



Inductance & impedance vs. frequency Curve, continued



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm3 <350	Volume mm3 ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm³ <350	Volume mm³ 350 - 2000	Volume mm³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder	
Preheat and soak • Temperature min. (T _{smin})	100 °C	150 °C	
Temperature max. (T _{smax})	150 °C	200 °C	
• Time (T _{smin} to T _{smax}) (t _s)	60-120 seconds	60-120 seconds	
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.	
Liquidous temperature (TL) Time (t_L) maintained above T_L	183 °C 60-150 seconds	217 °C 60-150 seconds	
Peak package body temperature (Tp)*	Table 1	Table 2	
Time $(t_p)^*$ within 5 °C of the specified classification temperature (T_c)	20 seconds*	30 seconds*	
Ramp-down rate (T _p to T _L)	6 °C/ second max.	6 °C/ second max.	
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.	

 $^{^{\}star}$ Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard

1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com/electronics

© 2022 Eaton All Rights Reserved Printed in USA Publication No. ELX1219 BU-ELX22079 July 2022

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

