## SIEMENS

## Data sheet

## US2:17DUD92WC



Non-reversing motor starter, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 5.5-22A, Combination type, 30A non-fusible disconnect, Encl NEMA type 4X 304 S-Steel, Water/dust tight noncorrosive, Standard width enclosure

Fi	gur	es	imi	lar
	-			

product brand name	Class 17 & 25			
design of the product	Full-voltage non-reversing motor starter with non-fusible disconnect			
special product feature	ESP200 overload relay; Dual voltage coil			
General technical data				
Height x Width x Depth [in]	24 × 11 × 8 in			
touch protection against electrical shock	(NA for enclosed products)			
installation altitude [ft] at height above sea level maximum	6560 ft			
ambient temperature [°F]				
<ul> <li>during storage</li> </ul>	-22 +149 °F			
during operation	-4 +104 °F			
ambient temperature				
<ul> <li>during storage</li> </ul>	-30 +65 °C			
<ul> <li>during operation</li> </ul>	-20 +40 °C			
Horsepower ratings				
yielded mechanical performance [hp] for 3-phase AC				
motor				
at 200/208 V rated value	3 hp			
at 220/230 V rated value	3 hp			
<ul> <li>at 460/480 V rated value</li> </ul>	10 hp			
• at 575/600 V rated value	10 hp			
Contactor				
size of contactor	NEMA controller size 1			
number of NO contacts for main contacts	3			
operational current at AC at 600 V rated value	27 A			
mechanical service life (switching cycles) of the main contacts typical	1000000			
Auxiliary contact				
number of NC contacts at contactor for auxiliary contacts	0			
number of NO contacts at contactor for auxiliary contacts	1			
number of total auxiliary contacts maximum	8			
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)			
Coil				
type of voltage of the control supply voltage	AC			
control supply voltage				
• at AC at 60 Hz rated value	220 480 V			
holding power at AC minimum	8.6 W			
apparent pick-up power of magnet coil at AC	218 VA			
apparent holding power of magnet coil at AC	25 VA			

operating range factor control supply voltage rated value of magnet coil	0.85 1.1	
percental drop-out voltage of magnet coil related to the input voltage	50 %	
ON-delay time	19 29 ms	
OFF-delay time	10 24 ms	
Overload relay		
product function		
<ul> <li>overload protection</li> </ul>	Yes	
<ul> <li>phase failure detection</li> </ul>	Yes	
<ul> <li>asymmetry detection</li> </ul>	Yes	
<ul> <li>ground fault detection</li> </ul>	Yes	
test function	Yes	
external reset	Yes	
reset function	Manual, automatic and remote	
trip class	CLASS 5 / 10 / 20 (factory set) / 30	
adjustable current response value current of the current- dependent overload release	5.5 22 A	
make time with automatic start after power failure maximum	3 s	
relative repeat accuracy	1 %	
product feature protective coating on printed-circuit board	Yes	
number of NC contacts of auxiliary contacts of overload relay	1	
number of NO contacts of auxiliary contacts of overload relay	1	
operational current of auxiliary contacts of overload relay		
• at AC at 600 V	5 A	
• at DC at 250 V	1 A	
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)	
insulation voltage (Ui)		
<ul> <li>with single-phase operation at AC rated value</li> </ul>	600 V	
<ul> <li>with multi-phase operation at AC rated value</li> </ul>	300 V	
Disconnect Switch		
response value of switch disconnector	30A / 600V	
design of fuse holder	non-fusible	
operating class of the fuse link	non-fusible	
Enclosure		
degree of protection NEMA rating	4X, 304 stainless steel	
design of the housing	dustproof, waterproof & resistant to corrosion	
Mounting/wiring		
mounting position	vertical	
fastening method	Surface mounting and installation	
type of electrical connection for supply voltage line-side	Box lug	
tightening torque [lbf·in] for supply	35 35 lbf in	
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)	
temperature of the conductor for supply maximum permissible	75 °C	
material of the conductor for supply	AL or CU	
type of electrical connection for load-side outgoing feeder	Screw-type terminals	
tightening torque [lbf·in] for load-side outgoing feeder	35 35 lbf-in	
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (14 2 AWG)	
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C	
material of the conductor for load-side outgoing feeder	AL or CU	
type of electrical connection of magnet coil	Screw-type terminals	
51		
tightening torque [lbf·in] at magnet coil type of connectable conductor cross-sections of magnet	5 12 lbf in	

temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17DUD92WC Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:17DUD92WC Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17DUD92WC⟨=en Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17DUD92WC/certificate				

last modified:

1/25/2022 🖸